
Built to Integrate.

The most versatile industrial-grade tablet that perfectly fits your application.

Tab-IND Series for Use in Industrial Environments



Your automation, our passion.

PEPPERL+FUCHS

Tablet Series Tab-IND®

Digital Workflows at the Point of Work

The Tab-IND series delivers durable, modular tablets and kiosk terminals for demanding industrial applications. Designed for manufacturing, logistics, and field service, it enables reliable digitalization at the point of operation.



Rugged





Tablets	Tab-IND® Rugged Android Tablet	Tab-IND® Rugged Windows Tablet
Highlights	■ Android™ 15 operating system ■ WWAN 5G RedCap model available ■ WiFi 6E ■ 13 MP rear camera + 5 MP front camera ■ 10.1" multitouch display ■ Operable with gloves ■ 9900 mAh battery ■ IP65 degree of protection	■ Windows® 11 LTSC operating system ■ WiFi 6E ■ 13 MP rear camera + 13 MP front camera ■ 8.4" or 10.1" multitouch display ■ Operable with gloves ■ 4950 mAh battery ■ IP65 degree of protection
Display	10.1" display, 1200 × 1920 px	8.4" or 10.1" display, 1200 × 1920 px
Processor	Qualcomm® QCS6490 octa-core 2.1 GHz	Intel® Alder Lake N100, quad-core 2.9 GHz
Memory	8 GB RAM, 128 GB storage	8 GB RAM, 128 GB storage
Communication	■ WWAN 5G RedCap model available ■ WLAN IEEE 802.11 ax + r/k/v ■ Wi-Fi 6E, WiDi, WWAN, BT5.3, BLE ■ GPS/GNSS/Galileo (only 5G model) ■ Front-facing NFC smart card reader with secure element	■ WLAN IEEE 802.11 ax + r/k/v ■ Wi-Fi 6E, WiDi, BT5.3, BLE ■ GPS/GNSS/Galileo ■ Front-facing NFC smart card reader with secure element





Kiosk Terminals	Tab-IND® 15 Kiosk Terminal	Tab-IND® 22 Kiosk Terminal
Highlights	■ Android™ 15 operating system ■ Wi-Fi 6E ■ 15.6" multitouch display ■ GMS certified ■ Cover glass with anti-glare treatment ■ Expandable with barcode scanner, camera, speaker, status light, etc. ■ Mounting options: VESA, in-panel ■ Side USB-C ports for accessories	■ Android™ 13 operating system ■ 13 MP front camera with autofocus ■ 21.5" multitouch display ■ GMS certified ■ Cover glass with anti-glare treatment
Display	15.6" Full HD touch screen (1920 × 1080 px), Brightness: 350 cd/m^2	21.5" Full HD touch screen (1080 × 1920 px), Brightness: 350 cd/m^2
Processor	Qualcomm® QCS6490	Qualcomm® QCS6490
Memory	8 GB RAM, 128 GB storage	8 GB RAM, 128 GB storage
Communication	■ Front-facing NFC antenna integrated behind the display ■ Wi-Fi 6E, BT5.3, LAN,PoE	■ Front-facing NFC antenna integrated behind the display ■ WLAN IEEE 802.11 ax, BT5.2

SmartBacks

Easy Customization for Specific Requirements

Characteristics

- Back covers provide additional features
- Seamless tablet integration with USB, GPIO, and power connections

Advantages

- Easy to customize for new applications
- Simple integration of additional functionalities
- Exclusively available from Pepperl+Fuchs

Features

- Battery extension
- Magnetic card readers
- Ethernet, USB, and more
- Customized industry interfaces (Industrial Ethernet, CAN, IO-Link, and more)
- Wireless connectivity (RFID, UWB, and more)




More information and accessories at:
pepperl-fuchs.com/pf-tab-ind


Accessories




Modular Charging Stations
support 1- to 5-bay charging




Full Docking Station
compatible with scanner frame



Rugged Frame
extended drop resistance up to 1.8 m



Scanner Frame
integrated scanner and extended drop resistance



VESA-75 Smartback
incl. integrated power supply and USB-C interface



Battery SmartBacks
10" tablet extendable with 8" SmartBack or extra battery powerpack

Additional accessories, such as hand and shoulder straps and styluses, are also available.

Your automation, our passion.

- Industrial Sensors
- Industrial Communication and Interfaces
- Enterprise Mobility
- Hazardous Area Products and Solutions

www.pepperl-fuchs.com

Subject to modifications • © Pepperl+Fuchs
Printed in USA • Part. No. 70210629 08/26

Pepperl+Fuchs Quality
Download our latest policy here:

www.pepperl-fuchs.com/quality

PEPPERL+FUCHS