



IO-Link Parameter Datasheet

Distance sensor

OMR60M-R200-2EP-IO* series

Support: fa-info@pepperl-fuchs.com
 Internet: www.pepperl-fuchs.com

DOCT-9036A - Version 1.01.000 / 2024-06-18

General Information

Device Identification

| | |
|-----------|--------------------|
| Vendor ID | 1 (0x0001) |
| Device ID | 1121041 (0x111B11) |

Features

| | |
|------------------------|-----|
| Data Storage | Yes |
| Block Parameterization | Yes |

Communication Characteristics

| | |
|--------------------------------|-----------------------------|
| IO-Link revision | V1.1 (specification V1.1.3) |
| IO-Link backward compatibility | n/a |
| Data transmission rate | COM2 (38.4 kbit/s) |
| Min. cycle time | 4.0 ms |
| Process data input | 6 byte |
| Process data output | 2 bit |
| SIO mode support | yes |
| Compatible master port type | Class A, Class B (see NOTE) |

NOTE: For use at master with port class B, use 3-pole adapter or 3-wire cable.

Profile


| | |
|---------------------------------|----------------|
| Identification and Diagnosis | 16384 (0x4000) |
| Function Class – Product URI | 33026 (0x8102) |
| Smart Sensor – SSP 4.2.1 | 20 (0x0014) |
| Function Class – Sensor Control | 32780 (0x800C) |
| | |
| | |
| | |

Supported Product Variants

| Product ID | Product Name | Description | Connector |
|---------------|------------------------------|-----------------------------------------------------------------------------------------------------|---------------------|
| 295670-100377 | OMR60M-R200-2EP-IO-V31-L | Measurement range 0.2 .. 60 m, adjustable, active high, configurable, Q2 output, M8 plug, 4-pin | Plug, M8, 4-pin |
| 295670-100388 | OMR60M-R200-2EP-IO-V1-L | Measurement range 0.2 .. 60 m, adjustable, active high, configurable, Q2 output, M12 plug, 4-pin | Plug, M12, 4-pin |
| 295670-100401 | OMR60M-R200-2EP-IO-0,3M-V1-L | Measurement range 0.2 .. 60 m, adjustable, active high, configurable, Q2 output, M12 pigtail, 4-pin | Pigtail, M12, 4-pin |

Connection

Connection Diagram



Description

Plug/Pigtail, M8/M12, 4-pin

- 1: Brown - +24V
- 2: White - Q2
- 3: Blue - 0V
- 4: Black - C/Q

Process Data

Process Data Input

| Sub | Name | Data type | Length | Bitoffs. | Value | Unit | Description |
|-----|-----------------------------|-----------|--------|----------|---------------------------------------------------------------|------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| .1 | MDC – Measurement Value | Integer | 32 bit | 16 | 0 .. 2147482880 -2147483640 2147483640 2147483644 | mm | Shows the current measurement value. <i>Out of Range (-)</i> <i>Out of Range (+)</i> <i>No measurement data</i> |
| .2 | MDC - Scale | Integer | 8 bit | 8 | -3 | | Shows the multiplier for the measurement value of the sensor - 10exp(scale). <i>Resolution 1 mm</i> |
| .3 | SSC.1 – Switching Signal | Boolean | 1 bit | 0 | 0 1 | | Indicates the detection status of an object or measurement value below/above a threshold. <i>Low</i> <i>High</i> |
| .4 | SSC.2 – Switching Signal | Boolean | 1 bit | 1 | 0 1 | | Indicates the detection status of an object or measurement value below/above a threshold. <i>Low</i> <i>High</i> |
| .5 | Signal Quality Indicator | UInteger | 2 bit | 2 | 0 1 2 3 | | Shows the quality of the evaluated sensor signal. Quality drops with weak signal or interference. <i>Insufficient</i> <i>Acceptable</i> <i>Good</i> <i>Excellent</i> |

Process Data Output

| Sub | Name | Data type | Length | Bitoffs. | Value | Unit | Description |
|-----|-----------------------------|-----------|--------|----------|--------|------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| .1 | CSC – Sensor Control | Boolean | 1 bit | 0 | 0 1 | | Controls the sensor emitter. If disabled, a substitute value is applied to the process data. <i>Enabled</i> <i>Disabled</i> |
| .2 | CSC – Evaluation Control | Boolean | 1 bit | 1 | 0 1 | | Controls the signal evaluation. If disabled, signal evaluation is inhibited. The last evaluation state and value is maintained in the process data. <i>Enabled</i> <i>Disabled</i> |

NOTE: The process data input content can also be read via parameter 'Process Data Input' at index 40 (0x28).
The process data output content can also be read via parameter 'Process Data Output' at index 41 (0x29).

Parameter Data

| Identification | | | | | | | | |
|----------------|--------------------------|--------|-----------|---------------------|-----------------------------------------|---------------------------------------------------------------------------------------|----|---|
| Index | Parameter | Access | Data type | Length | Default | Description | DS | R |
| 16 (0x10) | Vendor Name | ro | String | 13 byte | Pepperl+Fuchs | The vendor name that is assigned to a Vendor ID. | | |
| 17 (0x11) | Vendor Text | ro | String | 29 byte | www.pepperl-fuchs.com/io-link | Additional information about the vendor. | | |
| 18 (0x12) | Product Name | ro | String | max. 32 byte | See table Supported Product Variants | Complete product name. | | |
| 19 (0x13) | Product ID | ro | String | max. 32 byte | See table Supported Product Variants | Vendor-specific product or type identification (e.g., item number or model number). | | |
| 20 (0x14) | Product Text | ro | String | max. 32 byte | Distance sensor | Additional product information for the device. | | |
| 21 (0x15) | Serial Number | ro | String | 14 byte | | Unique, vendor-specific identifier of the individual device. | | |
| 22 (0x16) | Hardware Revision | ro | String | 7 byte | HW**.** | Unique, vendor-specific identifier of the hardware revision of the individual device. | | |
| 23 (0x17) | Firmware Revision | ro | String | 7 byte | FW**.** | Unique, vendor-specific identifier of the firmware revision of the individual device. | | |
| 24 (0x18) | Application Specific Tag | rw | String | max. 32 byte | Your automation, our passion. | Possibility to mark a device with user- or application-specific information. | Y | F |
| 25 (0x19) | Function Tag | rw | String | max. 32 byte | R200 series | Possibility to mark a device with function-specific information. | Y | F |
| 26 (0x1A) | Location Tag | rw | String | max. 32 byte | *** | Possibility to mark a device with location-specific information. | Y | F |
| 27 (0x1B) | Product URI | ro | String | max. 100 byte | https://pefu.de/<serial number> | Provides a unique instance identification compliant to DIN-SPEC 91406. | | |

| Diagnosis | | | | | | | | | | | |
|---------------|-------------------------------------|--------|----------------------|---------|----------|---------|----------------------------|------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----|----|
| Index .sub | Parameter | Access | Data type | Length | Bitoffs. | Default | Value | Unit | Description | DS | R |
| 36 (0x24) | Device Status | ro | UInteger | 8 bit | | 0 | 0 1 2 3 4 | | Indicator for the current device condition and diagnosis state. <i>Device is OK</i> <i>Maintenance required</i> <i>Out of specification</i> <i>Functional check</i> <i>Failure</i> | | FA |
| 37 (0x25) | Detailed Device Status | ro | Array ^{SO} | 12 byte | | | | | List of all currently pending events in the device. | | FA |
| | .1 Element 1 | | Octetstr | 3 byte | 72 | 0 | | | | | |
| | .2 Element 2 | | Octetstr | 3 byte | 48 | 0 | | | | | |
| | .3 Element 3 | | Octetstr | 3 byte | 24 | 0 | | | | | |
| | .4 Element 4 | | Octetstr | 3 byte | 0 | 0 | | | | | |
| 224 (0xE0) | Operating Hours | ro | UInteger | 32 bit | | | 0 .. 2 ³² -1 | h | Shows the overall hours of operation since initial commissioning. | | |
| 225 (0xE1) | Temperature Indicator | ro | UInteger | 8 bit | | | 0 1 2 3 4 | | Indicates the operation at ambient temperatures close to or in excess of specification limits. <i>Operating condition OK</i> <i>Close to upper limit</i> <i>Upper limit exceeded</i> <i>Close to lower limit</i> <i>Lower limit exceeded</i> | | |
| 226 (0xE2) | Temperature Monitor | ro | Record ^{SO} | 9 byte | | | | | Contains parameters showing current and past conditions of temperature exposure since initial commissioning. | | |
| | .1 Overtemperature Operating Hours | ro | UInteger | 32 bit | 40 | | 0 .. 2 ³² -1 | h | Shows the overall hours of powered operation above the specified temperature limit since initial commissioning. | | |
| | .2 Overtemperature Exceeded Counter | ro | UInteger | 16 bit | 24 | | 0 .. 65535 | | Shows the number of transitions to operating temperatures above the specified limit in powered operation since initial commissioning. | | |
| | .3 Maximum Operating Temperature | ro | Integer | 8 bit | 16 | | -50 .. 125 | °C | Shows the maximum observed temperature in powered operation since initial commissioning. | | |
| | .4 Minimum Operating Temperature | ro | Integer | 8 bit | 8 | | -50 .. 125 | °C | Shows the minimum observed temperature in powered operation since initial commissioning. | | |
| | .5 Device Operating Temperature | ro | Integer | 8 bit | 0 | | -50 .. 125 | °C | Shows the currently observed operating temperature of the device. | | |
| 227 (0xE3) | Power Monitor | ro | Record ^{SO} | 12 byte | | | | | Contains parameters showing current and past conditions of power cycles since initial commissioning. | | |
| | .1 Power Cycle Counter | ro | UInteger | 32 bit | 96 | | 0 .. 2 ³² -1 | | Shows the number of power cycles since initial commissioning (incremented on power-on). | | |
| | .2 Maximum Uptime | ro | UInteger | 32 bit | 64 | | 0 .. 2 ³² -1 | s | Shows the maximum observed powered operating time between power cycles in seconds since initial commissioning. | | |
| | .3 Average Uptime | ro | Integer | 32 bit | 32 | | 0 .. 2 ³² -1 | s | Shows the average observed powered operating time between power cycles in seconds since initial commissioning. | | |
| | .4 Uptime | ro | Integer | 32 bit | 0 | | 0 .. 2 ³² -1 | s | Shows the current operating time since the last power cycle in seconds. | | |
| 232 (0xE8) | Device Characteristic | ro | Record ^{SO} | 10 byte | | | | | Shows relevant key characteristics of the device for use in applications. | | |
| | .1 Min. Detection Range | ro | Integer | 32 bit | 48 | 20 | | mm | Shows the value of the minimum specified detection range. | | |
| | .2 Max. Detection Range | ro | Integer | 32 bit | 16 | 60500 | | mm | Shows the value of the maximum specified detection range. | | |

| Diagnosis | | | | | | | | | | | |
|-------------------|-------------------------------------|--------|----------------------|---------|----------|---------|--------|------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----|----|
| Index .sub | Parameter | Access | Data type | Length | Bitoffs. | Default | Value | Unit | Description | DS | R |
| .3 | Supply Current Requirement | ro | UInteger | 16 bit | 0 | 25 | | mA | Shows the maximum specified supply current for the device excluding load. | | |
| 238 (0xEE) | Device Operating State | ro | Record ^{SO} | 8 bit | | | | | Shows relevant key characteristics of the device for use in applications. | | |
| | Sensor Control | ro | Boolean | 1 bit | 0 | 0 | 0 1 | | Indicates if sensor operation is inhibited by any remote signal (process data, I/O signal or parameter value) or by an internal error condition. <i>Enabled</i> <i>Disabled</i> | | |
| | Local Control (in IO-Link mode) | ro | Boolean | 1 bit | 1 | 0 | 0 1 | | Indicates that local control elements are temporarily enabled for adjustment or teach-in in IO-Link mode. <i>Disabled</i> <i>Enabled</i> | | |
| 239 (0xEF) | I/O Feature | ro | UInteger | 16 bit | | 2 | 2 | | Shows the supported I/O features of the device. <i>Second signal in- / output on pin 2 / white wire</i> | | |
| 127 (0x7F) | Indication Control | rw | Record ^{SO} | 8 bit | | | | | Provides control functions for diagnosis purposes for indicators or display. | | FA |
| | Locator Indication | rw | Boolean | 1 bit | 0 | 0 | 0 1 | | Enables a defined flashing pattern of the indicator LEDs for better spotting a sensor in field application. <i>Disabled</i> <i>Enabled</i> | | FA |
| 16512 (0x4080) | Measurement Data Channel Descriptor | ro | Record ^{SO} | 11 byte | | | | | Descriptor containing characteristic data of the measurement data channel (process data MV). | | |
| | Lower Value | ro | Integer | 32 bit | 56 | 200 | | mm | Shows the lower value of the measurement range. | | |
| | Upper Value | ro | Integer | 32 bit | 24 | 60000 | | mm | Shows the upper value of the measurement range. | | |
| | Unit Code | ro | UInteger | 16 bit | 8 | 1010 | | | Shows the unique code for the physical unit. | | |
| | Scale | ro | Integer | 8 bit | 0 | -3 | | | Shows the multiplier for measurement value - 10exp(scale). | | |

| Parameterization & Configuration | | | | | | | | | | | |
|----------------------------------|------------------|--------|-----------|--------|----------|---------|-------------------------|------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|----|----|
| Index .sub | Parameter | Access | Data type | Length | Bitoffs. | Default | Value | Unit | Description | DS | R |
| 60 (0x3C) | SSC.1 Param | rw | Record | 8 byte | | | | | Defines the setpoint values for switching signal channel 1. | Y | FA |
| | SP1 | rw | Integer | 32 bit | 32 | 9000 | 0 .. 120000 | mm | Defines the setpoint 1 value for the switching signal channel. | Y | FA |
| | SP2 | rw | Integer | 32 bit | 0 | 6000 | 0 .. 120000 | mm | Defines the setpoint 2 value for the switching signal channel. | Y | FA |
| 61 (0x3D) | SSC.1 Config | rw | Record | 6 byte | | | | | Defines the configuration parameter for switching signal channel 1. | Y | FA |
| | Logic | rw | UInteger | 8 bit | 40 | 0 | 0 1 | | Defines the logical representation of the switching signal SSC in the process data. <i>High active</i> <i>Low active</i> | Y | FA |
| | Mode | rw | UInteger | 8 bit | 32 | 2 | 0 1 2 3 128 | | Defines the evaluation mode for the switching signal SSC. <i>Deactivated</i> <i>Single point</i> <i>Window</i> <i>Two point</i> <i>Centered window</i> | Y | FA |
| | Hysteresis | rw | Integer | 32 bit | 0 | 15 | 0 .. 500 | mm | Defines the hysteresis at the switch point. A higher hysteresis may help to improve the stability in critical applications. | Y | FA |
| 62 (0x3E) | SSC.2 Param | rw | Record | 8 byte | | | | | Defines the setpoint values for switching signal channel 2. | Y | FA |
| | SP1 | rw | Integer | 32 bit | 32 | 8000 | 0 .. 120000 | mm | Defines the setpoint 1 value for the switching signal channel. | Y | FA |
| | SP2 | rw | Integer | 32 bit | 0 | 4000 | 0 .. 120000 | mm | Defines the setpoint 2 value for the switching signal channel. | Y | FA |
| 63 (0x3F) | SSC.2 Config | rw | Record | 6 byte | | | | | Defines the configuration parameter for switching signal channel 2. | Y | FA |
| | Logic | rw | UInteger | 8 bit | 40 | 0 | 0 1 | | Defines the logical representation of the switching signal SSC in the process data. <i>High active</i> <i>Low active</i> | Y | FA |
| | Mode | rw | UInteger | 8 bit | 32 | 2 | 0 1 2 3 128 | | Defines the evaluation mode for the switching signal SSC. <i>Deactivated</i> <i>Single point</i> <i>Window</i> <i>Two point</i> <i>Centered window</i> | Y | FA |
| | Hysteresis | rw | Integer | 32 bit | 0 | 15 | 0 .. 500 | mm | Defines the hysteresis at the switch point. A higher hysteresis may help to improve the stability in critical applications. | Y | FA |
| 64 (0x40) | SSC.1 Config Ext | rw | Record | 5 byte | | | | | Provides configuration options for switching delay functions and timings for switching signal channel 1. | Y | FA |
| | Off delay | rw | UInteger | 16 bit | 24 | 0 | 0 .. 60000 | ms | Defines the switching delay for an on-to-off transition of the switching signal (0: disabled). | Y | FA |
| | On Delay | rw | UInteger | 16 bit | 8 | 0 | 0 .. 60000 | ms | Defines the switching delay for an off-to-on transition of the switching signal (0: disabled). | Y | FA |
| | Delay Mode | rw | UInteger | 8 bit | 0 | 0 | 0 1 | | Selects between a combination of 'on' and 'off' delay times or 'on' and 'one-shot' delay times. <i>On / Off delay</i> <i>On delay / One shot</i> | Y | FA |
| 65 (0x41) | SSC.2 Config Ext | rw | Record | 5 byte | | | | | Provides configuration options for switching delay functions and timings for switching signal channel 2. | Y | FA |

| Parameterization & Configuration | | | | | | | | | | | |
|----------------------------------|-------------------------------------|--------|-----------|--------|----------|---------|---------------------------------------------------|------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----|----|
| Index .sub | Parameter | Access | Data type | Length | Bitoffs. | Default | Value | Unit | Description | DS | R |
| .1 | Off delay | rw | UInteger | 16 bit | 24 | 0 | 0 .. 60000 | ms | Defines the switching delay for an on-to-off transition of the switching signal (0: disabled). | Y | FA |
| .2 | On Delay | rw | UInteger | 16 bit | 8 | 0 | 0 .. 60000 | ms | Defines the switching delay for an off-to-on transition of the switching signal (0: disabled). | Y | FA |
| .3 | Delay Mode | rw | UInteger | 8 bit | 0 | 0 | 0 1 | | Selects between a combination of 'on' and 'off' delay times or 'on' and 'one-shot' delay times. <i>On / Off delay</i> <i>On delay / One shot</i> | Y | FA |
| 66 (0x42) | SSC.1 Config Ext – SP Offset | rw | Integer | 32 bit | | 500 | 10 .. 12000 | mm | Defines the offset of the switch point relative to the setpoint for switching signal channel 1. | Y | FA |
| 67 (0x43) | SSC.2 Config Ext – SP Offset | rw | Integer | 32 bit | | 500 | 10 .. 12000 | mm | Defines the offset of the switch point relative to the setpoint for switching signal channel 2. | Y | FA |
| 58 (0x3A) | Teach Select | rw | UInteger | 8 bit | | 1 | 1 2 | | Selects the switching signal channel for which a teach procedure will be applied. <i>SSC.1</i> <i>SSC.2</i> | | FA |
| 59 (0x3B) | Teach Result | ro | Record | 8 bit | | | | | Shows the complete result information of the teach procedure including current state and result flags. | | FA |
| .1 | State | ro | UInteger | 4 bit | 0 | 0 | 0 1 2 3 4 5 7 12 13 14 | | Indicates the current state of the teach procedure. <i>Idle</i> <i>SP1 success</i> <i>SP2 success</i> <i>SP1, SP2 success</i> <i>Wait for command</i> <i>Busy</i> <i>Error</i> <i>Measurement offset success</i> <i>AO SP1 success</i> <i>AO SP2 success</i> | | FA |
| .2 | Flag SP1 TP1 | ro | Boolean | 1 bit | 4 | 0 | 0 1 | | Indicates the current teach result for the teach point. <i>Initial or not ok</i> <i>Ok</i> | | FA |
| .3 | Flag SP1 TP2 | ro | Boolean | 1 bit | 5 | 0 | 0 1 | | Indicates the current teach result for the teach point. <i>Initial or not ok</i> <i>Ok</i> | | FA |
| .4 | Flag SP2 TP1 | ro | Boolean | 1 bit | 6 | 0 | 0 1 | | Indicates the current teach result for the teach point. <i>Initial or not ok</i> <i>Ok</i> | | FA |
| .5 | Flag SP2 TP2 | ro | Boolean | 1 bit | 7 | 0 | 0 1 | | Indicates the current teach result for the teach point. <i>Initial or not ok</i> <i>Ok</i> | | FA |
| 97 (0x61) | Eval Config – Signal Filter | rw | UInteger | 8 bit | | 0 | 0 1 2 3 4 5 | | Defines the grade of filtering in the signal evaluation. A higher filtering improves stability in critical applications but increases the response time. <i>3 ms</i> <i>6 ms</i> <i>12 ms</i> <i>25 ms</i> <i>50 ms</i> <i>100 ms</i> | Y | FA |
| 98 (0x62) | Eval Config - Measurement Offset | rw | Integer | 32 bit | | 0 | -60000 .. 60000 | mm | Defines the offset of the measurement value for setting of a zero reference or calibration of mounting tolerances. | Y | FA |

| Parameterization & Configuration | | | | | | | | | | | |
|----------------------------------|----------------------------------|--------|----------------------|--------|----------|---------|-------------------------|------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----|----|
| Index .sub | Parameter | Access | Data type | Length | Bitoffs. | Default | Value | Unit | Description | DS | R |
| 99 (0x63) | Eval Config – Smart Hold | rw | UInteger | 8 bit | | 0 | 0 1 | | Reduces the noise of the distance value that is output at a standstill. The measurement remains active. <i>Disabled</i> <i>Enabled</i> | Y | FA |
| 104 (0x68) | PD Output Config | rw | Record ^{SO} | 1 byte | | | | | Defines which PD Output data are enabled to control the sensor function. | Y | FA |
| .1 | Sensor Control | rw | UInteger | 1 bit | 0 | 0 | 0 1 | | Enabled: The sensor function is controlled via process data output. A '1' at 'PD Output - Sensor Control' disables the sensor emitter. Distance measurement is disabled. <i>Disabled</i> <i>Enabled</i> | Y | FA |
| .2 | Evaluation Control | rw | UInteger | 1 bit | 0 | 0 | 0 1 | | Enabled: The signal evaluation is controlled via process data output. A '1' at 'PD Output - Evaluation Control' inhibits signal evaluation. The last evaluation state is maintained. <i>Disabled</i> <i>Enabled</i> | Y | FA |
| 120 (0x78) | Event Config | rw | Record ^{SO} | 2 byte | | | | | Defines which event sources can trigger events. | Y | FA |
| .2 | Warning – No Measurement Data | rw | Boolean | 1 bit | 1 | 0 | 0 1 | | Enabled: An event is generated if sensor signals do not allow a valid processing of measurement values or data are not available. <i>Disabled</i> <i>Enabled</i> | Y | FA |
| .9 | Warning – Sensor Disabled | rw | Boolean | 1 bit | 8 | 0 | 0 1 | | Enabled: An event is generated if the sensor is set to a disabled mode by a remote control signal (process data, I/O signal or parameter value) or by an internal error condition. <i>Disabled</i> <i>Enabled</i> | Y | FA |
| 113 (0x71) | I/O Config – I/Q Type | rw | UInteger | 8 bit | | 0 | 0 1 4 5 6 | | Defines the output or input characteristic at pin 2 or white wire. <i>Factory default</i> <i>Output - Push-pull</i> <i>High impedance</i> <i>Input – High active</i> <i>Input – Low active</i> | Y | FA |
| 117 (0x75) | I/O Config – Output Function | rw | UInteger | 8 bit | | 0 | 0 1 2 3 255 | | Defines the specific function at the additional I/O terminal if configured as output. <i>Factory default</i> <i>Antivalent</i> <i>Equivalent</i> <i>SSC2 - switching signal</i> <i>Inactive (constant)</i> | Y | FA |
| 118 (0x76) | I/O Config – Input Function | rw | UInteger | 8 bit | | 0 | 0 1 | | Defines the specific function at the additional I/O terminal if configured as input. <i>Factory default</i> <i>Test mode (emitter off)</i> | Y | FA |
| 125 (0x7D) | Device Operation | rw | UInteger | 8 bit | | 0 | 0 1 | | Allows setting the device into different operational states e.g. for diagnosis purposes. After a power cycle or communication restart the feature will be reset to normal operation. <i>Normal operation</i> <i>Sensor emitter disabled</i> | | FA |

| Parameterization & Configuration | | | | | | | | | | | |
|----------------------------------|------------------------------------|--------|----------------------|--------|----------|---------|--------|------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----|----|
| Index .sub | Parameter | Access | Data type | Length | Bitoffs. | Default | Value | Unit | Description | DS | R |
| 126 (0x7E) | UI Control | rw | Record ^{SO} | 8 bit | | | | | Provides possibilities for controlling the functionality of the user interface or local control elements. | | FA |
| | Local Control (in IO-Link mode) | rw | Boolean | 1 bit | 1 | 0 | 0 1 | | During IO-Link communication local control is generally inhibited. Setting this parameter to 'Enabled' allows for adjustment or teach-in over local control elements. After a power cycle or communication restart the feature will be disabled. <i>Disabled</i> <i>Enabled</i> | | FA |
| 12 (0x0C) | Device Access Locks | rw | Record ^{SO} | 2 byte | | | | | The access to the device parameters can be restricted by setting appropriate flags within this parameter. | Y | FA |
| | Local Parameterization | rw | Boolean | 1 bit | 1 | 0 | 0 1 | | This lock prevents the device settings from being changed via local operating elements on the device. <i>Unlocked</i> <i>Locked</i> | Y | FA |

| Observation | | | | | | | | | | | |
|---------------|--------------------------------|--------|----------------------|---------|----------|---------|---------------------------------------------------------------|------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----|----|
| Index .sub | Parameter | Access | Data type | Length | Bitoffs. | Default | Value | Unit | Description | DS | R |
| 36 (0x24) | Device Status | ro | UInteger | 8 bit | | 0 | | | Indicator for the current device condition and diagnosis state. See <i>Diagnosis – Device Status</i> | | FA |
| 236 (0xEC) | Observation Data | ro | Record ^{S0} | 11 byte | | | | | Provides a set of relevant data suitable for observation purposes. | | |
| .1 | MDC – Measurement Value | ro | Integer | 32 bit | 56 | 0 | 0 .. 2147482880 -2147483640 2147483640 2147483644 | mm | Shows the current measurement value. <i>Out of range (-)</i> <i>Out of range (+)</i> <i>No measurement data</i> | | |
| .2 | DSC – Signal Quality Indicator | ro | UInteger | 8 bit | 48 | 0 | 0 1 2 3 | | Shows the quality of the evaluated sensor signal. Quality drops with weak signal or interference. <i>Insufficient</i> <i>Acceptable</i> <i>Good</i> <i>Excellent</i> | | |
| .3 | SSC.1 – Switching Signal | ro | UInteger | 8 bit | 40 | 0 | 0 1 | | Indicates the detection status of an object or measurement value below/above a threshold. <i>Low</i> <i>High</i> | | |
| .4 | SSC.2 – Switching Signal | ro | UInteger | 8 bit | 32 | 0 | 0 1 | | Indicates the detection status of an object or measurement value below/above a threshold. <i>Low</i> <i>High</i> | | |
| .5 | Teach Value | ro | Integer | 32 bit | 0 | 0 | 0 .. 2147482880 | mm | Shows the teach value which has been determined in the last teach procedure. | | |

NOTE 1: The parameter data provide the attributes DS (Data Storage) and R (Reset behavior). The following rules apply:

DS: Parameter marked with 'Y' (yes) are exchanged with the master via the data storage mechanism.

R: Parameter marked with 'F' are reset to the factory default value upon reception of the command 'Back-to-box'.

Parameter marked with 'A' are reset to the factory default value upon reception of the command 'Application Reset'.

NOTE 2: Parameter with datatype Record or Array, which are marked with 'S0' can only be accessed over subindex 0 (whole parameter object). Subindex access to single items is not possible.

Command Interface

| Index | Parameter | Access | Data type | Length | Value | Description |
|-------------|----------------|--------|-----------|--------|-------------------|---------------------------------------------------------------------------------------------------------------------------------------|
| 2 (0x02) | System Command | wo | UInteger | 8 bit | See command value | Command interface for applications. A positive acknowledge indicates the complete and correct finalization of the requested function. |

| Command Value | Command | Description |
|---------------|--------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 129 (0x81) | Application Reset | The parameters of the technology-specific application are set to default values. Identification parameter remain unchanged. An upload to the data storage of the master will be executed, if activated in the port configuration of the master. |
| 131 (0x83) | Back-to-box | The parameters of the device are set to factory default values and communication will be inhibited until the next power cycle. Note: Directly detach the device from the master port! |
| 65 (0x41) | Teach SP1 | Determine setpoint 1 in a single teach procedure. The new setpoint 1 value is automatically applied after successful execution. |
| 66 (0x42) | Teach SP2 | Determine setpoint 2 in a single teach procedure. The new setpoint 2 value is automatically applied after successful execution. |
| 170 (0xAA) | Teach Measurement Offset | Determine the measurement offset within a specific installation setup. The new measurement offset is automatically applied after successful execution. |

Error Codes

| Code | Additional code | Name | Description |
|------------|-----------------|---------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------|
| 128 (0x80) | 17 (0x11) | Index not available | Read or write access attempt to a non-existing index. |
| 128 (0x80) | 18 (0x12) | Subindex not available | Read or write access attempt to a non-existing subindex of an existing index. |
| 128 (0x80) | 32 (0x20) | Service temporarily not available | Parameter not accessible due to the current state of the technology-specific application. |
| 128 (0x80) | 33 (0x21) | Service temporarily not available - local control | Parameter not accessible. The device is currently in an ongoing, locally controlled operation. |
| 128 (0x80) | 34 (0x22) | Service temporarily not available - device control | Parameter not accessible. The technology-specific application is currently in a remotely triggered operation. |
| 128 (0x80) | 35 (0x23) | Access denied | Write access to a read-only parameter or read access to write-only parameter. |
| 128 (0x80) | 48 (0x30) | Parameter value out of range | Written parameter value is outside of the permitted value range. |
| 128 (0x80) | 49 (0x31) | Parameter value above limit | Written parameter value is above its specified value range. |
| 128 (0x80) | 50 (0x32) | Parameter value below limit | Written parameter value is below its specified value range. |
| 128 (0x80) | 51 (0x33) | Parameter length overrun | Written parameter is longer than specified. |
| 128 (0x80) | 52 (0x34) | Parameter length underrun | Written parameter is shorter than specified. |
| 128 (0x80) | 53 (0x35) | Function not available | Written command is not supported by the technology-specific application. |
| 128 (0x80) | 54 (0x36) | Function temporarily unavailable | Written command is unavailable due to the current state of the technology-specific application. |
| 128 (0x80) | 64 (0x40) | Invalid parameter set | Written single parameter value collides with other existing parameter settings. |
| 128 (0x80) | 65 (0x41) | Inconsistent parameter set | Parameter set inconsistencies at the end of block parameter transfer. Device plausibility check failed. |
| 129 (0x81) | 129 (0x81) | Invalid combination of setpoint and measurement offset values | Measurement offset and setpoint setting result in a switch point outside of the specified measurement range. Check values. |

Event Codes

| Code | Type | Name | Description |
|----------------|---------|-------------------------------------------------|--------------------------------------------------|
| 20480 (0x5000) | Error | Device hardware fault | Exchange device |
| 36161 (0x8D41) | Warning | Measurement not possible, invalid data | Check sensor adjustment or target position. |
| 36163 (0x8D43) | Warning | Temperature outside specified temperature range | Check sensor environment. |
| 36224 (0x8D80) | Warning | Sensor operation disabled | Object detection or measurement is not possible. |