



# Retroreflective sensor RL61-55-Z/92/136



- Cost-optimized series for standard tasks in a special design
- Compact design
- Wide range of mounting options thanks to cubic housing design with M30 thread
- 360° high visibility LEDs
- Programmable ON-delay, OFF-delay, and One-shot timers
- 4-in-1 output (push-pull)

Retroreflective sensor with polarization filter




### **Function**

The Series 61 sensor family is a comprehensive product line, offering five sensing modes. Each sensor is equipped with four LEDs that are highly visible from all directions, indicating Power-On, target presence and marginal excess gain. The widely recognized, polycarbonate housing provides a IP67 protection degree rating. Color-coded labels are clearly printed on the housing to easily identify the sensing mode. DC models offer a 4-in-1 output while AC/DC models have a SPDT relay output rated to 3 A. All versions come standard with an integral multifunction timer, sensitivity adjustment and Light-ON/Dark-ON switch. Series 61 sensors are cross-talk protected and have a high degree of resistance to ambient lighting. Each sensor can be mounted via front and rear slots, rear dovetail guide or M30 x 1.5 mounting base. Additionally, cabled sensor models provide ½" - 14 NPT internal threads for use with flexible conduit.

### **Application**

- Object tracking in material handling, and the packaging sector
- Material flow monitoring
- Bin occupancy check in storage technology
- Fine positioning in high-bay warehouses
- · Presence and height monitoring on pallet conveyors
- Single-beam protection for automatic industrial gates and elevator doors
- Protection at automatic gates

# **Dimensions**



# **Technical Data**

General specifications		
Effective detection range		0 18 m
Reflector distance		0.3 18 m
Threshold detection range		25 m
Reference target		FE-RR1 reflector
Light source		LED
Light type		modulated visible red light , 630 nm
Polarization filter		yes
Diameter of the light spot		approx. 350 mm at a distance of 18 m
Opening angle		1.1 °
Ambient light limit		5000 Lux; according EN 60947-5-2
Indicators/operating means		
Operation indicator		2 LEDs green
Function indicator		2 LEDs yellow on: reflector inside the sensing range off: reflector outside the sensing range
Control elements		Light-on/dark-on changeover switch
Control elements		Sensing range adjuster
Control elements		Time adjuster ( 0 50 ms )
Electrical specifications		
Operating voltage	$U_B$	10 30 V DC
Ripple		10 %
No-load supply current	I <sub>0</sub>	≤ 35 mA


Protection class		II , rated voltage ≤ 250 V AC with pollution degree 1-2 according to IEC 60664-1 Output circuit basis insulation of input circuit according to EN 50178, rated insulation voltage 240 V AC
Output		
Switching type		light/dark on, switchable
Signal output		2 push-pull (4 in 1) outputs, short-circuit protected, reverse polarity protected
Switching voltage		max. 30 V DC
Switching current		max. 100 mA
Voltage drop	$U_{\text{d}}$	≤ 2.5 V
Switching frequency	f	500 Hz
Response time		≤1 ms
Timer function		DIP switch for selection of operating modes
Compliance with standards and directives		
Standard conformity		
Product standard		EN 60947-5-2:2007 IEC 60947-5-2:2007
Approvals and certificates		
EAC conformity		TR CU 020/2011
UL approval		cULus
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-40 55 °C (-40 131 °F)
Storage temperature		-40 70 °C (-40 158 °F)
Mechanical specifications		
Housing width		45 mm
Housing height		73.7 mm
Housing depth		48.6 mm
Degree of protection		IP67
Connection		4-pin, M12 x 1 connector
Material		
Housing		PC (Polycarbonate)

# **Connection Assignment**

Tightening torque, fastening screws

Optical face

Mass



- O = Light on
- = Dark on

**PMMA** 

120 g

max. 2 Nm


# **Connection Assignment**




Wire colors in accordance with EN 60947-5-2

BN (brown)  $\mathsf{WH}$ 2 3 4 (white) BU (blue) BK (black)


# **Assembly**






1	Operating display	green
2	Signal display	yellow
3	Sensing range adjuster	
4	Time adjuster	
5	DIP-switches	

# **Characteristic Curve**




# RL(K)61-55-Z **Excess Gain vs. Sensing Distance** 60 50 40 Reflector Excess Gain C110-2 FE-RR1 H85 H50 30 20 10 0 5000 10000 25000 15000 20000 Distance X [mr

**5**PEPPERL+FUCHS





# MPZB01 Mounting bracket with vertical slots MPZB02 Mounting bracket with circular slots MPZB06 Ball and Swivel Mounting Bracket MPZB07 Ball and Swivel Vertical Mounting Plate V1-G-2M-PUR Female cordset single-ended M12 straight A-coded, 4-pin, PUR cable grey V1-W-2M-PUR Female cordset single-ended M12 angled A-coded, 4-pin, PUR cable grey





DIP-Switch position -

### **Adjustment Instructions**

### Intended use:

The retroreflective sensor contains the emitter and receiver in a single housing. The light from transmitter is reflected back from a reflector to the receiver. If an object interrupts the light beam, the switching function is initiated.

### Mounting instructions:

The sensor can be mounted using the through-holes or with a mounting bracket (not included with delivery).

The base surface must be flat to avoid distorting the sensor housing during mounting. It is advisable to secure the bolts and screws with washers so that the sensor does not become misaligned.

### **Adjustment Instructions:**

Connect the sensor to operating voltage and the green LED lights up solid.

Mount a suitable reflector opposite the sensor and make a rough adjustment.

The precise adjustment is done by swiveling the sensor horizontally and vertically. With optimum light reception, the yellow LED lights up solid. It will blink if the sensor requires fine adjustment.

Object detection:

Move an object into the light beam. If the object is detected, the yellow LED switches off. If it does not switch off, reduce the sensitivity with the potentiometer until it does. It should light up solid when the object is removed.

### Cleaning:

The yellow LED flashes if the light received decreases (e.g. dirty lenses).

We recommend that you clean the optical interfaces and check all connections at regular intervals.