


Glass fiber optic LCR 18-3,2-2,0-K2



■ M8 x 1 thread

Glass fiber optic - diffuse with PVC covering

Dimensions



Technical Data

General specifications

Fiber optic length	l	2000 mm
Fiber optic diameter	d	5 mm
Adapter form		18
End piece		thread
Bending radius		min. 25 mm (static)
Fiber bundle diameter		2.3 mm
Fiber configuration	Fv	optical seperated
Opening angle		68 °

Approvals and certificates

Approvals		CE
-----------	--	----

Ambient conditions

Ambient temperature		-20 ... 85 °C (-4 ... 185 °F) [Adapter]
		-20 ... 85 °C (-4 ... 185 °F) [End head and Covering]
Storage temperature		-20 ... 85 °C (-4 ... 185 °F)

Mechanical specifications

Degree of protection		IP65
----------------------	--	------

Release date: 2022-08-04 Date of issue: 2022-08-04 Filename: 021749_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

PF PEPPERL+FUCHS

Technical Data

Material		
Optical face		glass
Sheathing		PVC
Core		Glass fiber
End piece		Stainless steel 1.4305 / AISI 303
Adapter		PBT
Extraction force		100 N
Fiber optic amplifiers		
Device series		VL18LL VariKont M

Application

Attention:

Fiber optics must not be twisted or kinked. Excessive tensile loads will lead to destruction. Contact with petrol or organic solvents must be prevented.



Release date: 2022-08-04 Date of issue: 2022-08-04 Filename: 021749_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com