Release date: 2023-04-04 Date of issue: 2023-04-04 Filename: 117836_eng.pdf



Retroreflective sensor

MLV12-54/47/92



- Robust photoelectric sensor series in a widely used standard housing
- Resistant against noise: reliable operation under all conditions
- Clear and functional display concept for the operating modes
- High level of stability thanks to the metal housing frame
- Tightly sealed thanks to welded plastic components
- Suitable for operation at low temperatures down to -40 °C

Robust retroreflective sensor for complex applications, small design, polarization filter, 9 m detection range, red light, light/dark on, 2 PNP outputs, M12 plug










Dimensions





Technical Data


| General specifications Effective detection range | | 0 6.5 m |
|---|----------------|---|
| Reflector distance | | 0 6.5 m |
| | | |
| Threshold detection range | | 9 m |
| Reference target | | H85-2 reflector |
| Light source | | LED |
| Light type | | modulated visible red light , 660 nm |
| Polarization filter | | yes |
| Diameter of the light spot | | approx. 170 mm at detection range 6.5 m |
| Opening angle | | 1.5° |
| Ambient light limit | | |
| Continuous light | | 50000 Lux |
| Modulated light | | 5000 Lux |
| Functional safety related parameters | | |
| MTTF _d | | 1000 a |
| Mission Time (T _M) | | 20 a |
| Diagnostic Coverage (DC) | | 0% |
| ndicators/operating means | | |
| Operation indicator | | LED green, flashes in case of short-circuit |
| Function indicator | | 2 LEDs yellow, light up when light beam is free, flash when falling short of the stabilit control, off when light beam is interrupted |
| Control elements | | rotary switch for light/dark, sensitivity adjuster |
| Electrical specifications | | |
| Operating voltage | U_B | 10 30 V DC |
| Ripple | | max. 10 % |
| No-load supply current | I ₀ | max. 40 mA |
| Output | | |
| Switching type | | light/dark on switchable |
| Signal output | | 2 PNP outputs, complementary, short-circuit protected, reverse polarity protected, open collector |
| Switching voltage | | max. 30 V DC |
| Switching current | | max. 0.2 A |
| Voltage drop | U_{d} | ≤ 2.5 V DC |
| Switching frequency | f | 1000 Hz |
| Response time | | 0.5 ms |
| Conformity | | |
| Product standard | | EN 60947-5-2 |
| Compliance with standards and directives | | |
| Standard conformity | | |
| Shock and impact resistance | | IEC / EN 60068. half-sine, 40 g in each X, Y and Z directions |
| Vibration resistance | | IEC / EN 60068-2-6. Sinus. 10 -150 Hz, 5 g in each X, Y and Z directions |
| Approvals and certificates | | |
| Protection class | | II, rated voltage ≤ 300 V AC with pollution degree 1-2 according to IEC 60664-1 |
| UL approval | | cULus |
| CCC approval | | CCC approval / marking not required for products rated ≤36 V |
| Ambient conditions | | · · |
| Ambient temperature | | -40 60 °C (-40 140 °F) |
| Storage temperature | | -40 75 °C (-40 167 °F) |
| Mechanical specifications | | , |
| Housing width | | 41.5 mm |
| Housing height | | 49 mm |
| , , | | 15 mm |
| Housing depth | | 13 111111 |

Retroreflective sensor MLV12-54/47/92

Technical Data

| Connection | 4-pin, M12 metal connector, 90° rotatable |
|--------------|---|
| Material | |
| Housing | Frame: nickel plated, die cast zinc, Laterals: glass-fiber reinforced plastic PC |
| Optical face | Plastic pane |
| Mass | 60 g |

Connection



- O = Light on
- = Dark on


Connection Assignment




Wire colors in accordance with EN 60947-5-2

| 1 | BN | (brown) |
|---|----|---------|
| 2 | WH | (white) |
| 3 | BU | (blue) |
| 4 | BK | (black) |

Assembly





| | 1 | Operating display green | | |
|---|---|-------------------------|--------|--|
| | 2 | Switch state | yellow | |
| | 3 | Light/dark switch | | |
| | 4 | Sensitivity adjuster | | |
| Γ | 5 | Optical axis emitter | | |
| | 6 | Optical axis receiver | | |


Mounting


The sensors can be secured directly using thru-holes or using a mounting bracket or mounting clamp. Mounting brackets and clamping elements are available as accessories.

Ensure that the background is level to prevent the housing from becoming distorted when the fittings are tightened.

Secure the nut and screw with spring disks to prevent the sensor from becoming misaligned.

Characteristic Curve





System Description

System Description

The retro-reflective sensor contains both an emitter and a receiver in a single housing. A reflector reflects the light from emitter back to the receiver. If an object interrupts the light beam, the switching function is initiated.

Commissioning

Aligning the sensor: Apply the operating voltage to the sensor. The operating indicator lights up green.

Mount a suitable reflector opposite the light barrier. Roughly align the sensor (without an object) with the reflector. Next, adjust the sensor to the reflector by swiveling the sensor horizontally and vertically so that the yellow signal indicator lights up continuously. In the event of misalignment, the yellow signal indicator flashes.

Commissioning
Checking object detection: Follow the steps below to check that the sensor detects objects as required.
Position the object in the beam path of the sensor.

When the object is detected, the yellow signal indicator goes out. If the yellow signal indicator remains lit, reduce the sensitivity of the potentiometer until the yellow signal indicator goes out.

When the object disappears from the beam path of the sensor, the yellow signal indicator lights up again continuously.

Maintenance

Maintenance

Cleaning: If the transmission reception deteriorates, e.g., due to dirt, the yellow signal indicator on the receiver flashes. Clean the optical interfaces of the sensor (e.g., lenses) at regular intervals.

Maintenance: Check the mounting fittings and the electrical connections regularly.

Accessories

| The W | OMH-MLV12-HWG | Mounting bracket for series MLV12 sensors |
|-------|---------------|---|
| | OMH-MLV12-HWK | Mounting bracket for series MLV12 sensors |
| 12 | OMH-K01 | dove tail mounting clamp |
| 1 | OMH-K02 | dove tail mounting clamp |
| ~ | OMH-K03 | dove tail mounting clamp |
| | OMH-06 | Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm |