


Coupling

9410 12*12

- Precision coupling

Precision coupling

Dimensions



Technical Data

Mechanical specifications	
Shaft diameter	d1 = 12 mm , d2 = 12 mm
Material	Delrin 107, AlMgSi1, hard coated
Mass	25 g
Rotational speed	max. 15000 min $^{-1}$
Max. torque	1 Nm
Tightening torque, fastening screws	1.3 Nm
Radial offset	max. ± 0.5 mm
Axial offset	max. ± 0.3 mm
Angle error	max. ± 1.5 °
Torsional rigidity	50 Nm / rad
Moment of inertia	20 kg m^2 x 10^{-7}
Mounting	clamping flange

Release date: 2022-08-09 Date of issue: 2022-12-12 Filename: 045022_eng.pdf