


Glass fiber optic


LSE 18-1,9-5,0-K10



- Chemical-resistant

Glass fiber optic - thru-beam with silicon covering

Dimensions



Technical Data

General specifications

Fiber optic length	l	5000 mm
Fiber optic diameter	d	5.3 mm
Adapter form		18
End piece		Thread / cylindrical right angle
Bending radius		min. 20 mm
Fiber bundle diameter		1.9 mm

Approvals and certificates

Approvals		CE
-----------	--	----

Ambient conditions

Ambient temperature		-20 ... 85 °C (-4 ... 185 °F) [Adapter] -40 ... 180 °C (-40 ... 356 °F) [End head and Covering]
Storage temperature		-20 ... 85 °C (-4 ... 185 °F)

Mechanical specifications

Degree of protection		IP65
Material		
Optical face		glass

Release date: 2021-07-07 Date of issue: 2021-07-07 Filename: 045522_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

PF PEPPERL+FUCHS

Technical Data

Sheathing	silicone
Core	Glass fiber
End piece	Stainless steel 1.4305 / AISI 303
Adapter	PBT
Extraction force	70 N
Fiber optic amplifiers	
Device series	VariKont M

Application

Attention:

Fiber optics must not be twisted or kinked. Excessive tensile loads will lead to destruction. Contact with petrol or organic solvents must be prevented.

