




Coupling

9402 8*8

- Universally suitable for backlash-free rotation transmission
- Highly vibration-isolating
- Well misalignment compensation
- Low torsion spring stiffness
- Small reset forces
- No movable parts
- Very rugged construction

Spring steel coupling

Dimensions



Technical Data

Ambient conditions	
Operating temperature	-30 ... 120 °C (-22 ... 248 °F)
Mechanical specifications	
Shaft diameter	d1 = 8 mm , d2 = 8 mm
Material	
Spring	spring steel, nickel plated
End piece	Diecast zinc
Mass	28 g
Rotational speed	max. 3000 min
Max. torque	0.5 Nm
Radial offset	max. ± 1 mm
Axial offset	max. ± 1 mm
Angle error	max. ± 5 °
Torsion angle	at torque 0.25 Nm drive shaft view
CW rotation direction	50 °
CCW rotation direction	70 °
Moment of inertia	10 kg m ² x 10 ⁻⁷

Release date: 2022-08-27 Date of issue: 2022-12-12 Filename: 046723_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

PF PEPPERL+FUCHS

Technical Data

Mounting	clamp screws M4 x 4, DIN 916
Tightening torque of clamping screws	max. 1.5 Nm

Release date: 2022-08-27 Date of issue: 2022-12-12 Filename: 046723_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.comUSA: +1 330 486 0001
fa-info@us.pepperl-fuchs.comGermany: +49 621 776 1111
fa-info@de.pepperl-fuchs.comSingapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com **PEPPERL+FUCHS**