

# $\epsilon$

# **Model Number**

### UCC1000-30GM-E6-V1


Single head system

#### **Features**

- · 2 independent switch outputs
- High chemical resistance through PTFE coated transducer surface
- Switch points can be taught-in
- Window function can be selected
- **Temperature compensation**
- Compact design
- Plug connection

# **Diagrams**

## Characteristic response curves



Curve 1: flat plate 100 mm x 100 mm Curve 2: round bar, Ø 25 mm

# **Technical data**

General specifications	
Sensing range	200 1000 mm
Unusable area	0 200 mm
Standard target plate	100 mm x 100 mm
Transducer frequency	approx. 175 kHz
Response delay	< 100 ms

Indicators/operating means

LED vellow switching state output 1, program function output 1 switching state output 2, program function output 2 LED red/green solid green: Power on

green, flashing: program function, object detected solid red: Connector removed

red, flashing: error, program function object not detected

Temperature compensation , Switch points programming ,

output function setting

**Electrical specifications** 

Temperature/TEACH-IN connector

10 ... 30 V DC , ripple 10  $\%_{SS}$ Operating voltage U<sub>B</sub>

Power consumption P<sub>0</sub> ≤ 600 mW

Output

2 switch outputs PNP, NO/NC Output type

Rated operating current Ie 200 mA, short-circuit/overload protected

Voltage drop U<sub>d</sub>  $\leq$  3 V DC

Repeat accuracy ≤ 0.1 % of full-scale value

Switching frequency f ≥5 Hz

Range hysteresis H  $\leq$  3.2 % of the set operating distance

Temperature influence < 2 % of full-scale value ( $\leq$  0.2 % / K without temperature

compensation)

Standard conformity EN 60947-5-2 Standards

**Ambient conditions** 

**Dimensions** 

-25 ... 70 °C (-13 ... 158 °F) Ambient temperature Storage temperature -40 ... 85 °C (-40 ... 185 °F)

Mechanical specifications

Connection type Connector M12 x 1, 4-pin

Protection degree


Material

Housing Stainless steel, PTB

epoxy resin/hollow glass bead mixture; Polyurethane foam, PTFE coated Transducer

153 g


# Mass



### **Electrical Connection**

# Standard symbol/Connection:

(version E6, pnp)



Core colours in accordance with EN 60947-5-2.

#### **Pinout**

# **Connector V1**



# **Accessories**

#### **BF 30**

Mounting flange, 30 mm

Universal mounting bracket for cylindrical sensors with a diameter of 5 ... 30 mm

#### **UC-30GM-PROG**

#### V1-G-2M-PVC

Cable socket, M12, 4-pin, PVC cable

#### V1-W-2M-PVC

Cable socket, M12, 4-pin, PVC cable

# Description of the sensor functions

This ultrasonic sensor features a four-pole temperature/TEACH-IN plug, that can be connected in four different positions. These have the following significance.

Plug position	Meaning
A1	TEACH-IN switching point A1
A2	TEACH-IN switching point A2
E2/E3	Switching: 2 independent switching positions/window function
T	Temperature compensation

# **Description of the TEACH-IN procedure**

- Remove temperature plug
- Cut and restore supply voltage (e.g. by removing and replacing unit plug)

#### **TEACH-IN** of switching points 1 or 2

- Set object to desired switching point
- Connect TEACH-IN plug in pos. A1 or A2
- Green LED flashes when object detected, red LED flashes when no object detected
- Pull the plug (the current object position is taught and stored when the plug is removed!!)

#### **TEACH-IN of switching function**

- Connect TEACH-IN plug in pos. E2/E3
- The yellow LED indicates the switching function
- E2: 2 independent switching points (NO)
- E3: window function: switch output 1 NO, switch output 2 NC
- Pull the plug when the desired function is activated, otherwise reconnect the TEACH-IN plug in pos. E2/E3
- Pull plug

# Completing the TEACH-IN procedure

- Connect TEACH-IN plug in pos. T. Temperature compensation is now activated.


If the temperature plug has not been plugged in within 5 minutes, the sensor will return to normal mode without temperature compensation.

#### Default setting

# **Additional Information**

# Programmed switching output function

Position of insert Switch output functions




A1: unusable area

A2: nominal sensing range

# **LED Displays**

Displays depending on position of temperature/	Green dual	Red dual	Yellow LED	Yellow LED
TEACH-IN plug position	LED	LED	A1/E2	A2/E3
TEACH-IN switching point output A1 Object detected No object detected	flashes	off	flashes	off
	off	flashes	flashes	off
TEACH-IN switching point output A2 Object detected No object detected	flashes	off	off	flashes
	off	flashes	off	flashes
TEACH-IN of switch output functions: E2: 2 independent switching positions E3: window function	on on	off off	flashes off	off flashes
Normal mode temperature compensated plug pulled/shorted	on off	off on	switching state A1	switching state A2
Interference (e.g. compressed air)	off	flashes	previous state	previous state

# **LED-Window**



# **Mounting conditions**

If the sensor is installed in places where the operating temperature can fall below 0 °C, the BF30, BF30-F or BF 5-30 fixing clamp must be used.