
Features

- Dummy
- · DIN rail mounting

Function


The Zener barrier is an empty housing. This device will be used as a dummy, to reserve place and wiring for future expansions.


Assembly



 ϵ

Connection





Singapore: +65 6779 9091

pa-info@sg.pepperl-fuchs.com

www.pepperl-fuchs.com

_
0
~
=
(0)
ena.xr
071818
~
$\overline{}$
m
~
_
~
0
~
2018-04-09
~
_
4
Ò
Y
σ
~
_
\simeq
CA
O)
_
ഗ
m
.22
*=
U
m
ė
ate
ate
Date o
Date
Date
Date of issue
2018-04-09 08:45 Date of
2018-04-09 08:45
2018-04-09 08:45
2018-04-09 08:45
2018-04-09 08:45
2018-04-09 08:45
2018-04-09 08:45
2018-04-09 08:45
2018-04-09 08:45
2018-04-09 08:45
2018-04-09 08:45

Hazardous area connection	
Connection	terminals 1, 2, 3, 4
Safe area connection	
Connection	terminals 5, 6, 7, 8
Indicators/settings	
Labeling	space for labeling at the front
Conformity	
Degree of protection	IEC 60529
Ambient conditions	
Ambient temperature	-20 60 °C (-4 140 °F)
Storage temperature	-25 70 °C (-13 158 °F)
Relative humidity	max. 75 %, without condensation
Mechanical specifications	
Degree of protection	IP20
Connection	screw terminals
Core cross-section	max. 2 x 2.5 mm ²
Mass	approx. 150 g
Dimensions	12.5 x 115 x 110 mm (0.5 x 4.5 x 4.3 inch)
Construction type	modular terminal housing, see system description
Mounting	on 35 mm DIN mounting rail acc. to EN 60715:2001
General information	
Supplementary information	Observe the certificates, declarations of conformity, instruction manuals, and manuals where applicable. For information see www.pepperl-fuchs.com.

