


# Inductive analog sensor


## NBN15-30GM60-I3



- Inductive analog
- Output 0 mA ... 20 mA
- Non-flush



### Dimensions



### Technical Data

#### General specifications

Output type	Analog current output
Installation	non-flush
Output polarity	DC
Measurement range	5 ... 15 mm
Output type	3-wire

#### Nominal ratings

Operating voltage	$U_B$	15 ... 30 V DC
Repeat accuracy		0 ... 200 $\mu$ m
No-load supply current	$I_0$	$\leq$ 12 mA

#### Analog output

Output type	0 ... 20 mA
Slope of output characteristic	2 mA / mm
Linearity error	$\leq \pm 5$ % of full-scale value

Release date: 2022-06-30 Date of issue: 2022-06-30 Filename: 282838\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111  
fa-info@de.pepperl-fuchs.com


Singapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS

## Technical Data

Load resistor	≤ 500 Ω
Rate of current rise	
0 ... 20 mA	≤ 17.5 A/s
20 ... 0 mA	≤ 16.4 A/s
Temperature drift	≤ ± 0.15 %/K of the measured value
Residual ripple	± 125 μA
<b>Compliance with standards and directives</b>	
Standard conformity	
Standards	EN 60947-5-2:2007 IEC 60947-5-2:2007 EN 60947-5-7:2003 IEC 60947-5-7:2003
<b>Approvals and certificates</b>	
UL approval	cULus Listed, General Purpose
CCC approval	CCC approval / marking not required for products rated ≤36 V
<b>Ambient conditions</b>	
Ambient temperature	-25 ... 70 °C (-13 ... 158 °F)
<b>Mechanical specifications</b>	
Connection type	cable PVC , 2 m
Core cross section	0.75 mm <sup>2</sup>
Housing material	Stainless steel V2A
Sensing face	PBT
Degree of protection	IP67
Cable	
Cable diameter	6.4 mm ± 0.2 mm
Bending radius	> 10 x cable diameter

## Connection



## Accessories

	<b>BF 30</b>	Mounting flange, 30 mm
---	--------------	------------------------

Release date: 2022-06-30 Date of issue: 2022-06-30 Filename: 282838\_eng.pdf