

# Glass fiber optic


## LMR 18-2,7-0,5-K9



- Sturdy metallic version
- Chemical-resistant

Glass fiber optic - diffuse with metal covering

### Dimensions



### Technical Data

#### General specifications

Fiber optic length	l	500 mm
Fiber optic diameter	d	6.8 mm
Adapter form		18
End piece		Cylindrical right angle
Bending radius		min. 20 mm
Fiber bundle diameter		1.9 mm
Angle of divergence		68 °

#### Approvals and certificates

Approvals		CE
-----------	--	----

#### Ambient conditions

Ambient temperature		-20 ... 85 °C (-4 ... 185 °F) [Adapter] -50 ... 200 °C (-58 ... 392 °F) [End head and Covering]
Storage temperature		-20 ... 85 °C (-4 ... 185 °F)

#### Mechanical specifications

Degree of protection		IP40
Material		

Release date: 2021-07-05 Date of issue: 2021-07-05 Filename: 020968\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

**Technical Data**

Optical face	glass
Sheathing	metal
Core	Glass fiber
End piece	Stainless steel 1.4305 / AISI 303
Adapter	PBT
Extraction force	120 N
<b>Fiber optic amplifiers</b>	
Device series	VL18LL VariKont M

## Application

**Attention:**

Fiber optics must not be twisted or kinked. Excessive tensile loads will lead to destruction. Contact with petrol or organic solvents must be prevented.

