

0102


## **Model Number**

NJ25-50-N-Y19292


## **Features**


- Comfort series
- 25 mm not embeddable

## Connection



# **Dimensions**





# **Technical Data**

General specifications		
Switching element function		NAMUR NC
Rated operating distance	s <sub>n</sub>	25 mm
Installation		not embeddable
Output polarity		NAMUR
Assured operating distance	sa	0 20.25 mm
Reduction factor r <sub>Al</sub>		0.4
Reduction factor r <sub>Cu</sub>		0.3
Reduction factor r <sub>V2A</sub>		0.85

ricadollori lactor 172A		0.00
Nominal ratings		
Nominal voltage	U <sub>o</sub>	8 V
Switching frequency	f	0 250 Hz

 $\begin{tabular}{lll} Current consumption & & \geq 3 mA \\ Measuring plate not detected & & \geq 1 mA \\ Measuring plate detected & & \leq 1 mA \\ \end{tabular}$ 

Standard conformityEMC in accordance withIEC / EN 60947-5-2:2004StandardsDIN EN 60947-5-6 (NAMUR)

Ambient conditions
Ambient temperature -25 ... 100 °C (248 ... 373 K)

Mechanical specifications

 Connection type
 2 m, PVC cable

 Core cross-section
 0.75 mm²

 Housing material
 PBT

 Sensing face
 PBT

 Protection degree
 IP67

General information
Use in the hazardous area see instruction manuals
Category 2G

www.pepperl-fuchs.com

### ATEX 2G

Instruction

#### Device category 2G

Directive conformity Standard conformity

CE symbol

Ex-identification

**EC-Type Examination Certificate** Appropriate type

Effective internal capacitance Ci

Effective internal inductance Li

General

Highest permissible ambient temperature

Installation Comissioning

Maintenance

[Fett]Special conditions

Protection from mechanical danger

### Manual electrical apparatus for hazardous areas

for use in hazardous areas with gas, vapour and mist

EN 60079-0:2006, EN 60079-11:2007 Ignition protection "Intrinsic safety" Use is restricted to the following stated conditions €0102

⟨Ex⟩ II 2G Ex ia IIC T6

PTB 00 ATEX 2048 X

NJ 25-50-N...

≤ 150 nF; a cable length of 10 m is considered.

 $\leq$  140  $\mu H$  ; a cable length of 10 m is considered.

The apparatus has to be operated according to the appropriate data in the data sheet and in this instruction manual. The EC-Type Examination Certificate has

to be observed. The special conditions must be adhered to!
Directive 94/9EG and hence also EC-Type Examination Certificates apply in general only to the use of electrical apparatus under atmospheric conditions. The use in ambient temperatures of > 60 °C was tested with regard to hot surfaces by the mentioned certification authority.

If the equipment is not used under atmospheric conditions, a reduction of the permissible minimum ignition energies may have to be taken into consideration.

The temperature ranges, according to temperature class, are given in the EC-Type Examination Certificate.

Laws and/or regulations and standards governing the use or intended usage goal must be observed. The intrinsic safety is only assured in connection with an appropriate related apparatus and according to the proof of intrinsic safety.

No changes can be made to apparatus, which are operated in hazardous areas. Repairs to these apparatus are not possible.

When used in the temperature range below -20 °C the sensor should be protected from knocks by the provision of an additional housing.

**PEPPERL+FUCHS** 

Pepperl+Fuchs Group

www.pepperl-fuchs.com