

# Base for read/write station U-P4-R4

- Degree of protection IP67
- Simple bus system with up to 30 units
- Serial interface RS 485, addressable

Base with addressable serial Interface RS 485



### **Function**


The base is used in combination with an upper part, the IPT\*-FP read/write station. An addressable RS 485 interface is available. It is thus possible to create a simple bus connection with up to 30 subscribers.

The address is set and the terminating resistor for the bus is connected via DIP switches.

The read/write station is connected to a higher-order control system via the serial interface and receives the commands for writing and/or reading code or data carriers via this interface.

#### **Dimensions**





## **Technical Data**

Indicators/operating means		
DIP switch		Setting the station address bus connection ON = active OFF = non-active
Electrical specifications		
Rated operating voltage	$U_e$	20 30 V DC , ripple 10 $\%_{SS}$ , PELV
Power consumption	P <sub>0</sub>	max. 4 W with read/write head IPT*-FP
Galvanic isolation		
Operating voltage/interface		functional insulation acc. to DIN EN 50178, rated insulation voltage 50 $\ensuremath{V_{\text{eff}}}$
Interface		
Physical		RS-485, addressable, up to 30 bases, address 1 30

Release date: 2020-03-31 Date of issue: 2020-03-31 Filename: 113813\_eng.pdf

Technical Data	
Protocol	ASCII
Transfer rate	1200; 2400; 4800; 9600; 19200; 38400 Bit/s
Cable length	≤ 1200 m
Ambient conditions	
Ambient temperature	-25 70 °C (-13 158 °F)
Storage temperature	-40 85 °C (-40 185 °F)
Mechanical specifications	
Degree of protection	IP67 according to EN 60529 with IPT*-FP
Connection	screw terminals
Interface cable	2 conductor, acc. to RS-485
Supply	up to 3 x 1.5 mm <sup>2</sup>
Material	
Housing	diecast aluminum

# Connection

