

# Thru-beam sensor LD28/LV28-F1/49/76a/82b/115




- Universal series with highly versatile fields of use
- Resistant against noise: reliable operation under all conditions
- Highly visible LED as alignment aid in receiver optics
- Emitter with test input
- Version with red light

Universal thru-beam sensor, large housing design, 30 m detection range, red light, 25 kHz transmission frequency, light/dark on, DC version, NPN output, PNP output, test input, pre-fault output, fixed cable



### **Dimensions**



Technical Data

#### System components LD28-F1/76a/115 Emitter Receiver LV28-F1/49/82b/115 General specifications Effective detection range 0 ... 30 m Threshold detection range 40 m Light source LED modulated visible red light, 660 nm Light type Alignment aid LED red (in receiver lens) illuminated constantly: beam is interrupted, flashes: reaching switching point, off: sufficient stability control Transmitter frequency F1 = 25 kHzapprox. 0.6 m at 30 m Diameter of the light spot Emitter 1.2°, Opening angle Receiver 5° Ambient light limit 50000 Lux Functional safety related parameters $\mathsf{MTTF}_\mathsf{d}$ 620 a Mission Time (T<sub>M</sub>) 20 a Diagnostic Coverage (DC) 90 % Indicators/operating means Operation indicator LED green Function indicator LED yellow: 1. LED lit constantly: signal > 2 x switching point (function reserve) 2. LED flashes: signal between 1 x switching point and 2 x switching point 3. LED off: signal < switching point Control elements sensitivity adjustment (Adjustment to < 25% of the effective operating range), Lighton/dark-on changeover switch **Electrical specifications** 10 ... 30 V DC Operating voltage $U_{B}$ 10 % Ripple No-load supply current Emitter: ≤ 50 mA In Receiver: ≤ 35 mA Input emitter deactivation at $+U_B$ ( $I_{max.}$ < 3 mA at 30 V DC) Test input Output 1 PNP transistor, short-circuit protected, protected from reverse polarity, open collector, Umax = 30 V DC, Imax = 0.2 Å Stability alarm output The output becomes inactive if the signal level has fallen below the function reserve for approx. 10 s (yellow and red LEDs flash). If the light beam is interrupted four times during this period, the output immediately becomes inactive. Switching type light/dark on, switchable 1 NPN, 1 PNP synchronized-switching, short-circuit protected, reverse polarity Signal output protected, open collectors Switching voltage max. 30 V DC Switching current max. 200 mA 1000 Hz Switching frequency Response time 0.5 ms Conformity Product standard EN 60947-5-2 Approvals and certificates Protection class II, rated voltage ≤ 250 V AC with pollution degree 1-2 according to IEC 60664-1 **UL** approval cULus Listed, Class 2 power source



CCC approval

**Ambient conditions** 

Ambient temperature

Storage temperature


-40 ... 60 °C (-40 ... 140 °F)

-40 ... 75 °C (-40 ... 167 °F)

CCC approval / marking not required for products rated ≤36 V


#### **Mechanical specifications** Housing width 25.8 mm 88 mm Housing height Housing depth 54.3 mm Degree of protection IP67 Connection 2.5 m, 5-wire, fixed cable, Euronorm Material Housing Plastic ABS Optical face Plastic pane Mass 500 g (emitter and receiver)


# **Connection Assignment**




- O = Light on
- = Dark on

## **Characteristic Curve**







# **Accessories**

0.	OMH-05	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
	OMH-21	Mounting bracket: mounting aid for sensors in the RL* series
	OMH-22	Mounting aid for RL* series
	OMH-RLK29-HW	Mounting bracket for rear wall mounting
	OMH-RL28-C	Weld slag cover model