


Glass fiber optic LCR 04-1,1-2,0-G



- M4 x 20 thread

Glass fiber optic - diffuse with PVC covering

Dimensions



Technical Data

General specifications

Fiber optic length	l	2000 mm
Fiber optic diameter	d	3.6 mm
Adapter form		04
End piece		thread
Bending radius		min. 15 mm
Fiber bundle diameter		1.8 mm optical face: 2.5 mm ²
Fiber configuration	Fv	optical seperated
Angle of divergence		approx. 69 °

Approvals and certificates

Approvals		CE
-----------	--	----

Ambient conditions

Ambient temperature		-20 ... 85 °C (-4 ... 185 °F) [Adapter] -20 ... 85 °C (-4 ... 185 °F) [End head and Covering]
Storage temperature		-20 ... 85 °C (-4 ... 185 °F)

Mechanical specifications

Degree of protection		IP65
----------------------	--	------

Release date: 2021-07-05 Date of issue: 2021-07-05 Filename: 119738_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Technical Data

Material	
Optical face	glass
Sheathing	PVC
Core	Glass fiber
End piece	Stainless steel 1.4305 / AISI 303
Adapter	PVC
Extraction force	at probe at 20°C: 120 N
Fiber optic amplifiers	
Device series	MLV41-LL

Application

Attention:

Fiber optics must not be twisted or kinked. Excessive tensile loads will lead to destruction. Contact with petrol or organic solvents must be prevented.

