




### Model Number

NBN8-18GM50-E2-M

### Features

- Basic series
- 8 mm not embeddable
- e1-Type approval

### Connection




### Accessories

#### BF 18

Mounting flange, 18 mm

## Dimensions



## Technical Data

### General specifications

Switching element function	PNP	NO
Rated operating distance	$s_n$	8 mm
Installation	not embeddable	
Output polarity	DC	
Assured operating distance	$s_a$	0 ... 6.48 mm
Reduction factor $r_{Al}$	0.5	
Reduction factor $r_{Cu}$	0.4	
Reduction factor $r_{V2A}$	0.7	

### Nominal ratings

Operating voltage	$U_B$	10 ... 30 V
Switching frequency	$f$	0 ... 500 Hz
Reverse polarity protected	reverse polarity protected	
Short-circuit protection	pulsing	
Voltage drop	$U_d$	$\leq 3$ V
Operating current	$I_L$	0 ... 200 mA
Off-state current	$I_r$	0 ... 0.5 mA typ. 0.1 $\mu$ A at 25 °C
No-load supply current	$I_0$	$\leq 18$ mA
Indication of the switching state	all direction LED, yellow	

### Ambient conditions

Ambient temperature	-25 ... 70 °C (-13 ... 158 °F)
---------------------	--------------------------------

### Mechanical specifications

Connection type	cable PVC, 2 m
Core cross-section	0.34 mm <sup>2</sup>
Housing material	brass, nickel-plated
Sensing face	PBT
Protection degree	IP67

### Compliance with standards and directives

Standard conformity	
Standards	EN 60947-5-2:2007 IEC 60947-5-2:2007

### Approvals and certificates

e1 Type approval	95/54/EC
------------------	----------