

Release date: 2012-05-04 09:21 Date of issue: 2012-05-04 051660_eng.xml

Subject to modifications without notice Pepperl+Fuchs Group

www.pepperl-fuchs.com

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com Germany: +49 621 776-4411 fa-info@pepperl-fuchs.com

Copyright Pepperl+Fuchs Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



ATEX 2G

Instruction

Device category 2G Directive conformity Standard conformity

CE symbol

Ex-identification

EC-Type Examination Certificate Appropriate type Effective internal capacitance C_i Effective internal inductance L General

Highest permissible ambient temperature

Installation, Comissioning

Maintenance

Special conditions

Manual electrical apparatus for hazardous areas

for use in hazardous areas with gas, vapour and mist 94/9/EG EN 50014:1997, EN 50020:1994 Ignition protection "Intrinsic safety" Use is restricted to the following stated conditions €0102

⟨€x⟩ II 2G EEx ia IIC T6

PTB 99 ATEX 2128 X RC15-...-N3... \leq 90 nF ; a cable length of 10 m is considered.

 \leq 70 μH ; a cable length of 10 m is considered. The apparatus has to be operated according to the appropriate data in the data sheet and in this instruction manual. The EC-Type Examination Certificate has to

be observed. The special conditions must be adhered to!

The temperature ranges, according to temperature class, are given in the EC-Type Examination Certificate.

Laws and/or regulations and standards governing the use or intended usage goal must be observed. The intrinsic safety is only assured in connection with an appropriate related apparatus and according to the proof of intrinsic safety.

No changes can be made to apparatus, which are operated in hazardous areas. Repairs to these apparatus are not possible.

