

Features

- 1-channel
- DC version, negative polarity
- Working voltage 26.5 V at 10 μ A
- Series resistance max. 341 Ω
- Fuse rating 50 mA
- DIN rail mounting
- Replaceable back-up fuse


Function

The Zener Barrier prevents the transfer of unacceptably high energy from the safe area into the hazardous area.



The zener diodes in the Zener Barrier are connected in the reverse direction. The breakdown voltage of the diodes is not exceeded in normal operation. If this voltage is exceeded, due to a fault in the safe area, the diodes start to conduct, causing the fuse to blow. The Zener Barrier has a negative polarity, i. e. the cathodes of the zener diodes are grounded.

Additionally this Zener Barrier is equipped with a replaceable fuse.

Assembly



Connection



Zone 2
Div. 2

Release date 2018-04-09 08:47 Date of issue 2018-04-09 072203_eng.xml

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com

General specifications		
Type		DC version, negative polarity
Electrical specifications		
Nominal resistance		300 Ω
Series resistance		max. 341 Ω
Fuse rating		50 mA
Hazardous area connection		
Connection		terminals 1, 2
Safe area connection		
Connection		terminals 7, 8
Rated voltage	U _N	28 V
Supply voltage		max. 28 V
Working voltage		26.5 V at 10 μA
Conformity		
Degree of protection		IEC 60529
Ambient conditions		
Ambient temperature		-20 ... 60 °C (-4 ... 140 °F)
Storage temperature		-25 ... 70 °C (-13 ... 158 °F)
Relative humidity		max. 75 % , without condensation
Mechanical specifications		
Degree of protection		IP20
Connection		self-opening connection terminals, max. core cross section 2 x 2.5 mm ²
Mass		approx. 150 g
Dimensions		12.5 x 115 x 110 mm (0.5 x 4.5 x 4.3 inch)
Construction type		modular terminal housing , see system description
Mounting		on 35 mm DIN mounting rail acc. to EN 60715:2001
Data for application in connection with hazardous areas		
EU-Type Examination Certificate		BAS 00 ATEX 7096 , for additional certificates see www.pepperl-fuchs.com
Marking		⊕ II (1)GD [EEx ia] IIC (-20 °C ≤ T _{amb} ≤ 60 °C)
Voltage	U _o	28 V
Current	I _o	93 mA
Power	P _o	650 mW
Supply		
Maximum safe voltage	U _m	250 V
Series resistance		min. 301 Ω
Permissible connection values [EEx ia]		
Certificate		
Marking		TÜV 99 ATEX 1484 X , observe statement of conformity
Directive conformity		
Directive 94/9/EC		EN 50014, EN 50020, EN 50021
International approvals		
FM approval		
Control drawing		116-0118
CSA approval		
Control drawing		116-0119
General information		
Supplementary information		EC-Type Examination Certificate, Statement of Conformity, Declaration of Conformity, Attestation of Conformity and instructions have to be observed where applicable. For information see www.pepperl-fuchs.com .

Release date 2018-04-09 08:47 Date of issue 2018-04-09 072203_eng.xml