



Inductive sensor NJ5-18GM50-E



■ 5 mm flush



Dimensions



Technical Data

General specifications

Switching function		Normally open (NO)
Output type		NPN
Rated operating distance	s_n	5 mm
Installation		flush
Output polarity		DC
Assured operating distance	s_a	0 ... 4.05 mm
Actual operating distance	s_r	4.5 ... 5.5 mm typ. 5 mm
Reduction factor r_{AI}		0.2
Reduction factor r_{Cu}		0.15
Reduction factor r_{304}		0.62
Output type		3-wire

Nominal ratings

Operating voltage	U_B	10 ... 60 V
-------------------	-------	-------------

Technical Data

Switching frequency	f	0 ... 1500 Hz
Hysteresis	H	1 ... 15 typ. 6 %
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Voltage drop	U _d	≤ 3 V
Voltage drop at I _L		
Voltage drop I _L = 100 mA, switching element on	U _d	1.5 ... 2.5 V typ. 1.9 V
Operating current	I _L	0 ... 200 mA
Lowest operating current	I _m	0 mA
Off-state current	I _r	0 ... 0.5 mA typ. 0.01 mA
Off-state current T _U = 40 °C, switching element off		≤ 100 µA
No-load supply current	I ₀	≤ 9 mA
Time delay before availability	t _v	≤ 30 ms
Switching state indicator		LED, yellow

Compliance with standards and directives

Standard conformity		
Standards		EN 60947-5-2:2007 IEC 60947-5-2:2007

Approvals and certificates

UL approval		cULus Listed, General Purpose
CSA approval		cCSAus Listed, General Purpose
CCC approval		Certified by China Compulsory Certification (CCC)


Ambient conditions

Ambient temperature		-25 ... 70 °C (-13 ... 158 °F)
Storage temperature		-40 ... 85 °C (-40 ... 185 °F)

Mechanical specifications

Connection type		cablc PVC , 2 m
Core cross-section		0.5 mm ²
Housing material		Stainless steel 1.4305 / AISI 303
Sensing face		PBT
Degree of protection		IP67

Connection



Accessories

	BF 18	Mounting flange, 18 mm
	EXG-18	Quick mounting bracket with dead stop