



Model Number

NBB1,5-8GM50-E0-C-V3

Features

- Weld Immune

Accessories

V3-WM

Female connector, M8, 3-pin, field attachable

V3-GM

Female connector, M8, 3-pin, field attachable

V3-WM-2M-PUR

Cable socket, M8, 3-pin, PUR cable

BF 8

Mounting flange, 8 mm

V3-GM-2M-PUR

Cable socket, M8, 3-pin, PUR cable

Technical Data

General specifications

Switching element function		NPN	NO
Rated operating distance	s_n	1.5 mm	
Installation		flush	
Assured operating distance	s_a	0 ... 1.215 mm	
Reduction factor r_{AI}		0.3	
Reduction factor r_{Cu}		0.25	
Reduction factor r_{304}		0.65	

Nominal ratings

Operating voltage	U_B	10 ... 30 V	
Switching frequency	f	0 ... 1800 Hz	
Reverse polarity protection		reverse polarity protected	
Short-circuit protection		pulsing	
Voltage drop	U_d	≤ 3 V	
Operating current	I_L	0 ... 100 mA	
No-load supply current	I_0	≤ 20 mA	
Alternating magnetic field	B	150 mT	
Switching state indicator		LED, yellow	

Standard conformity

Standards	IEC / EN 60947-5-2:2004
-----------	-------------------------


Ambient conditions

Ambient temperature	-25 ... 70 °C (-13 ... 158 °F)
---------------------	--------------------------------


Mechanical specifications

Housing material	Brass, PTFE coated
Sensing face	PPS; Ryton R4
Degree of protection	IP67

Dimensions



Electrical Connection



Pinout





Wire colors in accordance with EN 60947-5-2

1		BN	(brown)
3		BU	(blue)
4		BK	(black)

Release date: 2015-02-24 10:43 Date of issue: 2015-02-24 085309_eng.xml