**Dimensions** 



**VISC**� CE C US

#### **Model Number**

#### ML4.2-8-H-60-RT/40b/110/115


Background suppression sensor with 2 m fixed cable

#### **Features**


- Precise background suppression •
- Very small black-white difference
- Small, sharp light spot •
- Highly visible LEDs for Power-On, • switching status, short-circuit, and undervoltage
- Metal-reinforced fastening holes
- Tamper-proof version with no adjustments
- Push-pull output

### **Product information**

The ML4.2 series is characterized by a robust, powerful and standard design in a miniature housing. The housing offers IP67/ IP69K degree of protection, a scratch- and chemical-resistant lens, highly visible LEDs and robust all-metal bushings for mounting. Adjustable and tamper-proof sensors are available with a universal push-pull output and an electrical light ON/dark ON switch. The sensors have a high ambient light limit. Reflections from the background are suppressed. The unusually small, sharp light spot and the quick response time offer maximum switching precision on object edges.. Both red and infrared light sources are available. A high-performance fixed focus background suppressor is a useful feature. The sensors are suitable for precise object detection and open up a wide range of application fields.




### **Electrical connection**





# Indicators/operating means



1	operating display	green
2	indication of the switching state	yellow
3	receiver axis	
4	emitter axis	

Pepperl+Fuchs Group

www.pepperl-fuchs.com

fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com **EPPPERL+FUCHS** 1

Technical data			Accessories
General specifications			
Detection range		10 60 mm	OMH-4.1
Detection range max.		10 80 mm	Mounting Clamp
Background suppression		starts from 80 mm	OMH-ML6
Light source		LED	Mounting bracket
Light type		modulated visible red light , 660 nm	Mounting bracket
Black/White difference (6 %/90 %	6)	approx. 10 mm	OMH-ML6-U
Diameter of the light spot	•)	approx. 4 mm at 60 mm	Mounting bracket
Angle of divergence		approx. 5 °	
Ambient light limit		TP	OMH-ML6-Z
Continuous light		40000 Lux	Mounting bracket
Modulated light		5000 Lux	
Functional safety related param	neters		Other suitable accessories can be found at
MTTF <sub>d</sub>		1940 a	www.pepperl-fuchs.com
Mission Time (T <sub>M</sub> )		20 a	
Diagnostic Coverage (DC)		0%	
Indicators/operating means			
Operation indicator		LED green, statically lit Power on , Undervoltage indicator:	
Operation indicator		Green LD, pulsing (approx. 0.8 Hz) , short-circuit : LED green flashing (approx. 4 Hz)	
Function indicator		LED yellow: lights when object is detected	
Electrical specifications			
Operating voltage	UB	10 30 V DC	
Ripple		10 %	
No-load supply current	I <sub>0</sub>	< 25 mA	
Output			
Switching type		light/dark on electrically switchable	
Signal output		Push-pull output, short-circuit protected, reverse polarity protected	
Switching voltage		max. 30 V DC	
Switching current		max. 100 mA	
Voltage drop	U <sub>d</sub>	≤ 2.5 V DC	
Switching frequency	f	1000 Hz	
Response time		0.5 ms	
Conformity			
Product standard		EN 60947-5-2	
Ambient conditions			
Ambient temperature		-20 60 °C (-4 140 °F)	
Storage temperature		-20 75 °C (-4 167 °F)	
Mechanical specifications			
Housing width		13.9 mm	
Housing height		31.4 mm	
Housing depth		18 mm	
Degree of protection		IP67 / IP69K	
Connection		2 m fixed cable	
Material			
Housing		ABS	
Optical face		glass pane	
Cable		PUR	
Mass		approx. 50 g	
Compliance with standards and directives	ł		
Standard conformity			
Shock and impact resistance Vibration resistance		IEC / EN 60068. half-sine, 40 g in each X, Y and Z directions IEC / EN 60068-2-6. Sinus. 10 -150 Hz, 5 g in each X, Y and Z directions	
Approvals and certificates			
CE conformity		yes	
UL approval		cULus Listed	
CCC approval		CCC approval / marking not required for products rated $\leq$ 36 V	

Release date: 2019-11-27 14:16 Date of issue: 2019-11-27 183459\_eng.xml

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" Pepperl+Fuchs Group

www.pepperl-fuchs.com

2


USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com


Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

# **EPPPERL+FUCHS**

## **Curves/Diagrams**





Release date: 2019-11-27 14:16 Date of issue: 2019-11-27 183459\_eng.xml

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" Pepperl+Fuchs Group www.pepperl-fuchs.com

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com