



Technical data

Ambient conditions

Ambient temperature	-40 ... 60 °C (-40 ... 140 °F)
Storage temperature	-40 ... 60 °C (-40 ... 140 °F)

Mechanical specifications

Material	PVC
Mass	100 g / m

Model number

WCS-SP2

Stabilization profile

Features

- Stabilization profile for laying tracks for the WCS code rail

Matching system components

WCS3-CS70-M1-1000FT

Code rail, stainless steel

WCS2-CS55-L1

Laminate type, 55 mm

WCS2-CS55-M1

Stainless steel type, 55 mm

WCS2-CS55-*1-PS1 SET

WCS2 aluminum profile system

WCS2-CS70-L1

Laminate type, 70 mm

WCS2-CS70-M1

Stainless steel type, 70 mm

WCS3-CS70-L*

Code rail, polyester laminate

WCS3-CS70-M1

Code rail, stainless steel

WCS3-CS70-*1-PS1 SET

WCS3 aluminum profile system

WCS-MB-B

Mounting bracket, curve

WCS-MB2-B-UNI

Mounting bracket for UNISTRUT™ profile, curved section

WCS-MB2-B

Mounting bracket for C profile, bend

WCS-MB1-B

Fastening angle for screw connection, curve

Release date: 2019-04-02 13:12 Date of issue: 2019-04-02 184110_eng.xml

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".