


Inductive sensor


NJ1,5-6,5-N-Y96220



■ Comfort series



Dimensions



Technical Data

General specifications

| | | |
|----------------------------|-------|-----------------------|
| Switching function | | Normally closed (NC) |
| Output type | | NAMUR |
| Rated operating distance | s_n | 1.5 mm |
| Installation | | flush |
| Assured operating distance | s_a | 0 ... 1.215 mm |
| Actual operating distance | s_r | 1.35 ... 1.65 mm typ. |
| Reduction factor r_{Al} | | 0.22 |
| Reduction factor r_{Cu} | | 0.19 |
| Reduction factor r_{304} | | 0.65 |
| Output type | | 2-wire |

Nominal ratings

| | | |
|---------------------|-------|---------------|
| Nominal voltage | U_o | 8 V |
| Switching frequency | f | 0 ... 5000 Hz |

Release date: 2020-11-04 Date of issue: 2020-11-04 Filename: 096220_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com


Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

PF PEPPERL+FUCHS

Technical Data

| | | |
|---|---|---|
| Hysteresis | H | 1 ... 10 typ. 5 % |
| Current consumption | | |
| Measuring plate not detected | | min. 3 mA |
| Measuring plate detected | | ≤ 1 mA |
| Compliance with standards and directives | | |
| Standard conformity | | |
| NAMUR | | EN 60947-5-6:2000 IEC 60947-5-6:1999 |
| Standards | | EN 60947-5-2:2007 EN 60947-5-2/A1:2012 IEC 60947-5-2:2007 IEC 60947-5-2 AMD 1:2012 |
| Approvals and certificates | | |
| IECEX approval | | |
| Equipment protection level Gb | | IECEX PTB 11.0037X |
| Equipment protection level Da | | IECEX PTB 11.0037X |
| Equipment protection level Mb | | IECEX PTB 11.0037X |
| ATEX approval | | |
| Equipment protection level Gb | | PTB 00 ATEX 2048 X |
| Equipment protection level Da | | PTB 00 ATEX 2048 X |
| UL approval | | cULus Listed, General Purpose |
| CSA approval | | cCSAus Listed, General Purpose |
| Ambient conditions | | |
| Ambient temperature | | -25 ... 100 °C (-13 ... 212 °F) |
| Mechanical specifications | | |
| Connection type | | cablc PVC , 2 m |
| Core cross-section | | 0.14 mm ² |
| Housing material | | Stainless steel 1.4305 / AISI 303 |
| Sensing face | | PBT |
| Degree of protection | | IP67 |
| Cable | | |
| Bending radius | | > 10 x cable diameter |
| General information | | |
| Use in the hazardous area | | see instruction manuals |

Connection



Release date: 2020-11-04 Date of issue: 2020-11-04 Filename: 096220_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**