











# **Model Number**

# ML8-8-H-140-RT/25/65a/103/115b

Background suppression sensor with fixed cable and M12 connector, 4-pin


# **Features**

- Miniature design
- Minimal black-white difference
- Flexible mounting possibilities due to slotted hole
- Not sensitive to ambient light, even with switched energy saving lamps
- Protection class II


# **Product information**

Small, robust and reliable, the ML8 series of miniature sensors is particularly suitable for non-contact detection of objects in confined spaces. The LED indicator is located behind the lens and provides reliable information on the sensor's operating status. The LED is always visible, even if the sensor is completely embedded. Flexible mounting options and fixed preset detection ranges simplify setup and operation.

# **Dimensions**



# **Electrical connection**



- O = Light on
- = Dark on

### **Pinout**


2

Wire colors in accordance with EN 60947-5-2

(brown) (white) (blue) (black)

1 BN WH 3 BU BK

# Indicators/operating means



- Functional display yellow
  Detection range adjuster
- 3 Optical axis Emitter
- 4 Optical axis Receiver min.
- 5 Optical axis Receiver max.

#### **Technical data General specifications** 5 ... 140 mm Detection range Detection range min. 5 ... 25 mm 13 ... 140 mm Detection range max Adjustment range 25 ... 140 mm standard white, 100 mm x 100 mm Reference target Light source Light type modulated visible red light Black/White difference (6 %/90 %) < 15 % Diameter of the light spot approx. 5 mm at detection range 120 mm Ambient light limit 30000 Lux Functional safety related parameters 2090 a $MTTF_d$ Mission Time (T<sub>M</sub>) 20 a Diagnostic Coverage (DC) Indicators/operating means LED yellow: lights when object is detected Function indicator Control elements Sensing range adjuster **Electrical specifications** 10 ... 30 V DC , class 2 Operating voltage Ripple max. 10 % No-load supply current < 20 mA Output Switching type light on Signal output 1 PNP output, short-circuit protected, reverse polarity protected, open collector Switching voltage max. 30 V DC

#### Conformity

Product standard EN 60947-5-2

#### Ambient conditions

Switching current

Response time

Switching frequency

-20 ... 60 °C (-4 ... 140 °F) Ambient temperature Storage temperature -40 ... 75 °C (-40 ... 167 °F)

# **Mechanical specifications**

Housing width 11 mm Housing height 31 mm Housing depth 23 mm Degree of protection IP65 Connection fixed cable 300 mm with M12 connector, 4-pin Material Housing PC (glass-fiber-reinforced Makrolon) Optical face РММА Mass approx. 50 g

max. 100 mA

200 Hz

2.5 ms


# Approvals and certificates

Protection class II, rated voltage  $\leq$  50 V AC with pollution degree 1-2 according

to IEC 60664-1

**UL** approval cULus Listed, Class 2 Power Source, Type 1 enclosure CCC approval CCC approval / marking not required for products rated ≤36 V

# **Curves/Diagrams**



### **Accessories**

# Montagekit OMH-ML7-01

Mounting set consisting of bracket OMH-ML-01 sheet OMH-ML7-03, and fastening material

# Montagekit OMH-ML7-02

Mounting set consisting of bracket OMH-ML-02 sheet OMH-ML7-03, and fastening material

# **OMH-ML7-01**

Mounting aid for ML7 and ML8 series, Mounting bracket

#### OMH-ML7-02

Mounting aid for ML7 and ML8 series, Mounting bracket

# OMH-ML7-03

Mounting aid for ML7 and ML8 series, Fixing plate

Other suitable accessories can be found at www.pepperl-fuchs.com

> 190146\_eng.xml Date of issue: 2019-11-26 Release date: 2019-11-26 15:36

**FPEPPERL+FUCHS**