



## **Model Number**

## UB2000-30GM-H3-Y190859


Single head system

#### **Features**

- · Separate evaluation
- · Direct detection mode
- With transmission pulse output

# **Diagrams**

## Characteristic response curves



Curve 1: flat surface 100 mm x 100 mm Curve 2: round bar, Ø 25 mm

| General specifications                 |                                                                                                                                                                                                                                                                                                                                         |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sensing range                          | 200 2000 mm                                                                                                                                                                                                                                                                                                                             |
| Adjustment range                       | 200 2000 mm                                                                                                                                                                                                                                                                                                                             |
| Unusable area                          | 0 200 mm <sup>1)</sup>                                                                                                                                                                                                                                                                                                                  |
| Standard target plate                  | 100 mm x 100 mm                                                                                                                                                                                                                                                                                                                         |
| Transducer frequency                   | approx. 180 kHz                                                                                                                                                                                                                                                                                                                         |
| Electrical specifications              |                                                                                                                                                                                                                                                                                                                                         |
| Operating voltage U <sub>B</sub>       | 10 30 V DC , ripple 10 % <sub>SS</sub>                                                                                                                                                                                                                                                                                                  |
| No-load supply current I <sub>0</sub>  | ≤ 30 mA                                                                                                                                                                                                                                                                                                                                 |
| Input                                  |                                                                                                                                                                                                                                                                                                                                         |
| Input type                             | 1 pulse input for transmitter pulse (clock) 0-level (active): $< 5 \text{ V (U}_B > 15 \text{ V)}$ 1-level (inactive): $> 10 \text{ V} + U_B \text{ (U}_B > 15 \text{ V)}$ 0-level (active): $< 1/3 \text{ U}_B \text{ (10 V < U}_B < 15 \text{ V)}$ 1-level (inactive): $> 2/3 \text{ U}_B  + U_B \text{ (10 V < U}_B < 15 \text{ V)}$ |
| Pulse length                           | 20 300 μs (typ. 200 μs) <sup>2)</sup>                                                                                                                                                                                                                                                                                                   |
| Pause length                           | ≥ 50 x pulse length                                                                                                                                                                                                                                                                                                                     |
| Impedance                              | 10 kOhm internal connected to +U <sub>B</sub>                                                                                                                                                                                                                                                                                           |
| Output                                 |                                                                                                                                                                                                                                                                                                                                         |
| Output type                            | 1 pulse output for echo run time and transmitter pulse, short-circuit proof open collector PNP with pulldown resistor = 22 kOhm level 0 (no echo): $-U_B$ level 1 (echo detected): $\ge (+U_B-2\ V)$                                                                                                                                    |
| Rated operating current I <sub>e</sub> | 15 mA , short-circuit/overload protected                                                                                                                                                                                                                                                                                                |
| Temperature influence                  | the echo propagation time: 0.17 % / K                                                                                                                                                                                                                                                                                                   |

# EN 60947-5-2

 Ambient conditions

 Ambient temperature
 -25 ... 85 °C (-13 ... 185 °F)

 Storage temperature
 -40 ... 85 °C (-40 ... 185 °F)

## Mechanical specifications

Protection degree IP67
Connection 2 m PVC cable 0.75 mm<sup>2</sup>

## Material


Standards

Standard conformity

**Technical data** 

Housing nickel plated brass; plastic components: PBT
Transducer epoxy resin/hollow glass sphere mixture; polyurethane foam
Mass 300 g

#### **Dimensions**



#### **Electrical Connection**

Standard symbol/Connection: (Transceiver)

WH = Emitter pulse input BK = Echo propagation time output

#### **Accessories**

#### **BF 30**

Mounting flange, 30 mm

#### **BF 30-F**

Mounting flange with dead stop, 30 mm

#### BF 5-30

Universal mounting bracket for cylindrical sensors with a diameter of 5 ... 30 mm

#### UVW90-M30

Ultrasonic -deflector


#### UVW90-K30

Ultrasonic -deflector


#### **Function**

The sensing range is determined in the downstream evaluation electronics such as PLC modules or other existing evaluation units.

The object distance in pulse-echo mode is obtained from the echo time  $\Delta t$ . The emission of an ultrasonic pulse starts simultaneously with the falling slope of the clock input signal.



We recommend the usage of a npn-transistor to trigger the sensors clock input. The sensors clock input is connected to the  $+ U_B$  potential internally by means of a pull up resistor.



- $^{1)}$  The unusable area (blind range) BR depends on the pulse duration  $T_i$ . The unusable area reaches a minimum with the shortest pulse duration.
- The sensors detection range depends on the pulse duration T<sub>i</sub>. With pulse duration < typical pulse duration, the sensors detection range may be reduced.</p>

## **Mounting conditions**

If the sensor is installed in places where the operating temperature can fall below 0  $^{\circ}$ C, the BF30, BF30-F or BF 5-30 fixing clamp must be used.