


Inductive positioning system PMI80-F90-IE8-V15

- Analog output 4 mA ... 20 mA
- Adjustable switch points
- Measuring range 0 ... 80 mm

Dimensions



Technical Data		
General specifications		
Switching element function		Analog current output with PNP binary NO
Ũ		
Object distance		0.5 3 mm , recommended: 2 mm
Measurement range		0 80 mm
Linearity range		1 79 mm
Nominal ratings		
Operating voltage	UB	18 30 V DC
Reverse polarity protection		reverse polarity protected
Linearity error		within measuring range: \pm 0.8 mm within linearity range: \pm 0.4 mm
Repeat accuracy	R	± 0.1 mm
Resolution		125 μm
Temperature drift		± 0.5 mm (-25 °C 70 °C)
No-load supply current	I ₀	≤ 40 mA
Operating voltage indicator		LED green

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Release date: 2020-03-23 Date of issue: 2020-10-16 Filename: 191137_eng.pdf

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com


1

PMI80-F90-IE8-V15

Technical Data		
Functional safety related parameters		
MTTF _d		300 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		0%
Switching output		
Output type		2 switch outputs PNP, NO , reverse polarity protected , short-circuit protected
Operating current	IL.	≤ 100 mA
Switching window	-	±1mm
Switching hysteresis		0.4 mm
Voltage drop		≤ 3 V
Short-circuit protection		pulsing
Analog output		
Output type		1 current output: 4 20 mA
Load resistor		≤ 400 Ω
Compliance with standards and directives		
Standard conformity		
Standards		EN 60947-5-2:2007 IEC 60947-5-2:2007
Approvals and certificates		
UL approval		cULus Listed, General Purpose, Class 2 Power Source
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-25 70 °C (-13 158 °F)
Mechanical specifications		
Connection type		5-pin, M12 x 1 connector
Degree of protection		IP67
Material		
Housing		ABS
Target		mild steel, e. g. 1.0037, SR235JR (formerly St37-2)

Connection

IE8



Connection Assignment



Refer to "General Notes Relating to Pepperl+Fuchs Product Information".


2


Inductive positioning system

Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)
5	GY	(gray)

dimensions for the target object:





Accessories

4	BT-F90-W	Damping element for sensors of type F90, F112, and F166; side hole
	MH-F90	Mounting bracket for mounting of F90 sensors
Z,	V15-G-2M-PVC	Female cordset, M12, 5-pin, PVC cable
	V15-W-2M-PVC	Female cordset, M12, 5-pin, PVC cable

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

3

Operation

Operating instructions

Safety information



П

This product may not be used in applications where personal safety depends on the function of the device.

This product is not a safety component as described in EU

Machinery Directive.

Sensor versions

The F90 linear position measurement system is available in 2 versions.

In the PMI...-F90-IU-V1 version, the position measuring system transmits current and voltage signals proportional to the position of the damping element at the outputs.

The PMI...-F90-**IE8**-V15 version offers a current signal as well as the option of teaching in two switching points directly at the sensor independently of one another at the press of a button, which is then indicated on two switching outputs. Two additional LEDs indicate the output states of the two switching outputs.

Version PMI...-F90-IU-V1

Output signals: 4 mA \dots 20 mA and 0 V \dots 10 V

- Only the current output or the voltage output may be used. The
- unused output must remain load free.

Version PMI...-F90-IE8-V15

Output signals: 4 mA ... 20 mA and 2 programmable switching amplifiers

Programming the PMI...-F90-IE8-V15

The rear of the PMI...-F90-IE8-V15 sensor has two small, slightly recessed push buttons for programming the switching points. The buttons are marked "teach in" and S1 for switching point S1 and S2 for switching point S2.

- To teach in a switching point, proceed as follows:
- The position detection damping element must be placed at the relevant position, i.e. the switching point that you wish to teach in.
- Press the corresponding push button for at least two seconds.
 - The associated switching state LED starts flashing to indicate that the sensor is now in "teach mode".
- · Press the button again to confirm the relevant switching point.

The switching state LED then lights up constantly as long as the damping element is not moved.

The switching point is now taught in and the associated switching point changes to an active state within an actuator adjustment range of ± 1 mm around the taught switching point.

- If the switching point is not confirmed within 80 seconds, the sensor
 - exits "teach mode" and continues operation with the previous values.
- Damping element

Ĩ


The linear position measurement system is adapted perfectly to the geometry of the damping elements offered in our product range.

- O When using other damping elements,
- always make sure that the active surface
 - of the damping element has a width of exactly 8 mm and covers the entire width of the sensor.
- Installation and operation

Instructions on installation

- Flush installation is possible
- to extend the measuring range, units from the -F90 linear position measurement system can be connected in series (both behind and adjacent to one another) without a minimum distance.
- The minimum distance between the measuring field (framed area on the sensor front) and mounting base or mounting elements on the damping element must be 3 mm.







Operating information

The specified measurement accuracy is achieved with an actuator distance of 1 to 3 mm.


- If the damping element leaves the measuring area (illustration below):
- the last valid value is retained at the voltage output (PMI...-F90-IU-V1 only) until the damping element enters the valid area again.
- the last valid value is retained for 0.5 seconds at the current output (all types). The output then switches to a fault current of 3.6 mA until the damping element enters the valid area again.





Inductive positioning system






Defining the measuring range / measured position

The measured position of the damping element (actuator) is based on half of the width (center of the actuator). The measuring range starts and finishes when half the width of the actuator covers the measurement field marked on the sensor when the actuator makes a longitudinal movement (see left illustration above).

Mounting bracket

MH-F90



Accessories

Damping elements BT-F90-W



Straight cable:V1-G-2M-PVC (4-wire) V15-G-2M-PVC (5-wire) Angled cable:V1-W-2M-PVC (4-wire) V15-W-2M-PVC (5-wire)

M-PVC (4-wir

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"