ML7-54-G/25/136/115

Dimensions



Model Number

ML7-54-G/25/136/115


Retroreflective sensor with fixed cable

Features

- Reliable sensor for standard • applications
- Miniature design with versatile ٠ mounting options
- Reliable recognition of reflective • objects and clear glass
- Two machines in one: clear object detection or reflection operating mode with long range
- TEACH-IN switch for setting the contrast detection levels
- Automatic adjustment in case of ٠ soiling in contrast detection mode
- Certified by ECOLAB ٠


Product information

Small, robust, effective, and reliable - these are the properties of the ML7 sensor series. Due to their small size, number of versions, and two different lens positions, they are particularly suited for installation in tight spaces. The robust design and high quality of Pepperl+Fuchs mean they can also be used under harsh environmental conditions. The efficient technology, switching frequencies up to 1000 Hz, high resistance to ambient light, and 4-in-1 output make the series suitable for non-contact object detection.






Electrical connection



O = Light on = Dark on

Indicators/operating means



1	Operating display	green
2	Signal display	yellow
3	Teach-In	
4	Optical center	

194185_eng.xml

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" Pepperl+Fuchs Group www.pepperl-fuchs.com fa-info@us.pepperl-fuchs.com

USA: +1 330 486 0001

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com **EPPPERL+FUCHS** 1

	0.
	0.
	7.6
	H8
	LE
	mc
	ye
	ma
	ар
	1.7
	40
meters	
	98
	20
	0 %
	LE
	Gr fla:
	LE
	5-5
	10
	18 40
	40 ad
Un	10
- D	ma
lo	< 2
Ū	
	ligl
	2 p
	rev
	ma
	ma
f	1 k
	50
	ΕN
	-20
	-40
	11
	31
	23
	IP
	ameters lo lo f

0 3.5 m in TEACH mode 0 5.7 m at switch position "N"
0 3.5 m in TEACH mode 0 5.7 m at switch position "N"
7.6 m
H85-2 reflector
LED
modulated visible red light , 660 nm
-
yes max. ± 1°
approx. 40 mm at detection range 1 m
1.7 °
40000 Lux
980 a
20 a
0%
0 /0
LED groop, statically lit Daway are the democratic structure in the
LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit : LED green flashing (approx. 4 Hz)
LED yellow: switching state ; Stability control ; Teach-In
5-step switch for setting the contrast detection levels.
10 % - clean, water filled PET bottles
18 % - clear glass bottles
40 % - colored glass or opaque materials
adjustable due to Teach-In switch
10 30 V DC
max. 10 %
< 20 mA at 24 V DC
light on
2 push-pull (4 in 1) outputs, complementary, short-circuit proof,
reverse polarity protected
max. 30 V DC
max. 100 mA
1 kHz
500 μs
500 µ5
EN 60947-5-2
EIN 0094/-0-2
-20 60 °C (-4 140 °F)
-40 75 °C (-40 167 °F)
11 mm
31 mm
23 mm
IP67 / IP69K
2 m fixed cable
PC (glass-fiber-reinforced Makrolon)
PMMA
50 g
II, rated voltage \leq 50 V AC with pollution degree 1-2 according
to IEC 60664-1 functional insulation acc. to DIN EN 50178
cULus
CCC approval / marking not required for products rated \leq 36 V

A

ML7-54-G/25/136/115
Accessories
Montagekit OMH-ML7-01 Mounting set consisting of bracket OMH- ML-01 sheet OMH-ML7-03, and fastening material
Montagekit OMH-ML7-02 Mounting set consisting of bracket OMH- ML-02 sheet OMH-ML7-03, and fastening material
OMH-ML7-01 Mounting aid for ML7 and ML8 series, Mounting bracket
OMH-ML7-02 Mounting aid for ML7 and ML8 series, Mounting bracket
OMH-ML7-03 Mounting aid for ML7 and ML8 series, Fixing plate
REF-MH23-2 Reflector with Micro-structure, rectangular 23 mm x 14 mm, diagonal mounting hole
ORR50G Reflector, rectangular 50.9 mm x 60.9 mm, mounting holes, fixing strap and polarization filter
Suitable reflectors and cable sockets can be found in the Internet

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" Pepperl+Fuchs Group USA: +1 330 486 0001

www.pepperl-fuchs.com

2

Connection Material Housing Optical face Mass

Approvals and certificates Protection class UL approval CCC approval


fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com


Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com


EPPPERL+FUCHS

Curves/Diagrams



Curves/Diagrams





Additional information

Adjustment instructions for Teach-In operation:

Step	Switch	LED	LED	Time/	Explanations/
	position	green	yellow	frequency	comments

3

	1	1			
1	N	on	flashes	4/s	In switch position "N" directed towards reflector.
					Reflector detected without function reserve.
	Ν	on	on	-	In switch position "N" directed towards reflector.
					Reflector detected with function reserve (recommended).
2	Т	off/on	on	200 ms	The selection of a new switch position is indicated by the green LED going out for a short time.
					This also applies to the selection of the other switch positions.
	Т	flashes	flashes	2.5 s	<i>Slow</i> alternating flashing: Teach-In process has been performed correctly .
					Max. duration of the Teach-In process: 2 s
	Т	flashes	flashes	8/s	<i>Quick</i> alternating flashing: Teach-In process has not been performed correctly . (e.g. receiver signal not sufficient, sensor not directed correctly towards reflector).
					Status is terminated by turning switch to position N.
3/1	I	on	on	-	Contrast detection 10 % is activated. (e.g. clean PET bottles filled with water)
3/2	II	on	on	-	Contrast detection 18 % is activated. (e.g. clear glass bottles)
3/3	III	on	on	-	Contrast detection 40 % is activated. (e.g. coloured glass or non-transparent materials)

fa-info@us.pepperl-fuchs.com