Dimensions






Model Number

SJ3,5-N LED-Y38999

Features

- Comfort series
- 3.5 mm slot width

Connection



Release date: 2013-02-07 18:30 Date of issue: 2013-02-07 106587_eng.xml

Subject to modifications without notice Pepperl+Fuchs Group www.pepperl-fuchs.com

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776-4411 fa-info@pepperl-fuchs.com

CSA approval



3.5 10 5 10 15 0.9 2 ø 1.85 6.75 .ED 19

Technical Data

Technical Data		
General specifications		
Switching element function		NAMUR, NC
Slot width		3.5 mm
Depth of immersion (lateral)		5 7 typ. 6 mm
Installation		
Output polarity		NAMUR
Nominal ratings		
Nominal voltage	U _o	8 V
Operating voltage	UB	5 25 V
Switching frequency	f	0 3000 Hz
Hysteresis	Н	0.1 0.4 mm
Current consumption		
Measuring plate not detected		≥ 3 mA
Measuring plate detected		≤1 mA
Switching state indication		LED, yellow
Ambient conditions		
Ambient temperature		-25 100 °C (-13 212 °F)
Mechanical specifications		
Connection type		flexible leads LIY, 500 mm
Core cross-section		0.14 mm ²
Housing material		PBT/PPS
Protection degree		IP67
General information		
Use in the hazardous area		see instruction manuals
Category		2G
Compliance with standards and c	lirective	S
Standard conformity		
NAMUR		EN 60947-5-6:2000 IEC 60947-5-6:1999
Standards		EN 60947-5-2:2007 IEC 60947-5-2:2007
Approvals and certificates		
UL approval		cULus Listed, General Purpose

cCSAus Listed, General Purpose

SJ3,5-N LED-Y38999

ATEX 2G

Instruction

Device category 2G Directive conformity Standard conformity

CE marking

Ex-identification

EC-Type Examination Certificate Appropriate type Effective internal capacitance C_i Effective internal inductance L_i General

Highest permissible ambient temperature

Installation, Comissioning

Maintenance

Specific conditions

Protection from mechanical danger

Manual electrical apparatus for hazardous areas

for use in hazardous areas with gas, vapour and mist 94/9/EG EN 60079-0:2009, EN 60079-11:2007 Ignition protection "Intrinsic safety" Use is restricted to the following stated conditions $C \in 0102$

⟨€x⟩ II 2G Ex ia IIC T6 Gb

PTB 99 ATEX 2219 X SJ3,5-...-N... ≤ 50 nF ; a cable length of 10 m is considered. ≤ 250 μH ; a cable length of 10 m is considered.

The apparatus has to be operated according to the appropriate data in the data sheet and in this instruction manual. The EC-Type Examination Certificate has to be observed. The special conditions must be adhered to!

The temperature ranges, according to temperature class, are given in the EC-Type Examination Certificate.

Laws and/or regulations and standards governing the use or intended usage goal must be observed. The intrinsic safety is only assured in connection with an appropriate related apparatus and according to the proof of intrinsic safety.

No changes can be made to apparatus, which are operated in hazardous areas. Repairs to these apparatus are not possible.

When used in the temperature range below -20 $^{\circ}$ C the sensor should be protected from knocks by the provision of an additional housing.

Subject to modifications without notice

