
Inductive proximity switches


6 mm embeddable



(€ 0102

General specifications	
Switching element function	NAMUR NC
Rated operating distance s _n	6 mm
Installation	embeddable
Assured operating distance s _a	0 4.86 mm
Reduction factor r _{Al}	0.4
Reduction factor r _{Cu}	0.3
Reduction factor r _{V2A}	0.85
Nominal ratings	
Nominal voltage U _o	8 V
Operating voltage U _B	5 25 V
Switching frequency f	0 2000 Hz
Current consumption	
Measuring plate not detected	≥ 3 mA
Measuring plate detected	≤ 1 mA
Standard conformity	
EMC in accordance with	IEC / EN 60947-5-2:2004
Standards	DIN EN 60947-5-6 (NAMUR) VDE 660 Part 209
Ambient conditions	
Ambient temperature	-40 100 °C (233 373 K)
Mechanical specifications	
Connection type	2 m, PVC cable
Core cross-section	0.75 mm ²
Housing material	Stainless steel
Sensing face	PBT
Protection degree	IP68
General information	
Use in the hazardous area	see instruction manuals

Connection type:



Inductive proximity switches

ATEX 2G

Instruction

Device category 2G

Directive conformity Standard conformity

CE symbol

Ex-identification

EC-Type Examination Certificate
Appropriate type
Effective internal capacitance C_i
Effective internal inductance L_i

General

Highest permissible ambient temperature

Installation, Comissioning

Maintenance

[Fett]Special conditions Electrostatic charging

Manual electrical apparatus for hazardous areas

for use in hazardous areas with gas, vapour and mist

EN 50014:1997, EN 50020:1994 Ignition protection "Intrinsic safety" Use is restricted to the following stated conditions

€0102

II 2G EEx ia IIC T6

PTB 00 ATEX 2049 X

NJ 6-22-SN-G...

 \leq 110 nF ; a cable length of 10 m is considered. \leq 150 μH ; a cable length of 10 m is considered.

The apparatus has to be operated according to the appropriate data in the data sheet and in this instruction manual. The EU prototype test certificate must be observed. The special conditions must be adhered to!

The temperature ranges, according to temperature class, are given in the EU prototype test certificate.

Laws and/or regulations and standards governing the use or intended usage goal must be observed. The intrinsic safety is only assured in connection with an appropriate related apparatus and according to the proof of intrinsic safety.

No changes can be made to apparatus, which are operated in hazardous areas. Repairs to these apparatus are not possible.

Electrostatic charges must be avoided on the mechanical housing components. Dangerous electrostatic charges on the mechanical housing components can be avoided by incorporating these in the equipotential bonding.