


## Connection cable, Ethernet V45-GP-10M-PUR-ABG-V45-G

- Industrial-strength push pull EtherNet connector for field installations
- Hard-wearing PUR cable
- Suitable for drag chains and abrasion resistant
- Industrial Ethernet
- Conforms to PROFINET
- CAT5/CAT5e cable
- Free of paint wetting interfering substances
- Halogen-free

Ethernet bus cable RJ45 to RJ45 PROFINET-coded, 4-pin, PUR cable green, Cat5e, shielded, drag chain suitable



### Dimensions



### Technical Data

#### General specifications

Connector 1			
Connection			plug
Construction type			RJ45
Style			straight
Locking			Push/pull
Number of pins			4
Coding			PROFINET
Connector 2			
Connection			plug
Construction type			RJ45
Style			straight
Locking			snap locking
Number of pins			8
Coding			PROFINET
Electrical specifications			
Operating voltage	U <sub>B</sub>		max. 48 V AC / 60 V DC
Conformity			
Degree of protection			EN 60529
Transmission technology			Cat. 5 Class D up to 100 MHz
Plug connection			connector RJ45 : IEC 60603-7 , IEC 61076-3-106 V4
Component category			CAT5 (IEC 11801)
Flammability			IEC 60332-1-2 / UL 2556 / ISO 6722-1 5.22 (UN ECE-R 118.01)

Release date: 2024-03-17 Date of issue: 2024-03-17 Filename: 202379\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111  
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com




PEPPERL+FUCHS

**Technical Data**

<b>Ambient conditions</b>		
Ambient temperature		
Cable, fixed		-30 ... 70 °C (-22 ... 158 °F) , UL: -20 ... 70 °C (-4 ... 158 °F)
Cable, flexing		-20 ... 70 °C (-4 ... 158 °F)
<b>Mechanical specifications</b>		
Connector 1		
Loosening protection		available
Mating cycles		min. 750
Shielding		via body
Degree of protection		IP67
Connector 2		
Loosening protection		available
Mating cycles		min. 100
Shielding		shield connected to connector
Degree of protection		IP20
Cable		
Sheath diameter		6 mm
Bending radius		> 10 x cable diameter, moving > 8 x cable diameter, fixed
Sheath stripping force		max. 60 N / 100 mm
Sheath color		green (similar to RAL 6018)
Number of cores		4
Core cross section		0.34 mm <sup>2</sup> / 22 AWG
Cores color		Core 1: yellow Core 2: orange Core 3: white Core 6: blue
Core construction		7 x 0.254 mm Ø twisted quad
Shield		aluminum-lined polyester foil Tinned copper braiding
Length	L	10 m
Drag chain suitability		
Drag chain cycles		max. 1000000
Motion velocity		max. 3 m/s
Traverse distance		max. 5 m
Acceleration		max. 2 m/s <sup>2</sup>
<b>Material</b>		
PWIS free		yes
Halogen-free		yes
Connector 1		
Body		thermoplastic, black
Flammability		V-0
Connector 2		
Body		PA, green
Flammability		V-0
Cable		
Sheathing		PUR based on polyether
Core insulation		PP
Flammability		FT2 complies with UN ECE-R 118.01

Release date: 2024-03-17 Date of issue: 2024-03-17 Filename: 202379\_eng.pdf

## Connection



Release date: 2024-03-17 Date of issue: 2024-03-17 Filename: 202379\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111  
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**