





 $\epsilon$ 



# **Model Number**

## ML8-8-H-30-RT/103/143/162

Background suppression sensor with 4-pin, M8 x 1 connector


## **Features**

- Diffuse mode sensor with multiple light spots
- Specially designed for detecting critical objects such as PCBs
- Detects objects in front of a close background through precise background suppression
- Precision object detection, almost irrespective of the color
- Tamper-proof, no operating controls
- · Plug and Play
- Not sensitive to ambient light, even with switched energy saving lamps


## **Product information**

Small, robust and reliable, the ML8 series of miniature sensors is particularly suitable for non-contact detection of objects in confined spaces. The LED indicator is located behind the lens and provides reliable information on the sensor's operating status. The LED is always visible, even if the sensor is completely embedded. Flexible mounting options and fixed preset detection ranges simplify setup and operation.

## **Dimensions**



## **Electrical connection**



- O = Light on
- = Dark on


## **Pinout**

Wire colors in accordance with EN 60947-5-2



1	BN	(brow
2	WH	(white
3	BU	(blue)
4	BK	(black

#### **Technical data General specifications** Detection range 15 ... 30 mm Reference target standard black, 100 mm x 100 mm LED Light source Light type modulated visible red light, 640 nm Black/White difference (6 %/90 %) < 10 % Diameter of the light spot 3 light spots, 12 mm apart (outer spot to outer spot), spotsize 3.5 mm at a distance of 30 mm (outer spot to outer spot) Ambient light limit EN 60947-5-2 Functional safety related parameters $MTTF_d$ 794 a Mission Time (T<sub>M</sub>) 20 a 0 % Diagnostic Coverage (DC) Indicators/operating means 2 LEDs yellow, light up in case of detection Function indicator **Electrical specifications** Operating voltage 10 ... 30 V DC, class 2 Ripple max. 10 % No-load supply current < 15 mA Output Switching type 1 PNP output, short-circuit protected, reverse polarity protected, Signal output open collector Switching voltage max. 30 V DC max 100 mA Switching current Voltage drop ≤ 1.5 V DC $U_{d}$ f 500 Hz Switching frequency Response time 1 ms Conformity EN 60947-5-2 Product standard Ambient conditions -20 ... 60 °C (-4 ... 140 °F) Ambient temperature Storage temperature -40 ... 70 °C (-40 ... 158 °F) **Mechanical specifications** Housing width 23 mm Housing height 31 mm Housing depth 11 mm Degree of protection IP67 Connection M8 x 1 connector, 4-pin Material Housing PC (glass-fiber-reinforced Makrolon) Optical face **PMMA** Connector plastic Mass approx. 10 g Approvals and certificates cULus Listed, Class 2 Power Source, Type 1 enclosure **UL** approval



#### **Accessories**

## Montagekit OMH-ML7-01

Mounting set consisting of bracket OMH-ML-01 sheet OMH-ML7-03, and fastening material

## Montagekit OMH-ML7-02

Mounting set consisting of bracket OMH-ML-02 sheet OMH-ML7-03, and fastening material

## **OMH-ML7-01**

Mounting aid for ML7 and ML8 series, Mounting bracket

#### OMH-ML7-02

Mounting aid for ML7 and ML8 series, Mounting bracket

## OMH-ML7-03

Mounting aid for ML7 and ML8 series, Fixing plate

#### V31-WM-2M-PUR

Female cordset single-ended, M8, 4-pin, PUR cable

#### V31-GM-2M-PUR

Female cordset single-ended, M8, 4-pin, PUR cable

Other suitable accessories can be found at www.pepperl-fuchs.com