Release date: 2023-04-04 Date of issue: 2023-04-04 Filename: 180711_eng.pdf



Background suppression sensor RL28-8-H-400-FFP-3019/47/115b



- Special range of application: Specialised fine positioning
- Ultra bright LEDs for power on and switching state
- Good alignability due to red transmission LED
- Not sensitive to ambient light, even with switched energy saving lamps
- Protection class II

Background suppression sensor










Dimensions




Technical Data

General specifications	
Detection range	20 400 mm
Detection range min.	20 150 mm

Technical Data Detection range max. 20 ... 400 mm Background suppression max. + 10 % of the upper limit of the detection range Light source Light type modulated visible red light, 660 nm Black-white difference (6 %/90 %) < 15 % 4 mm x 4 mm at a distance of 250 mm Diameter of the light spot Opening angle Emitter 1.2°, Receiver 2° Ambient light limit 50000 Lux Functional safety related parameters MTTF_d 720 a Mission Time (T_M) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green Function indicator 2 LEDs yellow ON: object inside the scanning range OFF: object outside the scanning range Control elements Sensing range adjuster **Electrical specifications** 10 ... 30 V DC Operating voltage U_B Ripple 10 % No-load supply current ≤ 40 mA I_0 Output Switching type light/dark on 2 PNP, complementary, short-circuit protected, reverse polarity protected , open Signal output collectors Switching voltage max. 30 V DC Switching current max. 200 mA 250 Hz Switching frequency f Response time 2 ms Conformity EN 60947-5-2 Product standard Approvals and certificates Protection class II, rated voltage ≤ 250 V AC with pollution degree 1-2 according to IEC 60664-1 **UL** approval E87056, cULus Listed, class 2 power supply, type rating 1 **Ambient conditions** Ambient temperature -40 ... 60 °C (-40 ... 140 °F) Storage temperature -40 ... 60 °C (-40 ... 140 °F) Mechanical specifications Housing width 25.8 mm Housing height 88 mm Housing depth 54.3 mm IP67 Degree of protection Connection 0.2 m fixed cable with 4-pin, M12 connector Material Housing Plastic ABS Optical face plastic Mass 70 g

Connection



- O = Light on
- = Dark on


Connection Assignment




Wire colors in accordance with EN 60947-5-2

1 | BN (brown) 2 | WH (white) 3 | BU (blue) 4 | BK (black)

Characteristic Curve



Characteristic Curve



Application



м		06	SO	17	06
	1975	-	-1 -1		-

6.	OMH-05	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
	OMH-21	Mounting bracket: mounting aid for sensors in the RL* series
	OMH-22	Mounting aid for RL* series
	OMH-RLK29-HW	Mounting bracket for rear wall mounting
	OMH-RL28-C	Weld slag cover model

Additional information

Intended use:

The transmitter and receiver are located in the same housing for direct detection sensors with background masking. Marking of objects outside the detection range is achieved by arranging the angle between the transmitter and receiver (2 receiver

Objects are detected independently of their surface structures, brightness and colour, as well as the brightness of the background.

Mounting instructions:

The sensors can be fastened directly with fixing screws or with a support bracket (not included with delivery).

The surface underneath must be flat to prevent the housing from moving when it is tightened into position. We recommend securing the nut and screw in place with spring washers to prevent the sensor from going out of adjustment.

Adjustment:

After the operating voltage is applied, the LED is lit green.

Align the sensor to the background. If the yellow LED is lit, the detection range should be reduced with the detection range adjuster until the yellow LED goes out.

Object direction:

Place the object to be detected at the desired maximum detection range and align the light spot to it. If the object is detected, the yellow LED lights up.

If it does not light up, the detection range must be adjusted on the potentiometer until it lights up when an object is detected. Cleaning:

We recommend cleaning the optical surface and checking the screwed connection and other connections at regular intervals.