



# Frequency voltage current converter KFU8-FSSP-1.D

- Limit frequency 40 kHz
- Voltage or current ouptput
- Incrementing output (Spacing factor 1 ... 9999)
- Multi-range power pack
- 2-, 3-, 4-wire and NAMUR sensors as well as rotary encoder
- Auxiliary power output for sensors
- Connection via Power Rail
- Period measurement
- Display: Input in Hz or 1/min, output in V or mA
- adjustable updating of indication (0,001 ... 2,5 s)

Frequency voltage current converter, 40 kHz version



#### **Function**

The KFU8-FSSP-1.D frequency-voltage/current converter is a device for displaying and monitoring periodic signals, which occur in almost all areas of the automation and processing industry, i.e. frequencies in general and rotational speeds in particular. Input pulses are evaluated according to the cycle method, i.e. by measurement of the periodicity, and are converted into a frequency or rotational speed by a  $\mu$  controller. Depending on the measurement range value selected, the  $\mu$  controller calculates a voltage or current value proportionate

speed by a µ controller. Depending on the measurement range value selected, the µ controller calculates a voltage or current value proportionate to the input frequency and exports this value via a digital-analog converter.

The following analogue signals are available for selection: 0 V ... 10 V, 0 mA ... 20 mA, 4 mA ... 20 mA

The serially switched output provides the input frequency which can be subdivided by the adjustable factor (1 ... 9999).

Special consideration was given to the frequently occurring special case of rotational speed measurement during the development of the device.

This makes it possible for the display and inputs to be either Hz or in min<sup>-1</sup>.

In addition, in applications with signal encoders that return multiple pulses per revolution, it is possible to operate automatically at the actual speed of the divise by conscious the purpose (1 ... 1200).


of the drive by assigning the number (1 ... 1200).

The frequency/voltage/current converter is supplied with 115 VAC, 230 VAC or 24 VDC. When it is connected with alternating voltage it provides an unstabilised 24-VDC source of power for the signal encoder.

All commonly available two- three- or four-wire proximity switches and incremental encoders on the input galvanically separated by an optical coupler are accepted as a signal source. In addition, two terminals are reserved for connecting proximity switches or incremental encoders in accordance with DIN 19234 (NAMUR).

The input signal frequency in Hz or the speed in min<sup>-1</sup> - or the output signal voltage in V or current in mA - appears in a 4-place 7-segment LED display on the front of the device. Parameters can be set with 4 buttons underneath the display.

# **Dimensions**




		_	
Obi	വ	10	to.
chi	 ai i		

Functional safety related parameters				
MTTF <sub>d</sub>		100 a		
Supply				
Rated voltage	U <sub>r</sub>	200 230 V AC ; 100 130 V AC; 50/60 Hz 20 VDC 30 VDC		
Fusing		external fusing 4 A		
Power consumption		AC: < 5 VA DC: < 5 W		
Indicators/operating means				
Туре		4-digit, 7-segment red display, 7 mm digit height		
Display interval		0.002 9999 Hz or 0.01 9999 min <sup>-1</sup>		
Parameter assignment		keypad-driven menu		
Input 1				
Connection		terminals 8-, 9+		
Connectable sensor types		NAMUR sensors according to DIN EN 60947-5-6		
Open loop voltage		8.2 V DC		
Short-circuit current		6.5 mA		
Switching point		1.2 2.1 mA Switching hysteresis approx. 0.2 mA		
Impedance		1.2 kOhm		
Input 2				
Switching point		high: 16 30 V DC; max.10 mA; $R_i \cong 3$ kOhm low: 0 6 V DC		
Connection		terminals 7+, 13- sensor supply terminals 14, 15 NPN/PNP input (galvanically isolated)		
Connectable sensor types		2-, 3-, or 4-wire proximity switches and incremental rotary encoder		
Sensor supply		19 28 V DC non-stabilised; ≤ 30 mA short-circuit protected		
Output				
Analog voltage output		0 10 V DC; 2 10 V DC; 30 mA max.; resolution: 12 mV; $R_i \ge$ 330 $\Omega$ (terminal 5+, 6-)		
Analog current output		0 20 mA; 4 20 mA; resolution: 25 $\mu\text{A};R_i$ $\leq$ 600 $\Omega$ (terminal 4-, 5+)		
*				

Technical Data

Technical Data	
Digital incrementing	$\geq$ (U <sub>b</sub> -3 V), 20 mA, short-circuit proof (Terminals 1-, 2+) with frequency division F <sub>in</sub> /1 F <sub>in</sub> /9999
Transfer characteristics	
Input frequency	≤ 40000 Hz, pulse pause/pulse length: ≥ 12 μs
Deviation	≤ 0.2 % of full-scale value
Changing interval	5 ms (Internal processing time)
Standard conformity	
Electromagnetic compatibility	acc. to EN 50081-2 / EN 50082-2
Ambient conditions	
Ambient temperature	-25 40 °C (-13 104 °F)
Storage temperature	-40 85 °C (-40 185 °F)
Relative humidity	max. 80 %, not condensing
Altitude	0 2000 m
Operating conditions	The device has only to be used in an indoor area.
Mechanical specifications	
Connection assembly	<b>Caution:</b> Please be aware that the device may only be connected to a switchable power supply. The switch or circuit breaker must be easy to reach and identified as the separator for the device.
Degree of protection	IP20
Connection	coded, removable terminals , max. core cross section 0.34 $\dots$ 2.5 mm $^2$
Construction type	modular terminal housing in Makrolon, System KF For use in the switch cabinet/switch cabinet module
Mounting	snap-on to 35 mm standard rail or screw fixing

## **Connection**



## Configuration

