





CE





Model Number

ML6-54-G/25/95/136

Retroreflective sensor with 4-pin, M8 x 1 connector


Features

- Precision sensor for standard applications
- Miniature design with very robust and versatile mounting options
- Reliable recognition of reflective objects and clear glass
- Two machines in one: clear object detection or reflection operating mode with long range
- TEACH-IN switch for setting the contrast detection levels
- Automatic adjustment in case of soiling in contrast detection mode
- Rear mounting option for easy mounting without mounting bracket


Product information

The ML6 series is characterized by a robust, powerful and standard design in a miniature housing. The housing offers IP67/IP69K degree of protection, a food-grade lens, highly visible LEDs and robust all-metal bushings for mounting. Adjustable and tamper-proof sensors with a double push-pull output are available. The sensors have a high ambient light limit. Reflections from the background are suppressed. The unusually small, sharp light spot and the quick response time offer maximum switching precision on object edges. Clearly visible red light sources facilitates alignment. A high-performance fixed focus background suppressor is a useful feature. The sensors are suitable for precise object detection and open up a wide range of application fields.

Dimensions



Electrical connection



- O = Light on
- = Dark on


Pinout

Wire colors in accordance with EN 60947-5-2

2 4 3

1 BN (brown)
2 WH (white)
3 BU (blue)
4 BK (black)

Indicators/operating means





Technical data			
General specifications			
Effective detection range		0 3.5 m in TEACH mode 0 5 m at switch position "N"	
Reflector distance		0 3.5 m in TEACH mode 0 5 m at switch position "N"	
Threshold detection range		6 m	
Reference target		H85-2 reflector	
Light source		LED	
Light type		modulated visible red light, 660 nm	
Polarization filter		yes	
Angle deviation		max. ± 1°	
Diameter of the light spot		approx. 40 mm at detection range 1 m	
Angle of divergence		1.7	
Ambient light limit		40000 Lux	
Continuous light Modulated light		5000 Lux	
•		5000 Lux	
Functional safety related parame	eters	000 -	
MTTF _d		980 a	
Mission Time (T _M)		20 a	
Diagnostic Coverage (DC)		0 %	
Indicators/operating means			
Operation indicator		LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit: LED gree flashing (approx. 4 Hz)	
Function indicator		LED yellow: switching state; Stability control; Teach-In	
Control elements		5-step switch for setting the contrast detection levels.	
Contrast detection levels		switch position I: 10 % - clean, water filled PET bottles	
Contrast detection levels		switch position II: 18 % - clear glass bottles switch position III: 40 % - coloured glass or opaque materials adjustable due to Teach-In switch	
Electrical specifications			
Operating voltage	U _B	10 30 V DC	
Ripple	ОВ	max. 10 %	
No-load supply current	I _O	< 15 mA at 24 V DC	
Output	U		
Switching type		light/dark on, programmable	
Signal output		2 push-pull (4 in 1) outputs, complementary, short-circuit pro reverse polarity protected	
Switching voltage		max. 30 V DC	
Switching current		max. 100 mA	
Voltage drop	U_d	≤ 2.5 V DC	
Switching frequency	f	1 kHz	
Response time		500 μs	
Conformity			
Product standard		EN 60947-5-2	
Ambient conditions			
Ambient temperature		-20 60 °C (-4 140 °F)	
Storage temperature		-20 75 °C (-4 167 °F)	
Mechanical specifications			
Housing width		13.9 mm	
Housing height		31.4 mm	
Housing depth		18 mm	
Degree of protection		IP67 / IP69K	
Connection		M8 x 1 connector, 4-pin	
Material			
Housing		ABS	
Optical face		PMMA	
Mass		approx. 10 g	
Compliance with standards and directives			
Standard conformity		IEC / EN 60068. half-sine, 40 g in each X, Y and Z directions	
Standard conformity Shock and impact resistance Vibration resistance		IEC / EN 60068-2-6. Sinus. 10 -2000 Hz, 10 g in each X, Y and irections	
Shock and impact resistance Vibration resistance			
Shock and impact resistance		IEC / EN 60068-2-6. Sinus. 10 -2000 Hz, 10 g in each X, Y an directions	

Accessories

OMH-4.1

Mounting Clamp

OMH-ML6

Mounting bracket

OMH-ML6-U

Mounting bracket

OMH-ML6-Z

Mounting bracket

OMH-11-02 Aperture-V-H 0.5 mm

Slit diaphragm can be affixed for detecting very small parts

OMH-11-04 Aperture-V-H 1.0 mm

Slit diaphragm can be affixed for detecting very small parts

OMH-11-06 Aperture-V-H 1.5 mm

Slit diaphragm can be affixed for detecting very small parts

OMH-11-08 Aperture-V-H 2.0 mm

Slit diaphragm can be affixed for detecting very small parts

V31-GM-2M-PVC

Female cordset single-ended, M8, 4-pin, PVC cable

V31-WM-2M-PVC

Female cordset single-ended, M8, 4-pin, PVC cable

REF-H85-2

Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes

REF-C110-2

Reflector, round ø 84 mm, central mounting hole

REF-H60-2

Reflector with mounting holes

REF-VR10

Reflector, rectangular 60 mm x 19 mm, mounting holes

OFR-100/100

Reflective tape 100 mm x 100 mm

REF-A17

Reflector, round ø 20.5 mm, selfadhesive

REF-A25

Reflector, round ø 25 mm, self-adhesive

REF-MH23

Reflector with Micro-structure, rectangular 23 mm x 13.8 mm, diagonal mounting hole

REF-CLIP50HT

Reflector, round ø 50 mm, snap-in, high temperature applications


REF-H50HT


Reflector, rectangular 50.9 mm x 50.9 mm, mounting holes, fixing strap


Suitable reflectors and cable sockets can be found in the Internet


FPEPPERL+FUCHS

Curves/Diagrams









Additional information

Adjustment instructions for Teach-In operation:

Step	Switch	LED	LED	Time/	Explanations/
	position	green	yellow	frequency	comments
1	N	on	flashes	4/s	In switch position "N" directed towards reflector.
					Reflector detected without function reserve.
	N	on	on	-	In switch position "N" directed towards reflector.
					Reflector detected with function reserve (recommended).
2	Т	off/on	on	200 ms	The selection of a new switch position is indicated by the green LED going out for a short time.
					This also applies to the selection of the other switch positions.
	Т	flashes	flashes	2.5 s	Slow alternating flashing: Teach-In process has been performed correctly .
					Max. duration of the Teach-In process: 2 s
	Т	flashes	flashes	8/s	Quick alternating flashing: Teach-In process has not been performed correctly . (e.g. receiver signal not sufficient, sensor not directed correctly towards reflector).
					Status is terminated by turning switch to position N.
3/1	1	on	on	-	Contrast detection 10 % is activated. (e.g. clean PET bottles filled with water)
3/2	II	on	on	-	Contrast detection 18 % is activated. (e.g. clear glass bottles)
3/3	III	on	on	-	Contrast detection 40 % is activated. (e.g. coloured glass or non-transparent materials)

FPEPPERL+FUCHS