

## Thru-beam sensor

# LD28/LV28-F1-3057/35/47/115b




- Ultra bright LEDs for power on, weak signal indication and switching state
- Highly visible LED as alignment aid in receiver optics
- Delivery status: Light on switching
- Emitter deactivation
- Various transmitter frequencies
- Not sensitive to ambient light, even with switched energy saving lamps
- Waterproof, degree of protection IP67
- Protection class II

Universal thru-beam sensor, large housing design, 65 m detection range, red light, 25 kHz transmission frequency, light/dark on, DC version, 2 PNP outputs, test input, fixed cable with M12 plug

## 

## Dimensions



Release date: 2023-04-04 Date of issue: 2023-04-04 Filename: 181738\_eng.pdf

### **Technical Data**

| System components  |                                      |   |  |
|--|--------------------------------------|---|--|
| Emitter  |                                      | LD28-F1-3057/35/76a/115b  |  |
| Receiver   |                                      | LV28-F1-3057/35/47/115b   |  |
| General specifications   |                                      |   |  |
| Effective detection range  |                                      | 0 65 m  |  |
| Threshold detection range  |                                      | 90 m  |  |
| Light source   |                                      | LED   |  |
| Light type   | modulated visible red light , 660 nm |   |  |
| Alignment aid  |                                      | LED red (in receiver lens)<br>illuminated constantly: beam is interrupted,<br>flashes: reaching switching point,<br>off: sufficient stability control   |  |
| Transmitter frequency  |                                      | F1 = 25 kHz   |  |
| Diameter of the light spot   |                                      | approx. 1.3 m at 65 m   |  |
| Opening angle  |                                      | Emitter 1.2°,<br>Receiver 5°  |  |
| Ambient light limit  |                                      | 50000 Lux   |  |
| Functional safety related parameters                                       |                                      |   |  |
| MTTF <sub>d</sub>  |                                      | 620 a   |  |
| Mission Time (T <sub>M</sub> )   |                                      | 20 a  |  |
| Diagnostic Coverage (DC)   |                                      | 90 %  |  |
| Indicators/operating means   |                                      |   |  |
| Operation indicator  |                                      | LED green, flashes in case of short-circuit   |  |
| Function indicator   |                                      | LED yellow:<br>1. LED lit constantly: signal > 2 x switching point (function reserve)<br>2. LED flashes: signal between 1 x switching point and 2 x switching point<br>3. LED off: signal < switching point |  |
| Control elements   |                                      | sensitivity adjustment  |  |
| Electrical specifications  |                                      |   |  |
| Operating voltage  | U <sub>B</sub>                       | 10 30 V DC  |  |
| Ripple   |                                      | 10 %  |  |
| No-load supply current   | lo                                   | Emitter: ≤ 50 mA<br>Receiver: ≤ 35 mA   |  |
| Input  |                                      |   |  |
| Test input   |                                      | emitter deactivation at $+U_B$ (I <sub>max.</sub> < 3 mA at 30 V DC)  |  |
| Output   |                                      |   |  |
| Switching type   |                                      | light/dark on , preset to light-on  |  |
| Signal output  |                                      | 2 PNP, complementary, short-circuit protected, reverse polarity protected , open collectors   |  |
| Switching voltage  |                                      | max. 30 V DC  |  |
| Switching current  |                                      | max. 200 mA   |  |
| Switching frequency  | f                                    | 25 Hz   |  |
| Response time  |                                      | 20 ms   |  |
| Conformity   |                                      |   |  |
| Product standard   |                                      | EN 60947-5-2  |  |
| Approvals and certificates   |                                      |   |  |
| Protection class   |                                      | II, rated voltage $\leq$ 250 V AC with pollution degree 1-2 according to IEC 60664-1  |  |
| UL approval  |                                      | cULus   |  |
| CCC approval   |                                      | CCC approval / marking not required for products rated ≤36 V  |  |
| Ambient conditions   |                                      |   |  |
| Ambient temperature  |                                      | -40 60 °C (-40 140 °F)  |  |
| •  |                                      | -40 75 °C (-40 167 °F)  |  |
| Storage temperature  |                                      |   |  |
| - ·  |                                      |   |  |
| Mechanical specifications  |                                      | 25.8 mm   |  |
| Storage temperature Mechanical specifications Housing width Housing height |                                      | 25.8 mm<br>88 mm  |  |

 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 Get

 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com


#### Thru-beam sensor

### LD28/LV28-F1-3057/35/47/115b

#### **Technical Data**

| Degree of protection | IP67  |
|----------------------|---|
| Connection           | fixed cable 230 mm with M12 x 1 male connector, 4-pin |
| Material             |   |
| Housing              | Plastic ABS   |
| Optical face         | Plastic pane  |
| Mass                 | 500 g (emitter and receiver)                          |

## Connection



O = Light on

= Dark on

#### **Connection Assignment**



Wire colors in accordance with EN 60947-5-2


| 1 | BN | (brown) |
|---|----|---------|
| 2 | WH | (white) |
| 3 | BU | (blue)  |
| 4 | BK | (black) |

Release date: 2023-04-04 Date of issue: 2023-04-04 Filename: 181738\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".



#### **Characteristic Curve**



Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

