((


Model Number

NBN3-F31K-Z8-3D


Features

- Direct mounting on standard actuators
- Compact and stable housing
- Fixed setting
- Satisfies machinery directive

Connection



Dimensions



Technical Data

General	specifications

General Specifications		
Switching element function		DC binary NO
Rated operating distance	s _n	3 mm
Installation		flush mountable
Output polarity		DC
Assured operating distance	s _a	0 2.43 mm
Reduction factor r _{Al}		0.5
Reduction factor r _{Cu}		0.4
Reduction factor r _{V2A}		1
Reduction factor r _{St37}		1.1
Nominal ratings		

Nominal ratings

Operating voltage	U_B	6 60 V
Switching frequency	f	0 500 Hz
Hysteresis	Н	typ. 5 %
Reverse polarity protection		tolerant
Short-circuit protection		no
Voltage drop	U_d	≤ 6 V
Operating current	ΙL	4 100 mA
Off-state current	I _r	0 1 mA typ. 0.7 mA
Indication of the switching state		LED, yellow

Limit data

0.4 Nm Tightening torque, fixing screws

Standard conformity

EMC in accordance with IEC / EN 60947-5-2:2004 Standards IEC / EN 60947-5-2:2004

Ambient conditions

-25 ... 70 °C (248 ... 343 K) Ambient temperature

Mechanical specifications

Connection (system side) Cage clamp terminals 1.5/2.5 mm² flexible/rigid Core cross-section (system side) Housing material PBT Sensing face IP65 Protection degree

General information

Use in the hazardous area see instruction manuals Category 3D

ATEX 3D

Instruction

Manual electrical apparatus for hazardous areas

Device category 3D

Directive conformity

Standard conformity

CE symbol

Ex-identification General

Installation, Comissioning

Maintenance

[Fett]Special conditions

Maximum operating current IL

Maximum operating voltage UBmax

Maximum heating (Temperature rise)

at U_{Bmax} =60 V, I_{L} =100 mA at U_{Bmax} =60 V, I_{L} =50 mA at U_{Bmax} =60 V, I_{L} =25 mA Protection from mechanical danger

Connections for external wire

Lead insertion

for use in hazardous areas with non-conducting combustible dust

94/9/FG EN 50281-1-1

Protection via housing Use is restricted to the following stated conditions

CE

15 °C

11 °C

⟨EX⟩ II 3D IP65 T 93 °C X

The apparatus has to be operated according to the appropriate data in the data sheet and in this instruction manual. The data stated in the data sheet are restricted by this operating instruction! The special conditions must be adhered to!

Laws and/or regulations and standards governing the use or intended usage goal must be observed.

No changes can be made to apparatus, which are operated in hazardous areas.

Repairs to these apparatus are not possible.

The maximum permissible load current must be restricted to the values given in the following list.

High load currents and load short-circuits are not permitted.

The maximum permissible operating voltage UBmax must be restricted to the values given in the following list. Toleran-

ces are not permitted.

dependant of the load current I_L and the max. operating voltage U_{Bmax} . Information can be taken from the following list. The maximum surface temperature at maximum ambient temperature

is given in the Ex identification of the apparatus. 23 °C

The sensor must not be mechanically damaged

The connecting cable must not be disconnected under voltage!

Terminal connection: minimum conductor cross-section: 0.5 mm², maximum conductor cross-section: 2.5 mm².

The cable entry must be such, that no tension load or twist is applied to the cable

The protection category must be in accordance with EN 60529 and as stated in the data sheet. The cable entry must be designed so that there are no sharp edges to damage the cable and impair the level of protection of the sensor. The cable entry must be in accordance with the relevant European standard for industrial cable and lead entries.. In addition, in the case of flexible leads, the points of entry of the cable must be rounded off over an angle of at least 75°, with a radius (R), which is at least one quarter of the maximum permissible cable diameter for the entry, but not greater than 3 mm.