




CE



VISCO ECOLAB

Dimensions



Model Number


ML7-8-H-140-RT/65a/115b/120

Background suppression sensor with fixed cable and M12 connector, 4-pin

Features

- Miniature design
- Reliable detection of all surfaces, independent of color and structure
- Minimal black-white difference
- Precision background suppression, adjustable
- Clearly visible function indicators
- Short circuit and low voltage indicator
- Certified by ECOLAB

Electrical connection



- O = Light on
- = Dark on

Product information

Small, robust, effective, and reliable - these are the properties of the ML7 sensor series. Due to their small size, number of versions, and two different lens positions, they are particularly suited for installation in tight spaces. The robust design and high quality of Pepperl+Fuchs mean they can also be used under harsh environmental conditions. The efficient technology, switching frequencies up to 1000 Hz, high resistance to ambient light, and 4-in-1 output make the series suitable for non-contact object detection.


Pinout


Wire colors in accordance with EN 60947-5-2



(brown (white) (blue)

Indicators/operating means





1	Operating display green		
2	Signal display	yellow	
3	Sensing range adjuster		
4	Emitter		
5	Receiver TW min.		
6	Receiver TW max.		

Technical data		
General specifications		
Detection range		5 140 mm
Detection range min.		5 25 mm
Detection range max.		13 140 mm
Adjustment range		25 140 mm
Reference target		standard white, 100 mm x 100 mm
Light source		LED
Light type		modulated visible red light
Black/White difference (6 %/90 %)		< 10 %
Diameter of the light spot		approx. 5 mm at detection range 120 mm
Functional safety related param	eters	
MTTF _d		1580 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		0 %
Indicators/operating means		
Operation indicator		LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit: LED green flashing (approx. 4 Hz)
Function indicator		LED yellow: lights when object is detected
Control elements		Sensing range adjuster
Electrical specifications		
Operating voltage	U_B	10 30 V DC , class 2
Ripple		max. 10 %
No-load supply current	I ₀	< 20 mA
Output		
Switching type		light/dark on
Signal output		2 PNP, complementary, short-circuit protected, reverse polarity protected
Switching voltage		max. 30 V DC
Switching current		max. 100 mA
Switching frequency	f	1 kHz
Response time		500 μs
Conformity		
Product standard		EN 60947-5-2
Ambient conditions		
Ambient temperature		-20 60 °C (-4 140 °F)
Storage temperature		-40 75 °C (-40 167 °F)
Mechanical specifications		
Housing width		11 mm
Housing height		31 mm
Housing depth		23 mm
Degree of protection		IP67 / IP69K
Connection		fixed cable 200 mm with M12 connector, 4-pin
Material		
Housing		PC (glass-fiber-reinforced Makrolon)
Optical face		PMMA
Mass		approx. 10 g
Approvals and certificates		
Protection class		II, rated voltage ≤ 50 V AC with pollution degree 1-2 according to IEC 60664-1
UL approval		cULus

Accessories

Montagekit OMH-ML7-01

Mounting set consisting of bracket OMH-ML-01 sheet OMH-ML7-03, and fastening material

Montagekit OMH-ML7-02

Mounting set consisting of bracket OMH-ML-02 sheet OMH-ML7-03, and fastening material

OMH-ML7-01

Mounting aid for ML7 and ML8 series, Mounting bracket

OMH-ML7-02

Mounting aid for ML7 and ML8 series, Mounting bracket

OMH-ML7-03


Mounting aid for ML7 and ML8 series, Fixing plate

Other suitable accessories can be found at www.pepperl-fuchs.com

CCC approval

CCC approval / marking not required for products rated ≤36 V

Curves/Diagrams



Curves/Diagrams

