


Function

This isolated barrier is used for intrinsic safety applications. The device can be used in shut down applications with HART positioners. Via the logic input the positioner is energized or de-energized (shut down). Independent of the status, a second input enables HART communication with the positioner. With this the asset management system can request for example diagnostic information or can initiate a partial stroke test. The HART communication also works with deenergized positioner. A unique collective error messaging feature is available when used with the Power Rail system.

Connection



Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Release date: 2022-01-17 Date of issue: 2022-01-17 Filename: 216568_eng.pdf



Solenoid Driver

KFD2-RCI-Ex1

Technical Data		
Connection		terminals 10+, 11-
Input current		40 mA at 19 30 V DC
Signal level		1-signal: 19 30 V DC 0-signal: 0 5 V DC
Power consumption		< 1.2 W
Operating mode		loop powered
Output		
Connection side		field side/control side
Connection		terminals 1+, 3- (terminals 1+, 2 for test loop)
Internal resistor	Ri	approx. 275 Ω
Current	l _e	≤ 20.4 mA
Voltage	Ue	≥ 13.5 V
Open loop voltage	Us	> 16 V
Voltage		1-signal: > 13.5 V
Current		1-signal: 20.4 A 0-signal: 4.2 mA
Load		max. 650 Ω
Response time		< 40 ms input to output
Line fault detection		short circuit voltage < 1 V , open circuit voltage > 16 V
Output II		
Connection		terminal 7: source (-) or sink (+), terminal 8: source (+), terminal 9: sink (-)
Current		11 mA (source or sink mode)
Voltage		9 30 V sink mode from external supply
Load		max. 650 Ω , source mode , for HART \geq 230 Ω
Communication		pass-through of HART signal between input II and output
Galvanic isolation		
Input/power supply		functional insulation acc. to IEC 62103, rated insulation voltage 50 V_{eff}
Output II/power supply		functional insulation acc. to IEC 62103, rated insulation voltage 50 $\mathrm{V}_{\mathrm{eff}}$
Indicators/settings		
Display elements		LEDs
Control elements		DIP switch
Configuration		via DIP switches
Labeling		space for labeling at the front
Directive conformity		
Electromagnetic compatibility		
Directive 2014/30/EU		EN 61326-1:2013 (industrial locations)
Conformity		
Electromagnetic compatibility		NE 21:2012
Degree of protection		IEC 60529:2001
Ambient conditions		
Ambient temperature		-20 60 °C (-4 140 °F)
Mechanical specifications		
Degree of protection		IP20
Connection		screw terminals
Mass		approx. 150 g
Dimensions		20 x 119 x 115 mm (0.8 x 4.7 x 4.5 inch) (W x H x D) , housing type B2
Mounting		on 35 mm DIN mounting rail acc. to EN 60715:2001
Data for application in connection with haza	rdous a	
EU-type examination certificate		CESI 09 ATEX 037
Marking		II (1)GD [Ex ia] IIC; [Ex iaD] [circuit(s) in zone 0/1/2/20/21/22]
Equipment		terminals $1+$, $2/3-$
Voltage	U。	24.5 V
Current	I _o	93.6 mA
Power	Po	595 mW (linear characteristic)
	U	

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"


Release date: 2022-01-17 Date of issue: 2022-01-17 Filename: 216568_eng.pdf

Solenoid Driver

KFD2-RCI-Ex1

Technical Data		
Supply		
Maximum safe voltage	Um	253 V (Attention! The rated voltage can be lower.)
Input		
Maximum safe voltage	Um	253 V (Attention! The rated voltage can be lower.)
Collective error message		
Maximum safe voltage	Um	253 V (Attention! The rated voltage can be lower.)
Certificate		PF 09 CERT 1438 X
Marking		ll 3G Ex nA IIC T4 Gc
Galvanic isolation		
Output I/other circuits		safe electrical isolation acc. to IEC/EN 60079-11, voltage peak value 375 V
Directive conformity		
Directive 2014/34/EU		EN 60079-0:2012+A11:2013, EN 60079-11:2012, EN 60079-15:2010
International approvals		
CSA approval		
Control drawing		116-0335
IECEx approval		
IECEx certificate		IECEx CES 09.0008
IECEx marking		[Ex ia] IIC , [Ex iaD]
General information		
Supplementary information		Observe the certificates, declarations of conformity, instruction manuals, and manuals where applicable. For information see www.pepperl-fuchs.com.

Assembly



Matching System Components

KFD2-EB2

Power Feed Module

UPR-03

Universal Power Rail with end caps and cover, 3 conductors, length: 2 $\ensuremath{\mathsf{m}}$

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group www.pepperl-fuchs.com

USA: +1 330 486 0002 pa-info@us.pepperl-fuchs.com Germany: +49 621 776 2222 pa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 pa-info@sg.pepperl-fuchs.com



KFD2-RCI-Ex1

Matching System Components

UPR-03-M	Universal Power Rail with end caps and cover, 3 conductors, length: 1,6 m
UPR-03-S	Universal Power Rail with end caps and cover, 3 conductors, length: 0.8 m
K-DUCT-BU	Profile rail, wiring comb field side, blue
K-DUCT-BU-UPR-03	Profile rail with UPR-03- * insert, 3 conductors, wiring comb field side, blue

Accessories

	KF-ST-5GN	Terminal block for KF modules, 3-pin screw terminal, green
	KF-ST-5BU	Terminal block for KF modules, 3-pin screw terminal, blue
*	KF-CP	Red coding pins, packaging unit: 20 x 6

 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group
 USA: +1 330 486 0002
 Gr

 www.pepperl-fuchs.com
 pa-info@us.pepperl-fuchs.com
 pa-info@us.pepperl-fuchs.com

4

Application

The device supplies power to safety valve controller with HART functionality.

It is controlled by means of a logic circuit. Voltage signals in a range of 19 V DC ... 30 V DC are accepted as 1-signal. The 0-signal must be within a range of 0 V DC ... 5 V DC. The current consumption of the logic input is about 40 mA.

At full load, 13.5 V at 20.4 mA is available for the hazardous area load.

Line fault detection of the field circuit is indicated by a red LED. The error signal switches on if the field voltage is > 16 V for lead breakage (LB) or < 1 V for short circuit (SC).

This device provides the HART pass-trough for maintenance and diagnostic of the solenoid valve. The HART communication is available both in ON condition and in OFF condition of the solenoid.

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

