





(€ ¢((

# **Model Number**

#### SBL-8-H-SL-V-Z-4568

Background suppression sensor with 4-pin, M12 x 1 connector and fixed cable with 4-pin, M12 socket

## **Features**

- Background suppression sensor for roller conveyors
- For installation between the rollers on a roller conveyor
- Pull-in/Drop-out delay can be set
- Minimal black/white difference
- Protection degree IP65
- Can be connected in series


## **Product information**

Sensors of the SBL series are used to easily control material flow on roller conveyors in material handling and other branches.


The SBL series is a precise background suppression sensor according to the 3 element method. The sensor features superior background suppression and a very good ambient light immunity. Material and transport container of all colors and opacities are reliably detected.

The special design allows the sensor to be mounted between the rollers of a roller conveyor or any other conveying unit. Mounting between the rollers is easy and protects the sensor.

## **Dimensions**




## **Electrical connection**




 \*) see table to functionality on the following page

- O = Light on
- = Dark on

## **Pinout**



# Indicators/operating means



|  | 1 | Signal display         | yellow |
|--|---|------------------------|--------|
|  | 2 | Sensing range adjuster |        |

| Technical data                   |                |  |  |  |  |
|----------------------------------|----------------|--|--|--|--|
| General specifications           |                |  |  |  |  |
| Detection range                  |                | 40 900 mm  |  |  |  |
| Detection range min.             |                | 40 340 mm  |  |  |  |
| Detection range max.             |                | 40 900 mm  |  |  |  |
| Adjustment range                 |                | 340 900 mm   |  |  |  |
| Reference target                 |                | standard white 200 mm x 200 mm   |  |  |  |
| Light source                     |                | IRED   |  |  |  |
| Light type                       |                | modulated infrared light , 880 nm  |  |  |  |
| Black/White difference (6 %/90   | (%)            | < 10 %   |  |  |  |
| Diameter of the light spot       |                | approx. 60 mm at detection range 900 mm  |  |  |  |
| Cascadability                    |                | max. 25 sensors per line   |  |  |  |
| Ambient light limit              |                | continuous light 30000 Lux, Fluorescent lamp 5000 Lux  |  |  |  |
| Indicators/operating means       |                |  |  |  |  |
| Function display                 |                | LED yellow: lights when object is detected   |  |  |  |
| Controls                         |                | Detection range adjuster   |  |  |  |
| Controls                         |                | Adjuster for switch-off delay and switch-on delay  |  |  |  |
| Electrical specifications        |                |  |  |  |  |
| Operating voltage                | $U_B$          | 24 V DC  |  |  |  |
| Ripple                           |                | max. 10 %  |  |  |  |
| No-load supply current           | I <sub>0</sub> | max. 125 mA  |  |  |  |
| Output                           |                |  |  |  |  |
| Switching type                   |                | light on   |  |  |  |
| Signal output                    |                | 1 PNP, short-circuit protected, reverse polarity protected   |  |  |  |
| Switching voltage                |                | max. 30 V DC   |  |  |  |
| Switching current                |                | max. 200 mA  |  |  |  |
| Switching frequency              | f              | 100 Hz   |  |  |  |
| Response time                    |                | 5 ms   |  |  |  |
| On-delay                         |                | 0 2000 ms  |  |  |  |
| Off-delay                        |                | 0 2000 ms  |  |  |  |
| Pneumatic output                 |                | 2/3 way valve  |  |  |  |
| Type of valve                    |                | currentless closed   |  |  |  |
| Operating pressure               |                | 0 7 bar (0 101.5 psi)  |  |  |  |
| Medium                           |                | air  |  |  |  |
| Ambient conditions               |                |  |  |  |  |
| Ambient temperature              |                | -20 50 °C (-4 122 °F)  |  |  |  |
| Storage temperature              |                | -30 60 °C (-22 140 °F)   |  |  |  |
| Mechanical specifications        |                | 00 00 0 ( ZZ 140 T )   |  |  |  |
| Protection degree                |                | IP65   |  |  |  |
| Connection                       |                | connector M12 x 1, 4-pin; Connecting cable with Socket,  |  |  |  |
| Connection                       |                | straight M12 x 1; 4-pin; Connecting Cable With Socket,   |  |  |  |
| Material                         |                |  |  |  |  |
| Housing                          |                | plastic  |  |  |  |
| Optical face                     |                | plastic lens   |  |  |  |
| Mass                             |                | approx. 200 g  |  |  |  |
| Compliance with standards ar ves | nd directi     | i-   |  |  |  |
| Directive conformity             |                | EMC Directive 2004/108/EC  |  |  |  |
| Standard conformity              |                |  |  |  |  |
| Product standard                 |                | EN 60947-5-2:2007<br>IEC 60947-5-2:2007  |  |  |  |
| Shock and impact resistance      |                | IEC / EN 60068. half-sine, 40 g in each X, Y and Z directions  |  |  |  |
| Vibration resistance             |                | IEC / EN 60068-2-6. Sinus. 10 -1000 Hz, 10 g in each X, Y and Z directions   |  |  |  |
| Approvals and certificates       |                |  |  |  |  |
| UL approval                      |                | cULus Listed, Class 2 Power Source, Type 1 enclosure   |  |  |  |
| CCC approval                     |                | Products with a maximum operating voltage of ≤36 V do not bear a CCC marking because they do not require approval. |  |  |  |

## **Accessories**

# OMH-SBL-01

Mounting bracket for sensors of SBL se-

## V1-G-2M-PVC

Cable socket, M12, 4-pin, PVC cable

#### V1-G-5M-PVC

Cable socket, M12, 4-pin, PVC cable

## V1-W-2M-PUR

Cable socket, M12, 4-pin, PUR cable

# V1-W-5M-PUR

Cable socket, M12, 4-pin, PUR cable

## V1S-TEE-V1/V1S

T-Distributor, M12 connector to M12 socket/connector

# Schraubendreher 0,5 x 3,0 mm

Screwdriver


Additional accessories can be found in the Internet.

Release date: 2011-02-23 16:52 Date of issue: 2012-02-17 219000\_eng.xml

**EPPERL+FUCHS** 

www.pepperl-fuchs.com

## **Curves/Diagrams**



# **Additional Information**

#### Intended use:

The transmitter and receiver are located in the same housing for direct detection sensors with background masking. Marking of objects outside the detection range is achieved by arranging the angle between the transmitter and receiver (2 receiver elements).

Objects are detected independently of the structure and colour of the surface.

The special design of the sensors makes it possible to install them between two rollers in the roller back-up conveyor systems under the material that is being moved. This allows for installation that saves space and prevents mechanical damage of the sensor caused by material being conveyed.

## **Mounting instructions:**

The sensors can be directly fastened in place with the pass-through bore holes or can be attached with a support bracket or a clamp (the last two are not included in delivery).

The surface underneath must be flat to prevent the housing from moving when it is tightened into position. We recommend securing the nut and screw in place with spring washers to prevent the sensor from going out of adjustment.

## For versions SBL-8-H-SL, -V, -Z

As many as 25 sensors can be cascaded with the aid of just one power supply. A solenoid valve is energised if the corresponding sensor itself or its predecessor in the cascade does not see any object.

It is also possible to energise the valves of all sensors included in the cascade with block movement  $(V_T)$ . To do this, apply the positive supply voltage (+UB) on the input  $V_T$  of the first sensor.

#### Adjustment:

Align the sensor to the background. If the yellow LED is lit, the detection range should be reduced with the detection range adjuster until the yellow LED goes out.

## Object detection:

Position the object to be detected in the path of the beam. If the object is detected, the yellow LED lights up.

If it does not light up, the detection range must be further adjusted on the potentiometer until it lights up when an object is detected.

## Version SBL-8-H-SL-V-Z only:

The two adjusting mechanisms on the front side of the sensor can be used separately for timer functions for the switching on or switching off process.

This results in a delay defined by the adjuster between the change of state (object detected -> object not detected or vice-versa) and the switching process. The duration of the delay can be set for up to 2 seconds.

## Cleaning:

We recommend cleaning the optical surface and checking all connections at regular intervals.

#### Note:

Use a screwdriver to adjust the sensing range. We strongly recommend to use the screwdriver given in the accessories section.