


# Inductive positioning system


# PMI210-F110-IU-V1


- Analog output 0 V ... 10 V/4 mA ... 20 mAMeasuring range 0 ... 210 mm



### **Dimensions**







## **Technical Data**


| General specifications               |       |                                   |
|--------------------------------------|-------|-----------------------------------|
| Switching element function           |       | analog, current or voltage output |
| Object distance                      |       | max. 6 mm                         |
| Measurement range                    |       | 0 210 mm                          |
| Nominal ratings                      |       |                                   |
| Operating voltage                    | $U_B$ | 18 30 V DC                        |
| Reverse polarity protection          |       | reverse polarity protected        |
| Linearity error                      |       | ± 0.4 mm                          |
| Repeat accuracy                      | R     | ± 0.2 mm                          |
| Resolution                           |       | 210 μm                            |
| Temperature drift                    |       | ± 0.5 mm (-25 °C 70 °C)           |
| No-load supply current               | $I_0$ | ≤ 40 mA                           |
| Operating voltage indicator          |       | LED green                         |
| Functional safety related parameters |       |                                   |

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Release date: 2021-04-06 Date of issue: 2021-04-06 Filename: 191142\_eng.pdf

## Connection

IU



Core colours in accordance with EN 60947-5-2.

## **Connection Assignment**



Wire colors in accordance with EN 60947-5-2

| 1 | BN | (brown) |
|---|----|---------|
| 2 | WH | (white) |
| 3 | BU | (blue)  |
| 4 | BK | (black) |

# **Accessories** BT-F110-G Damping element for F110 housing sensors; front screw holes Damping element for F110 housing sensors; lateral screw holes BT-F110-W Female cordset single-ended M12 straight A-coded, 4-pin, PVC cable grey V1-G-2M-PVC MH-F110 Mounting bracket for mounting F110 series sensors

#### Instruction manual

· Security advice



Note

This product must not be used in applications, where safety of persons depend on the correct device function.

This product is not a safety device according to EC machinery directive.


· Sensor Properties

The inductive positioning system F110 provides both, a current and voltage signal at the outputs, which is proportional to the position of the attenuating element.

Output signals: 4 mA ... 20 mA and 0 V ... 10 V

· Attenuating element

The inductive position encoding system F110 is optimally adjusted to the geometry of the attenuating elements we offer (see accessories, below).



A different width has a direct impact on the achievable resolution and accuracy of the system.

Spacing between sensor and attenuating element is from 0 ... 6 mm.

Sensing accuracy is guaranteed between 1 ... 6 mm..


· Installation and operation


#### Notes on installation

- A flush installation is possible.
- Fixation and installation of the positioning system F110 is carried out by the use of t-slides. This
  provides a flexible adaptation to the field situation.



- The distance between the measuring field (bordered area at the front of the sensor) and the fixing base or fixing element of the attenuating element must at least be 6 mm.







Notes on operation

The sensor accuracy can be guaranteed, when the spacing between attenuating element and sensor is within an interval of 1 ... 6 mm.

When the attenuating element leaves the measurement range (figures below):

- the last valid value is maintained at the voltage output until the attenuating element re-enters the valid range.
- the last valid value is maintained at the current output for 0.5 seconds. Afterwards, the output changes to a fault current of 3.6 mA until the attenuating element re-enters the valid range.





Definition of measuring range / of measured position


The measured attenuating elements (actuators) position refers to half its width (middle of the actuator). The measuring range starts and ends when the attenuating element overlaps the labeled measuring area on the sensor at transversal motion (see

Accessories

#### Attenuating elements BT-F110-G









Straight cables:V1-G-2M-PVC (4 wire) Angled cables:V1-W-2M-PVC (4 wire)