

# **Termination Board**

## HiCTB16-TRI-DIISS-EL-PL

- System board for Schneider Electric, Tricon series by Triconex
- TAN48 approval
- For 32-channel (16+16) DI card 3503E
- For 16 modules
- Recommended module: HiC2821 (DI)
- 24 V DC supply
- Line fault detection (LFD)
- Hazardous area: pluggable screw terminals, blue
- Non-hazardous area: ELCO socket, 56-pin











#### **Function**

The function of the termination board and the connector pinout is exactly fitted to the requirements of Triconex system.

The termination board has a fault bus (Fault) that is available at the redundant terminals. Power supply faults and module faults are indicated via this fault bus. The fault signals of several termination boards can be connected together and can be monitored by an optional fault indication board. The fault signals are then available to the control system as a volt-free contact.

In addition, the termination board has a fault indication output (LFD), which will be used to indicate module faults as a volt-free contact. These fault signals can also be output via this fault indication output without a separate fault indication board. This assumes that the termination board is fully equipped and the isolators are configured for this function.

The termination board is supplied with a robust plastic housing. This design permits the fast and reliable installation on 35 mm DIN mounting rail according to EN 60715 in the switch cabinet.

### **Application**


Triconex card Tricon:

- Termination board 1 and cable 1: channel 1 to 16
- Termination board 2 and cable 2: channel 17 to 32

Line fault detection

- A line fault detection via the X20 fault bus (Fault) and the separate HiATB01-FAULT-01 fault indication board is always possible, regardless of whether the termination board is partially or fully equipped.
- A line fault detection via the X3 fault indication output (LFD) of the termination board is only possible if the termination board is fully equipped with isolators.

#### Connection




#### Technical Data

Supply



Technical Data		
Connection	X20: terminals 3, 5(+); 4, 6(-)	
Nominal voltage	24 V DC, in consideration of rated voltage of used isolators	
Voltage drop	0.9 V , voltage drop across the series diode on the termination board must be considered	
Ripple	≤ 10 %	
Fusing	4 A, in each case for 16 modules	
Power dissipation	≤ 500 mW , without modules	
Reverse polarity protection	yes	
Redundancy		
Supply	Redundancy available. The supply for the isolators is decoupled, monitored and fuse	
Fault indication output		
Connection	fault bus (Fault) : X20: terminals 1, 2 fault indication output (LFD) : X3: terminals 1, 2	
Output type	volt-free contact	
Switch behaviour	fault bus (Fault) - no fault: relay contact of the fault indication board closed - power supply fault: relay contact of the fault indication board open - module fault: relay contact of the fault indication board open fault indication output (LFD) - no fault: relay contact closed - module fault: relay contact open	
Contact loading	fault bus (Fault): 30 V DC, 1 A, see fault indication board fault indication output (LFD): see datasheet of isolated barrier	
Indicators/settings		
Display elements	LED PWR1 (termination board power supply), green LED LED PWR2 (termination board power supply), green LED	
Directive conformity		
Electromagnetic compatibility		
Directive 2014/30/EU	EN 61326-1:2013 (industrial locations)	
Conformity		
Electromagnetic compatibility	NE 21:2017 For further information see system description.	
Degree of protection	IEC 60529:2001	
Ambient conditions		
Ambient temperature	-20 60 °C (-4 140 °F)	
Storage temperature	-40 70 °C (-40 158 °F)	
Mechanical specifications		
Degree of protection	IP20	
Connection		
Field side	explosion hazardous area: pluggable screw terminals , blue	
Control side	non-explosion hazardous area: ELCO socket, 56-pin	
Supply	pluggable screw terminals, black	
Fault output	pluggable screw terminals, black	
Core cross section	screw terminals: 0.2 2.5 mm² (24 12 AWG)	
Material	housing: polycarbonate, 10 % glass fiber reinforced	
Mass Dimensions	approx. 785 g 216 x 200 x 163 mm (8.5 x 7.9 x 6.42 inch) (W x H x D) , depth including module	
	assembly	
Mounting	on 35 mm DIN mounting rail acc. to EN 60715:2001	
Data for application in connection with hazardo		
EU-type examination certificate	CESI 06 ATEX 022	
Marking	<ul> <li>☑ II (1)G [Ex ia Ga] IIC</li> <li>☑ II (1)D [Ex ia Da] IIIC</li> <li>☑ I (M1) [Ex ia Ma] I</li> </ul>	
Non-hazardous area		
Maximum safe voltage	250 V (Attention! U <sub>m</sub> is no rated voltage.)	
Galvanic isolation		
Field circuit/control circuit	safe electrical isolation acc. to IEC/EN 60079-11, voltage peak value 375 V	



pdf
ang.
8
: 22238
ilename
20 Fi
3-02-20
2023-
:issne:
6
Date
-02-20
2023-02
date:
Release


#### **Technical Data** Directive conformity Directive 2014/34/EU EN IEC 60079-0:2018+AC:2020, EN 60079-11:2012, EN 50303:2000 International approvals **UL** approval E106378 Control drawing 116-0327 IECEx approval IECEx certificate IECEx CES 06.0003 [Ex ia Ga] IIC [Ex ia Da] IIIC [Ex ia Ma] I IECEx marking **General information** Observe the certificates, declarations of conformity, instruction manuals, and manuals where applicable. For information see www.pepperl-fuchs.com. Supplementary information

### **Accessories**



HiALC-HiCTB-SET-108 Label carrier for HiC termination boards

#### **Typical circuit**



### Module switch settings

If you want to use line fault detection (LFD), configure the modules as described in the following table. Note that all modules on the termination board must have the same configuration settings.

Type (DI)	DIP switch	Position
HiC2821	S1	II
Mode of operation:	S2	1
close – energized open – de-energized	S3	II
Second output: as fault     Input line fault detection: enabled	S4	no function



For exact pin assignment for connection to field side and control side, see the documentation of the isolated barrier.



The pin-out configuration has to be observed. For information see corresponding pin-out table on www.pepperl-fuchs.com.