



Diffuse mode sensor WTS10-12/21/105



- Specifically for quality checks on welding caps
- Upper and lower welding caps checked simultaneously
- High position and angle tolerance insensitivity of the welding cap
- Stability alarm indication
- Scratch resistant mineral glass lens

Diffuse mode sensor









Function

The welding tip sensor WTS10 series is a contrast evaluation sensor with a large and homogeneous light spot fitted to check the quality of the welding cap's face after milling of the welding tip and which is widely used for industrial welding robots.


After the milling process of the welding cap, both tips of the welding gun are inspected and defects such as inclusions, faulty milling or burrs are


Simultaneous control of the quality of both welding tip caps with one sensor is possible by providing two optical outputs on either side of the

sensor housing.

The WTS10 features an extended detection area of 11 mm diameter, an uniform lightspot over the full sensing range due to coaxial optics beam path, a new display concept, high switching accuracy, a homogenous light spot and improved position and tilting angle tolerance.

Dimensions





	_			\	
10	~n				ta
15	UII	 ca	_	70	


General specifications

delicial opcomoditions		
Detection range		2 12 mm
Reference target		Copper welding-electrode Diameter: 16 mm , Front end: 6 mm
Light source		LED
Light type		modulated visible red light , 640 nm
Ambient light limit		continuous light 40000 Lux, Modulated light 5000 Lux
Tilting angle		± 1.5 °
Position tolerance		± 2 mm
Indicators/operating means		
Operation indicator		LED green: Power on
Function indicator		LED yellow: switching state LED red: Stability alarm indicator
Teach-In indicator		LED, green/yellow flashing (approx. 4 Hz) Teach Error:LED green/yellow non equiphase flashing; 8.0 Hz
Control elements		Teach-In key
Electrical specifications		
Operating voltage	U_B	10 30 V DC
No-load supply current	I_0	≤ 70 mA
Output		
Switching type		light-on
Signal output		2 switch outputs NPN, NO short-circuit protected reverse polarity protected
Switching current		max. 100 mA
Switching frequency	f	100 Hz

Response time 5 ms Conformity Product standard EN 60947-5-2 Compliance with standards and directives Standard conformity Shock and impact resistance IEC / EN 60068. half-sine, 50 g in each X, Y and Z directions Vibration resistance IEC / EN 60068-2-6. Sinus. 10 -150 Hz, 5 g in each X, Y and Z directions Approvals and certificates Protection class II, rated voltage ≤ 250 V AC with pollution degree 1-2 according to IEC 60664- UL approval CUL sListed CCC approval CCC approval / marking not required for products rated ≤36 V Ambient conditions Ambient temperature 0 50 °C (32 122 °F) The switching accuracy will remain, if the temperature after Teach-In does not a more than ±7 °C Storage temperature -20 70 °C (-4 158 °F) Mechanical specifications Degree of protection IP67 Connection 5-pin. M12 x 1 connector	
Product standard EN 60947-5-2 Compliance with standards and directives Standard conformity Shock and impact resistance IEC / EN 60068. half-sine, 50 g in each X, Y and Z directions Vibration resistance IEC / EN 60068-2-6. Sinus. 10 -150 Hz, 5 g in each X, Y and Z directions Approvals and certificates Protection class II, rated voltage ≤ 250 V AC with pollution degree 1-2 according to IEC 60664- UL approval CULus Listed CCC approval CCC approval / marking not required for products rated ≤36 V Ambient conditions Ambient temperature 0 50 °C (32 122 °F) The switching accuracy will remain, if the temperature after Teach-In does not work than ±7 °C Storage temperature -20 70 °C (-4 158 °F) Mechanical specifications Degree of protection IP67	
Compliance with standards and directives Standard conformity Shock and impact resistance Vibration resistance Vibration resistance Approvals and certificates Protection class II, rated voltage ≤ 250 V AC with pollution degree 1-2 according to IEC 60664- UL approval CCC approval CCC approval Ambient conditions Ambient temperature O 50 °C (32 122 °F) The switching accuracy will remain, if the temperature after Teach-In does not varior than ±7 °C Storage temperature Degree of protection IP67	
Standard conformity Shock and impact resistance Vibration resistance Approvals and certificates Protection class UL approval CCC approval CCC approval Ambient conditions Ambient temperature O 50 °C (32 122 °F) The switching accuracy will remain, if the temperature after Teach-In does not word than ±7 °C Storage temperature Degree of protection IEC / EN 60068. half-sine, 50 g in each X, Y and Z directions IEC / EN 60068-2-6. Sinus. 10 -150 Hz, 5 g in each X, Y and Z directions III, rated voltage ≤ 250 V AC with pollution degree 1-2 according to IEC 60664-100 CCC approval / marking not required for products rated ≤36 V CCC approval / marking not required for products rated ≤36 V The switching accuracy will remain, if the temperature after Teach-In does not word than ±7 °C Storage temperature 1-20 70 °C (-4 158 °F) Mechanical specifications Degree of protection IP67	
Shock and impact resistance Vibration resistance Vibration resistance Approvals and certificates Protection class UL approval CCC approval CCC approval Ambient conditions Ambient temperature O 50 °C (32 122 °F) The switching accuracy will remain, if the temperature after Teach-In does not word than ±7 °C Storage temperature Degree of protection IEC / EN 60068. half-sine, 50 g in each X, Y and Z directions IEC / EN 60068-2-6. Sinus. 10 -150 Hz, 5 g in each X, Y and Z directions II, rated voltage ≤ 250 V AC with pollution degree 1-2 according to IEC 60664- CULus Listed CCC approval / marking not required for products rated ≤36 V Ambient temperature 0 50 °C (32 122 °F) The switching accuracy will remain, if the temperature after Teach-In does not word than ±7 °C Storage temperature 1 -20 70 °C (-4 158 °F) Mechanical specifications Degree of protection IP67	
Vibration resistance Approvals and certificates Protection class II, rated voltage ≤ 250 V AC with pollution degree 1-2 according to IEC 60664-7 UL approval CCC approval CCC approval CCC approval / marking not required for products rated ≤36 V Ambient conditions Ambient temperature O 50 °C (32 122 °F) The switching accuracy will remain, if the temperature after Teach-In does not vimore than ±7 °C Storage temperature -20 70 °C (-4 158 °F) Mechanical specifications Degree of protection IP67	
Approvals and certificates Protection class II, rated voltage ≤ 250 V AC with pollution degree 1-2 according to IEC 60664- UL approval CCC approval CCC approval / marking not required for products rated ≤36 V Ambient conditions Ambient temperature 0 50 °C (32 122 °F) The switching accuracy will remain, if the temperature after Teach-In does not wanted than ±7 °C Storage temperature -20 70 °C (-4 158 °F) Mechanical specifications Degree of protection IP67	
Protection class II, rated voltage ≤ 250 V AC with pollution degree 1-2 according to IEC 60664- UL approval CCC approval CCC approval / marking not required for products rated ≤36 V Ambient conditions Ambient temperature 0 50 °C (32 122 °F) The switching accuracy will remain, if the temperature after Teach-In does not with more than ±7 °C Storage temperature -20 70 °C (-4 158 °F) Mechanical specifications Degree of protection IP67	
UL approval CCC approval CCC approval / marking not required for products rated ≤36 V Ambient conditions Ambient temperature 0 50 °C (32 122 °F) The switching accuracy will remain, if the temperature after Teach-In does not was more than ±7 °C Storage temperature -20 70 °C (-4 158 °F) Mechanical specifications Degree of protection IP67	
CCC approval CCC approval / marking not required for products rated ≤36 V Ambient conditions Ambient temperature 0 50 °C (32 122 °F) The switching accuracy will remain, if the temperature after Teach-In does not with more than ±7 °C Storage temperature -20 70 °C (-4 158 °F) Mechanical specifications Degree of protection IP67	1
Ambient conditions Ambient temperature 0 50 °C (32 122 °F) The switching accuracy will remain, if the temperature after Teach-In does not want to more than ±7 °C Storage temperature -20 70 °C (-4 158 °F) Mechanical specifications Degree of protection IP67	
Ambient temperature 0 50 °C (32 122 °F) The switching accuracy will remain, if the temperature after Teach-In does not was more than ±7 °C Storage temperature -20 70 °C (-4 158 °F) Mechanical specifications Degree of protection IP67	
The switching accuracy will remain, if the temperature after Teach-In does not with more than ±7 °C Storage temperature -20 70 °C (-4 158 °F) Mechanical specifications Degree of protection IP67	
Mechanical specifications Degree of protection IP67	varies
Degree of protection IP67	
• .	
Connection Figin M10 v.1 connector	
Connection 5-pin, M12 x 1 connector	
Material	
Housing PC + ABS	
Optical face Scratch resistant mineral glass lens	
Mass 80 g	

Connection Assignment

Option:



- O = Light on
- = Dark on

Connection Assignment




Connection Assignment

Wire colors in accordance with EN 60947-5-2


1 BN (brown)
2 WH (white)
3 BU (blue)
4 BK (black)
5 GY (gray)


Assembly



1	LED Power On	green
2	LED channel I	red
3	LED channel I	yellow
4	Teach-In channel I	
5	LED channel II	yellow
6	LED channel II	red
7	Teach-In channel II	

Characteristic Curve





Teach-In

- 1. Position the reference welding cap in front of the optical system of the desired sensor channel (channel I or channel II).
- 2. Press and hold the corresponding teach-in button. The sensor confirms the keystroke by the green signal indicator being extinguished briefly (200 ms). After 2 s the sensor switches to teach-in mode: both switching outputs are deactivated. The sensor is taught the properly milled welding cap as a reference sample for the selected sensor channel.
- 3. When the green signal indicator and the yellow signal indicator that belongs to the selected sensor channel flash simultaneously, release the teach-in button. Teach-in is completed. The green signal indicator and the yellow signal indicator that belongs to the selected sensor channel flash alternately for 2 s.

Teach-in successful: The taught reference welding cap is permanently saved. The sensor switches back to switching mode. **Teach-in unsuccessful:** The green signal indicator and the yellow signal indicator that belongs to the selected sensor channel flash quickly (approx. 8 Hz) and alternately for 5 s. The sensor discards the taught values. After 5 s the sensor switches to switching mode and works with the last valid values. For signal levels below the fixed switching threshold, the teach-in mode can't be entered. A teach-in error is indicated.

Accessories

	OMH-WTS10-01	Mounting bracket for sensors of WTS10 series
6/	V15-G-2M-PVC	Female cordset single-ended M12 straight A-coded, 5-pin, PVC cable grey
6/	V15-G-2M-PUR	Female cordset single-ended M12 straight A-coded, 5-pin, PUR cable grey
6/	V15-W-5M-PVC	Female cordset single-ended M12 angled A-coded, 5-pin, PVC cable grey