





 ϵ



Model Number

SBL-8-H/25/30

Background suppression sensor with 4-pin, M12 x 1 connector

Features

- Minimal black/white difference
- For installation between the rollers on a roller conveyor
- Protection degree IP65


Product information

Sensors of the SBL series are used to easily control material flow on roller conveyors in material handling and other branches.


The SBL series is a precise background suppression sensor according to the 3 element method. The sensor features superior background suppression and a very good ambient light immunity. Material and transport container of all colors and opacities are reliably detected.

The special design allows the sensor to be mounted between the rollers of a roller conveyor or any other conveying unit. Mounting between the rollers is easy and protects the sensor.

Dimensions



Electrical connection




- O = Light on
- = Dark on

Pinout



Indicators/operating means



	1	Signal display	yellow
	2	Sensing range adjuster	

Technical data General specifications 40 ... 900 mm Detection range Detection range min. 40 ... 340 mm 40 ... 900 mm Detection range max Adjustment range 340 ... 900 mm standard white 200 mm x 200 mm Reference target Light source Light type modulated infrared light, 880 nm Black/White difference (6 %/90 %) < 10 % Diameter of the light spot approx. 60 mm at detection range 900 mm Ambient light limit continuous light 30000 Lux, Fluorescent lamp 5000 Lux Functional safety related parameters 1100 a $MTTF_d$ Mission Time (T_M) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means Function display LED yellow: lights when object is detected Controls Detection range adjuster **Electrical specifications** 24 VDC -20% +10% Operating voltage Ripple max. 10 % No-load supply current max. 30 mA Output Switching type light on Signal output 1 NPN, short-circuit protected, reverse polarity protected Switching voltage max. 30 V DC Switching current max. 200 mA 100 Hz Switching frequency Response time 5 ms **Ambient conditions** -20 ... 50 °C (-4 ... 122 °F) Ambient temperature Storage temperature -30 ... 60 °C (-22 ... 140 °F) **Mechanical specifications** Protection degree Connection connector M12 x 1, 4-pin Material Housing plastic Optical face plastic lens approx. 50 g Mass Compliance with standards and directives Directive conformity EMC Directive 2004/108/EC Standard conformity Product standard EN 60947-5-2:2007 IEC 60947-5-2:2007 Shock and impact resistance IEC / EN 60068. half-sine, 40 g in each X, Y and Z directions Vibration resistance IEC / EN 60068-2-6. Sinus. 10 -1000 Hz, 10 g in each X, Y and Approvals and certificates **UL** approval cULus Listed, Class 2 Power Source, Type 1 enclosure CCC approval Products with a maximum operating voltage of ≤36 V do not

Accessories

OMH-SBL-01

Mounting bracket for sensors of SBL se-


Schraubendreher 0,5 x 3,0 mm Screwdriver

Additional accessories can be found in the Internet.

PEPPERL+FUCHS

bear a CCC marking because they do not require approval.

Curves/Diagrams



Additional Information

Intended use:

The transmitter and receiver are located in the same housing for direct detection sensors with background masking. Marking of objects outside the detection range is achieved by arranging the angle between the transmitter and receiver (2 receiver elements).

Objects are detected independently of the structure and colour of the surface.

The special design of the sensors makes it possible to install them between two rollers in the roller back-up conveyor systems under the material that is being moved. This allows for installation that saves space and prevents mechanical damage of the sensor caused by material being conveyed.

Mounting instructions:

The sensors can be directly fastened in place with the pass-through bore holes or can be attached with a support bracket or a clamp (the last two are not included in delivery).

The surface underneath must be flat to prevent the housing from moving when it is tightened into position. We recommend securing the nut and screw in place with spring washers to prevent the sensor from going out of adjustment.

For versions SBL-8-H-SL, -V, -Z

As many as 25 sensors can be cascaded with the aid of just one power supply. A solenoid valve is energised if the corresponding sensor itself or its predecessor in the cascade does not see any object.

It is also possible to energise the valves of all sensors included in the cascade with block movement (V_T) . To do this, apply the positive supply voltage (+UB) on the input V_T of the first sensor.

Adjustment:

Align the sensor to the background. If the yellow LED is lit, the detection range should be reduced with the detection range adjuster until the yellow LED goes out.

Object detection:

Position the object to be detected in the path of the beam. If the object is detected, the yellow LED lights up.

If it does not light up, the detection range must be further adjusted on the potentiometer until it lights up when an object is detected

Version SBL-8-H-SL-V-Z only:

The two adjusting mechanisms on the front side of the sensor can be used separately for timer functions for the switching on or switching off process.

This results in a delay defined by the adjuster between the change of state (object detected -> object not detected or vice-versa) and the switching process. The duration of the delay can be set for up to 2 seconds.

Cleaning:

We recommend cleaning the optical surface and checking all connections at regular intervals.

Note:

Use a screwdriver to adjust the sensing range. We strongly recommend to use the screwdriver given in the accessories section.

199530 ENG.xml