



Features

- Max. 24 slots for I/O modules
- 5 SIL 2 output shutdown segments
- Redundancy (power supply)
- Fieldbus type determined by base backplane
- Backplane for LB-System
- Mounting in Zone 2, Class I/Div.2 or in the safe area

Technical data

General specifications

Suitable components backplane LB9022E , backplane LB9022S , LB8111A2* , LB8105* , LB8106* , LB8108* , LB8109* , LB8107*

Slots

Supply 3
Output shut-down 5 SIL2 output shutdown segments
slots 25 ... 29, 30 ... 34, 35 ... 39, 40 ... 44, 45 ... 48

I/O modules (single width) max. 24

I/O modules (dual width) max. 12

Supply

Maximum safe voltage U_m 60 V DC (SELV/PELV)

Input voltage range U 18 ... 32 V DC (SELV/PELV)

Redundancy yes

Fieldbus interface

Fieldbus type PROFIBUS DP/DP-V1, MODBUS RTU, or MODBUS TCP , depending on the base backplane

Redundancy no

Directive conformity

Electromagnetic compatibility
Directive 2014/30/EU EN 61326-1:2006

Conformity

Electromagnetic compatibility NE 21

Degree of protection EN 60529

Ambient conditions

Ambient temperature -20 ... 60 °C (-4 ... 140 °F) , 70 °C (non-Ex)

Storage temperature -25 ... 85 °C (-13 ... 185 °F)

Relative humidity 95 % non-condensing

Shock resistance shock type I, shock duration 11 ms, shock amplitude 15 g, number of shocks 18

Vibration resistance
frequency range 10 ... 150 Hz; transition frequency: 57.56 Hz, amplitude/acceleration \pm 0.075 mm/1 g; 10 cycles
frequency range 5 ... 100 Hz; transition frequency: 13.2 Hz amplitude/acceleration \pm 1 mm/0.7 g; 90 minutes at each resonance

Damaging gas designed for operation in environmental conditions acc. to ISA-S71.04-1985, severity level G3

Mechanical specifications

Degree of protection IP20

Mass approx. 1800 g

Dimensions (W x H x D)
605 x 127 x 80 mm (23.8 x 5 x 3.15 inch) , without modules

Data for application in connection with hazardous areas

Certificate PF 08 CERT 1234 X

Marking II 3 G Ex nA IIC T4 Gc

Directive conformity
Directive 2014/34/EU EN 60079-0:2009
EN 60079-15:2010

International approvals

ATEX approval PF 08 CERT 1234 X

UL approval E106378

Control drawing 116-0321

Approved for cUL (Canada): CL I Zn. 2 IIC; IS circuits for CL I Zn. 0 IIC
ULus (USA): CL I Div. 2 Grp. A, B, C, D; IS circuits for CL I, II, III Div. 1 Grp. A, B, C, D, E, F, G

IECEX approval BVS 09.0037X

Approved for Ex nA IIC T4 Gc

EAC approval Russia: RU C-IT.MIII06.B.00129

Marine approval

Lloyd Register 15/20021

American Bureau of Shipping T1450280/UN


Bureau Veritas Marine 22449/B0 BV

General information

Supplementary information

Statement of Conformity, Declaration of Conformity, Attestation of Conformity and instructions have to be observed where applicable. For information see www.pepperl-fuchs.com.

Assembly



Release date 2017-06-21 17:24 Date of issue 2017-06-26 231658_eng.xml

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com