











Model Number

ML6-54-F/25/115/136

Retroreflective sensor with 2 m fixed cable


Features

- Precision sensor for standard applications
- Miniature design with very robust and versatile mounting options
- Objects can be reliably detected down to 0 mm: no blind zone
- Small, sharp light spot
- Rear mounting option for easy mounting without mounting bracket
- Tamper-proof version with no adjustments


Product information

The ML6 series is characterized by a robust, powerful and standard design in a miniature housing. The housing offers IP67/IP69K degree of protection, a food-grade lens, highly visible LEDs and robust all-metal bushings for mounting. Adjustable and tamper-proof sensors with a double push-pull output are available. The sensors have a high ambient light limit. Reflections from the background are suppressed. The unusually small, sharp light spot and the quick response time offer maximum switching precision on object edges. Clearly visible red light sources facilitates alignment. A high-performance fixed focus background suppressor is a useful feature. The sensors are suitable for precise object detection and open up a wide range of application fields.

Dimensions




Electrical connection



- O = Light on
- = Dark on

Indicators/operating means



1	Operating display	green
2	Signal display	yellow
3	Optical axis	



Technical data				
General specifications				
Effective detection range		0 5 m		
Reflector distance		0 5 m		
Threshold detection range		6 m		
Reference target		H85-2 reflector		
Light source		LED		
Light type		modulated visible red light, 660 nm		
Polarization filter		yes		
Angle deviation		max. ± 1°		
Diameter of the light spot		approx. 40 mm at detection range 1 m		
Angle of divergence		1.7 °		
Ambient light limit				
Continuous light		40000 Lux		
Modulated light		5000 Lux		
Functional safety related parameters				
MTTF _d		980 a		
Mission Time (T _M)		20 a		
Diagnostic Coverage (DC)		0 %		
Indicators/operating means				
Operation indicator		LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit : LED green flashing (approx. 4 Hz)		
Function indicator		LED yellow: switching state ; Stability control		
Electrical specifications				
Operating voltage	U _B	10 30 V DC		
Ripple		max. 10 %		
No-load supply current	I ₀	< 20 mA at 24 V DC		
Output				
Switching type		light/dark on, programmable		
Signal output		2 push-pull (4 in 1) outputs, complementary, short-circuit proof, reverse polarity protected		
Switching voltage		max. 30 V DC		
Switching current		max. 100 mA ≤ 2.5 V DC		
Voltage drop	U _d f	≤ 2.3 ¥ DC 1 kHz		
Switching frequency Response time		500 μs		
·		300 μ3		
Conformity Product standard		EN 60947-5-2		
		EN 00947-3-2		
Ambient conditions		20 60 °C (4 140 °E)		
Ambient temperature		-20 60 °C (-4 140 °F) -20 75 °C (-4 167 °F)		
Storage temperature		-20 75 C (-4 107 F)		
Mechanical specifications		13.9 mm		
Housing width		31.4 mm		
Housing height Housing depth		18 mm		
Degree of protection		IP67 / IP69K		
Connection		2 m fixed cable		
Material		2 III lixed cable		
Housing		ABS		
Optical face		PMMA		
Cable		PUR		
Mass		50 g		
Compliance with standards and directives				
Standard conformity				
Shock and impact resistance		IEC / EN 60068. half-sine, 40 g in each X, Y and Z directions		
Vibration resistance		IEC / EN 60068-2-6. Sinus. 10 -2000 Hz, 10 g in each X, Y and Z directions		
Approvals and certificates				
UL approval		cULus Listed		
CCC approval		CCC approval / marking not required for products rated ≤36 V		
		11 3		

Accessories

OMH-4.1

Mounting Clamp

OMH-ML6

Mounting bracket

OMH-ML6-U

Mounting bracket

OMH-ML6-Z

Mounting bracket

OMH-11-02 Aperture-V-H 0.5 mm

Slit diaphragm can be affixed for detecting very small parts

OMH-11-04 Aperture-V-H 1.0 mm

Slit diaphragm can be affixed for detecting very small parts

OMH-11-06 Aperture-V-H 1.5 mm

Slit diaphragm can be affixed for detecting very small parts

OMH-11-08 Aperture-V-H 2.0 mm

Slit diaphragm can be affixed for detecting very small parts

REF-H85-2

Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes

Reflector, round ø 84 mm, central mounting hole

REF-H60

Reflector, rectangular 40.5 mm x 60 mm, mounting holes

REF-VR10

Reflector, rectangular 60 mm x 19 mm, mounting holes

OFR-100/100

Reflective tape 100 mm x 100 mm


REF-A17


Reflector, round ø 20.5 mm, selfadhesive


Other suitable accessories can be found at www.pepperl-fuchs.com

FPEPPERL+FUCHS

Curves/Diagrams







Aperture alignment

When attaching the aperture, make sure that the sensor lens is aligned exactly with the black aperture.



