Thru-beam sensor

Model Number

MD17/MV17/115/136


Thru-beam sensor with fixed cable


Features


- Compact series in universal housing for standard applications
- Miniature design
- Front mounting with M18-threads or side mounting holes
- 360° high visibility LEDs
- Time-saving mounting with quick clamp system

Product information

The ML17 sensor family offers diverse connection and installation options, which means that it can adapt to the most varied automation tasks. In addition to the usual fitting method using M4 screws, these sensors can also be installed by means of M18 threaded insert. All devices are equipped with a green Power On display and a yellow function display. These displays are arranged in such a way that they are clearly visible from different directions.












Electrical connection





Indicators/operating means



1	Signal display	yellow
2	Operating display	green


Subject to modifications without notice Pepperl+Fuchs Group US www.pepperl-fuchs.com fa-info

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com Germany: +49 621 776-4411 fa-info@pepperl-fuchs.com Copyright Pepperl+Fuchs Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

1

MD17/MV17/<u>115/136</u>


Technical data			Accessories
System components			OMH-ML17-EZ
Emitter		MD17/115	Mounting bracket
Receiver		MV17/115/136	Mounting Blacker
General specifications			OMH-ML17
Effective detection range		0 15 m	Mounting bracket
Threshold detection range		20 m	
Light source		IRED	OMH-ML17-1
Light type		modulated infrared light , 950 nm	Mounting bracket
Ambient light limit		≤ 10000 Lux	Other suitable accessories can be found at
Indicators/operating means			www.pepperl-fuchs.com
Operating display		LED green	
Function display		LED yellow, lights up with receiver lit	
Electrical specifications			
Operating voltage	UB	10 30 V DC , class 2	
Ripple		max. 10 %	
No-load supply current	I ₀	< 25 mA	
Operating current		100 mA max per output	
Time delay before availability	t _v	≤ 200 ms	
Output			
Switching type		light/dark on	
Signal output		2 push-pull (4 in 1)outputs, short-circuit protected, reverse pola- rity protected, overvoltage protected	
Switching voltage		max. 30 V DC	
Switching current		max. 100 mA	
Voltage drop	Ud	\leq 2 V DC	
Switching frequency	f	150 Hz	
Response time		≤ 3 ms	
Ambient conditions			
Ambient temperature		-20 55 °C (-4 131 °F)	
Storage temperature		-20 75 °C (-4 167 °F)	
Mechanical specifications			
Protection degree		IP67	
Connection		2 m fixed cable	
Material			
Housing		ABS	
Optical face		Acrylic	
Mass		approx. 80 g (emitter and receiver)	
Compliance with standards and ves	d directi	-	
Standard conformity			
Product standard		EN 60947-5-2:2007 IEC 60947-5-2:2007	
Standards		EN 50178, UL 508	
Approvals and certificates			
UL approval		cULus	
CCC approval		Products with a maximum operating voltage of \leq 36 V do not bear a CCC marking because they do not require approval.	
Curves/Diagrams			
Characteristic			



Release date: 2013-01-03 21:41 Date of issue: 2013-01-03 208372_eng.xml

2





Subject to modifications without notice

Pepperl+Fuchs Group www.pepperl-fuchs.com

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Copyright Pepperl+Fuchs Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

