ML4.2-54-F/40b/95/103

Dimensions



VISC� CE c US

Model Number

ML4.2-54-F/40b/95/103


Retroreflective sensor with 4-pin, M8 x 1 connector

Features

- High-precision sensors for complex • applications
- Miniature design with very robust and ٠ versatile mounting options
- Optical surface made of scratch-• resistant glass for areas that are prone to high levels of dirt
- Objects can be reliably detected down to 0 mm: no blind zone
- Small, sharp light spot
- Tamper-proof version with no adjustments


Product information

The ML4.2 series is characterized by a robust, powerful and standard design in a miniature housing. The housing offers IP67/ IP69K degree of protection, a scratch- and chemical-resistant lens, highly visible LEDs and robust all-metal bushings for mounting. Adjustable and tamper-proof sensors are available with a universal push-pull output and an electrical light ON/dark ON switch. The sensors have a high ambient light limit. Reflections from the background are suppressed. The unusually small, sharp light spot and the quick response time offer maximum switching precision on object edges.. Both red and infrared light sources are available. A high-performance fixed focus background suppressor is a useful feature. The sensors are suitable for precise object detection and open up a wide range of application fields.



Electrical connection

Option:



Pinout






2

(brown) (white) (blue) (black)

Indicators/operating means



1	Operating display	green
2	Signal display	yellow
3	Optical axis	

1

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" USA: +1 330 486 0001

Pepperl+Fuchs Group www.pepperl-fuchs.com fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

⁵ PEPPERL+FUCHS

Technical data

General specifications Effective detection range Reflector distance Threshold detection range Reference target Light source Light type Polarization filter Angle deviation Diameter of the light spot Angle of divergence Ambient light limit Continuous light Modulated light Functional safety related parameters MTTFd Mission Time (T_M) Diagnostic Coverage (DC) Indicators/operating means Operation indicator Function indicator Electrical specifications Operating voltage UB Ripple No-load supply current I_0 Output Switching type Signal output Switching voltage Switching current Voltage drop Ud Switching frequency Response time Conformity Product standard Ambient conditions Ambient temperature Storage temperature **Mechanical specifications** Housing width Housing height Housing depth Degree of protection Connection Material Housing Optical face Mass Compliance with standards and directives Standard conformity Shock and impact resistance Vibration resistance Approvals and certificates

CE conformity UL approval CCC approval 0...5m 0...5 m 6 m H85-2 reflector I FD modulated visible red light, 660 nm yes $max. \pm 1^\circ$ approx. 40 mm at detection range 1 m 1.7 40000 Lux 5000 Lux 1940 a 20 a 0% LED green, statically lit Power on , Undervoltage indicator: Green LED, pulsing (approx. 0.8 Hz) , short-circuit : LED green flashing (approx. 4 Hz) LED yellow: switching state ; Stability control 10 ... 30 V DC max 10 % < 20 mA at 24 V DC light/dark on electrically switchable PNP, open collector, short-circuit protected max. 30 V DC max. 100 mA ≤ 2.5 V DC 1 kHz 500 µs EN 60947-5-2 -20 ... 60 °C (-4 ... 140 °F) -20 ... 75 °C (-4 ... 167 °F) 13.9 mm 31.4 mm 18 mm IP67 / IP69K M8 x 1 connector, 4-pin ABS glass pane approx. 10 g IEC / EN 60068. half-sine, 40 g in each X, Y and Z directions IEC / EN 60068-2-6. Sinus. 10 -2000 Hz, 10 g in each X, Y and Z directions

ves cULus Listed CCC approval / marking not required for products rated ≤36 V Accessories

OMH-4.1 Mounting Clamp

OMH-ML6 Mounting bracket

OMH-ML6-Z Mounting bracket

OMH-ML6-U Mounting bracket

OMH-11-02 Aperture-V-H 0.5 mm Slit diaphragm can be affixed for detecting very small parts

OMH-11-04 Aperture-V-H 1.0 mm Slit diaphragm can be affixed for detecting very small parts

OMH-11-06 Aperture-V-H 1.5 mm Slit diaphragm can be affixed for detecting very small parts

OMH-11-08 Aperture-V-H 2.0 mm Slit diaphragm can be affixed for detecting very small parts

V31-GM-2M-PVC Female cordset single-ended, M8, 4-pin, **PVC** cable

V31-WM-2M-PVC Female cordset single-ended, M8, 4-pin, **PVC** cable

REF-H85-2 Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes

REF-C110-2 Reflector, round ø 84 mm, central mounting hole

REF-H60-2 Reflector with mounting holes

REF-VR10 Reflector, rectangular 60 mm x 19 mm, mounting holes

OFR-100/100 Reflective tape 100 mm x 100 mm

REF-A17 Reflector, round ø 20.5 mm, selfadhesive

Other suitable accessories can be found at www.pepperl-fuchs.com

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" USA: +1 330 486 0001

Pepperl+Fuchs Group www.pepperl-fuchs.com


2


fa-info@us.pepperl-fuchs.com


Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com EPPERL+FUCHS

Curves/Diagrams







Refer to "General Notes Relating to Pepperl+Fuchs Product Information" Pepperl+Fuchs Group USA: +1 330 486 0001 www.pepperl-fuchs.com

fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

EPPPERL+FUCHS 3