




### Model Number

NBB1,5-8GM16-E2

### Features

- 1.5 mm flush
- Stainless steel version
- Extended temperature range
- Short version

### Connection



### Accessories


#### BF 8

Mounting flange, 8 mm

#### EXG-08

Quick mounting bracket with dead stop

### Dimensions



### Technical Data

#### General specifications

Switching element function	PNP	NO
Rated operating distance	$s_n$	1.5 mm
Installation		flush
Output polarity		DC
Assured operating distance	$s_a$	0 ... 1.2 mm
Actuating element		structural steel, e. g. 1.0037, SR235JR (formerly St37-2) 8 mm x 8 mm x 1 mm

Reduction factor $r_{Al}$	0.4
Reduction factor $r_{Cu}$	0.3
Reduction factor $r_{304}$	0.7
Reduction factor $r_{Brass}$	0.4

#### Nominal ratings

Operating voltage	$U_B$	10 ... 30 V
Switching frequency	$f$	0 ... 6000 Hz
Hysteresis	$H$	0.02 ... 0.15 mm
Reverse polarity protected		yes
Short-circuit protection		yes
Overload resistance		yes
Wire breakage protection		yes
Inductive overvoltage protection		yes
Surge suppression		yes
Ripple		10 %
Voltage drop	$U_d$	$\leq 1.5$ V
Repeat accuracy		0.02 mm
Operating current	$I_L$	0 ... 200 mA
Off-state current	$I_r$	0.01 mA
No-load supply current	$I_0$	$\leq 10$ mA
Indication of the switching state		LED, yellow

#### Functional safety related parameters

MTTF <sub>d</sub>	3530 a
Mission Time ( $T_M$ )	20 a
Diagnostic Coverage (DC)	0 %

#### Ambient conditions

Ambient temperature	-25 ... 85 °C (-13 ... 185 °F)
Storage temperature	-40 ... 85 °C (-40 ... 185 °F)

#### Mechanical specifications

Connection type	cable PVC, 2 m
Core cross-section	0.14 mm <sup>2</sup>
Housing material	Stainless steel 1.4305 / AISI 303
Sensing face	PVC
Protection degree	IP67
Mass	35 g

#### Compliance with standards and directives

Standard conformity	
Standards	EN 60947-5-2:2007 IEC 60947-5-2:2007

#### Approvals and certificates

CCC approval	Products with a maximum operating voltage of $\leq 36$ V do not bear a CCC marking because they do not require approval.
--------------	--