

Background suppression sensor SBL-8-H-900-IR/25/32/65b/73



- Background suppression sensor for roller conveyors
- For installation between the rollers on a roller conveyor
- Very small black-white difference
- Adjustable detection range

Congested track scanner, background suppression sensor, 900 mm adjustable detection range, infrared light, light on, 1 PNP output, M12 plug


Function


Sensors of the SBL serie are used to easily control material flow on roller conveyors in material handling and other branches. The SBL series is a precise background suppression sensor according to the 3 element method. The sensor features superior background suppression and a very good ambient light immunity.

Material and transport container of all colors and opacities are reliably detected. The special design allows the sensor to be mounted between the rollers of a roller conveyor or any other conveying unit. Mounting between the rollers is easy and protects the sensor.



Dimensions





Technical Data


General specifications			
Detection range		40 900 mm	
Detection range min.		40 340 mm	
Detection range max.		40 900 mm	
Adjustment range		340 900 mm	
Reference target		standard white 200 mm x 200 mm	
Light source		IRED	
Light type		modulated infrared light , 880 nm	
Black-white difference (6 %/90 %)		< 10 %	
Diameter of the light spot		approx. 60 mm at detection range 900 mm	
Ambient light limit		continuous light 30000 Lux, Fluorescent lamp 5000 Lux	
Functional safety related parameters			
MTTF _d		1100 a	
Mission Time (T _M)		20 a	
Diagnostic Coverage (DC)		0 %	
Indicators/operating means			
Function indicator		LED yellow: lights when object is detected	
Control elements		Sensing range adjuster	
Electrical specifications			
Operating voltage	UB	24 VDC -20% +10%	
Ripple		max. 10 %	
No-load supply current	I ₀	max. 20 mA	

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Technical Data

Output		
Switching type		light-on
Signal output		1 PNP, short-circuit protected, reverse polarity protected
Switching voltage		max. 30 V DC
Switching current		max. 200 mA
Switching frequency	f	100 Hz
Response time		5 ms
Conformity		
Product standard		EN 60947-5-2
Compliance with standards and directives		
Standard conformity		
Shock and impact resistance		IEC / EN 60068. half-sine, 40 g in each X, Y and Z directions
Vibration resistance		IEC / EN 60068-2-6. Sinus. 10 -1000 Hz, 10 g in each X, Y and Z directions
Approvals and certificates		
UL approval		cULus Listed, Class 2 Power Source, Type 1 enclosure
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-20 50 °C (-4 122 °F)
Storage temperature		-30 60 °C (-22 140 °F)
Mechanical specifications		
Housing width		18 mm
Housing height		100 mm
Housing depth		46 mm
Degree of protection		IP65
Connection		4-pin, M12 x 1 connector
Material		
Housing		plastic
Optical face		plastic lens
Mass		approx. 50 g

Connection Assignment



Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 223825_eng.pdf


Connection Assignment




Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)

Assembly



1	Signal display	yellow
2	Sensing range adjuster	



Difference in detection distance

Measured detection distance X [mm]

1000 · 800 600 400 200 0**+** 600 700 800 900 Adjusted detection distance X [mm] 100 200 300 400 500 Adjustment range white 90 % grey 18 % black 6 % _ _

Release date: 2023-03-28 Date of issue: 2023-03-28 Filename: 223825_eng.pdf

Accessories

	OMH-SBL-01	Mounting bracket for sensors of SBL series		
ø /	V1-G-2M-PVC	Female cordset single-ended M12 straight A-coded, 4-pin, PVC cable grey		
ø /	V1-G-5M-PVC	Female cordset single-ended M12 straight A-coded, 4-pin, PVC cable grey		
6/	V1-W-2M-PUR	Female cordset single-ended M12 angled A-coded, 4-pin, PUR cable grey		
6 /	V1-W-5M-PUR	Female cordset single-ended M12 angled A-coded, 4-pin, PUR cable grey		

 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 Get

 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com

System Description

Options:

Sensors with the **version -V** are equipped with a solenoid valve and can directly control a 3/2 way pneumatic actuator, without any-interaction of an external system controlling unit (PLC). As soon as conveyed goods are detected, the diffuse mode sensor gives an electrical-signal to the pneumatic solenoid valve, which is then activated.

Sensors with the control logic **option -SL-(V)** allows up to 50 diffuse mode sensors to be connected-to each other (data and power), depending on the current consumption of sensor and solenoid valve. An additional supply power and data bus cable is used to interconnect the sensors with control logic option -SL. All necessary functions for controlling the material flow of conveyed goods are supported, such as: single feed, single release, slug release, external motor and solenoid valve control. It is also possible to energize the valves of all sensors included in the cascade by slug release (VT). To do this, apply the positive supply voltage (+UB) on the input VT of the first sensor.

Sensors with timing **function -Z** features the adjustment of the ON- and OFF delay of the output independently. This optimizes control of the solenoid valve. A zero pressure accumulation of the conveyed goods can be realized with application of time ON- and OFF delay of the output. The ON- and OFF delay to control the switching of the solenoid valve may be adjusted between 0 and 2 seconds.

Additional power supply between every 20 to 25 sensors can be realized by the use of the power in feed junction V1S-TEE-V1/V1S in combination with a cable V1-G-...-PVC. This features to practically connect any number of SBL sensors in series. Attention should be paid to the maximum rated current of the cable and the connectors which usually is max. I = 4 A. For more details on the maximum rated current of single components, please refer to our datasheet values. For the electrical supply of the sensors the country specific standards have to be considered.

Accessories

Note:

Use a screwdriver to adjust the sensing range. We strongly recommend to use the screwdriver given in the accessories section.

Refer to "General Notes Relating to Pepperl+Fuchs Product Information